


Description

tML® is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP® and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML® cabling system as a proven tML® standard system and in the highly innovative variants tML® 12, tML® 24, tML® 32 and now tML® 24+ System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G, 400G and 800G and more.



The tML® - Inscription Panel is intended for the for the tML® - Patch Cord Management Panel TML-RP-TP-5.

Technical Data

Front plate	black
Assembly	Inscription strip
Mounting	Two fixing clips provided at the rings of the Patch Cord Management Panel are up-rested. The inscription field can be hung up then from above.
Size	1U
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Art.-No.	Description
TML-RP-L-5-BE-S	tML® - Inscription Panel for Patch Cord Management TML-RP-L-5
TML-RP-TP-5-BE-S	tML® - Inscription Panel for Patch Cord Management TML-RP-TP-5