


FO Simplex cord 50/125μ OM2 LSOH 2,4mm

Description

The standard fiber optic cable types of tde specifically for the assembling of patch and adapter cables, pigtails and trunk cables has been developed. Also the use in FTTD applications inside buildings is possible. The breakout cables have up to 24 individual elements with a 2mm diameter. The overall cable diameter is very slim.

These cables are characterized by very good termination properties. The cable jacket and the secondary coating are easy removable.



Technical Data

Flame resistance	IEC 60332-3
	IEC 60754
	IEC 61034-1
	IEC 61034-2

Cable construction

Tight buffer	1x 900μ coated fiber (free movable in the compound)
Fiber type	MM-OM2, 50/125μ, Corning
Strength members	Aramid yarn (free movable in the compound)
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Orange, RAL 2003
Identification	"t d e – IVH01G50-2.4 LSZH" and sequential meter marking + Lot number

Physical properties

Outer diameter cable	2.4 ± 0.1 mm
Temperature range	-20°C to +70°C

FO Fiber

Type	Corning 50/125μ OM2 multimode fiber
------	-------------------------------------

FO Simplex cord 50/125 μ OM2 LSOH 2,4mm

Manufacturer	Corning
--------------	---------

Optical Specifications

Bandwidth	500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 2.5 dB/km At 1300 nm max. ≤ 0.8 dB/km
Numerical Aperture	0.200 ± 0.015

Dimensional Specifications

Core Diameter	$50.0 \pm 3.0 \mu\text{m}$
Cladding Diameter	$125.0 \pm 2.0 \mu\text{m}$
Core-Clad Concentricity	$\leq 3.0 \mu\text{m}$
Cladding Non-Circularity	$< 2.0\%$
Core Non-Circularity	$\leq 5.0\%$
Coating Diameter	$245 \pm 5 \mu\text{m}$
Coating-Cladding Concentricity	$< 12 \mu\text{m}$

Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to $+85^{\circ}\text{C}$	≤ 0.20
Temperature Humidity Cycling	-10°C to $+85^{\circ}\text{C}$ and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to $+85^{\circ}\text{C}$	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m ²).
Length	Fiber lengths available up to 8.8 km/spool.

Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.490 1300 nm: 1.486

FO Simplex cord 50/125μ OM2 LSOH 2,4mm

Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Cromatic Dispersion	Zero Dispersion Wavelength (λ_0): 1300 nm $\leq \lambda_0 \leq$ 1320 nm Zero Dispersion Slope (S0): ≤ 0.101 ps/(nm ² *km)

Art.-No.	Description
L-IVH01E09-2.4	FO Simplex cord 9/125μ G.652.D LSOH 2,4mm
L-IVH01G50-2.4	FO Simplex cord 50/125μ OM2 LSOH 2,4mm
L-IVH01G50-OM3-2.4	FO Simplex cord 50/125μ OM3 LSOH 2,4mm
L-IVH01G50-OM4-2.4	FO Simplex cord 50/125μ OM4 LSOH 2,4mm
L-IVH01G62-2.4	FO Simplex cord 62,5/125μ OM1 LSOH 2,4mm