


# FO Simplexcord 50/125 $\mu$ OM2 LSOH 2,0mm

## Description

The standard fiber optic cable types of tde specifically for the assembling of patch and adapter cables, pigtails and trunk cables has been developed. Also the use in FTTH applications inside buildings is possible. The breakout cables have up to 24 individual elements with a 2mm diameter. The overall cable diameter is very slim.

These cables are characterized by very good termination properties. The cable jacket and the secondary coating are easy removable.



## Technical Data

### Cable Data

Fiber Amount	1
Fiber Type	MM-OM2, 50/125 $\mu$ , Corning
Secondary Coating	900 $\mu$ , easy strippable
Strength Members	Aramid yarns
Outer Jacket	LSOH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket Colour	Orange
Outer Diameter	2.0 ( $\pm$ 0.1mm)
Standard printing	"t d e – IVH01G50/125-2.0" and sequential meter marking + Lot number
Applications	Patchcords/ Pigtails

### Mechanical/ Thermal Characteristics

Weight	6 kg/km
Operational tensile load	105 N
Bending radius	10 x outer diameter
Operating temperature	-5°C to + 60°C
Fire resistance	Pass (EN 50266, IEC 60332-3)
Halogen content	Free (EN 50267, IEC 60754)
Smoke density	Low (EN 50268, IEC 61034-1/2)

# FO Simplexcore 50/125µ OM2 LSOH 2,0mm

## Special features

Characteristics	Fiber and aramid yarn free movable in the compound
-----------------	--

## FO Fiber

Type	Corning 50/125µ OM2 multimode fiber
Manufacturer	Corning

## Optical Specifications

Bandwidth	500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 2.5 dB/km At 1300 nm max. ≤ 0.8 dB/km
Numerical Aperture	0.200 ± 0.015

## Dimensional Specifications

Core Diameter	50.0 ± 3.0 µm
Cladding Diameter	125.0 ± 2.0 µm
Core-Clad Concentricity	≤ 3.0 µm
Cladding Non-Circularity	< 2.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	245 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

## Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

## Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m <sup>2</sup> ).
Length	Fiber lengths available up to 8.8 km/spool.

## FO Simplex cord 50/125 $\mu$ OM2 LSOH 2,0mm

### Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.490 1300 nm: 1.486
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength ( $\lambda_0$ ): 1300 nm $\leq \lambda_0 \leq$ 1320 nm Zero Dispersion Slope (S0): $\leq 0.101$ ps/(nm <sup>2</sup> *km)

Art.-No.	Description
L-IVH01E09-2.0	FO Simplex cord 9/125 $\mu$ G.652.D LSOH 2,0mm
L-IVH01G50-2.0	FO Simplex cord 50/125 $\mu$ OM2 LSOH 2,0mm
L-IVH01G50-OM3-2.0	FO Simplex cord 50/125 $\mu$ OM3 LSOH 2,0mm
L-IVH01G50-OM4-2.0	FO Simplex cord 50/125 $\mu$ OM4 LSOH 2,0mm
L-IVH01G62-2.0	FO Simplex cord 62,5/125 $\mu$ OM1 LSOH 2,0mm