

## Description

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards, and the company has one of the most up-to-date fiber optic assembly houses in Europe. Fiber optic patch cables and trunk cables are manufactured in many different configurations using highly automated processes on two independent mass production lines. The range of products on offer encompasses the entire spectrum of connector types available on the market. Production capacity is around 100,000 fiber optic connectors per month, and this can be ramped up easily whenever required. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment such as laser cleavers and glue-dispensing robots.

Each cable application is subjected to a full test procedure comprising interferometer measurements, insertion loss and return loss measurements and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.



## Technical Data

The FO patch cord is preterminated with MPO/MTP® connectors on both ends. The Cable is very slim and flexible. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3µ with a difference ≤ 0,5µ. All system components (modules, trunk cables and patch cords) are coordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number.

Cable	Round cable, 3mm, loose tube, LSOH, magenta
Option	Unsesitive ClearCurve® Corning fiber
Connectors	MPO/MTP®Female Push Pull (magenta)
Pin out	Method A
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

xxx - stands for the cable length in m (every length available)

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a

# FO Patch cord MPO/MPO Female 12G50/125µ OM4 LSOH, Type A, Length: xxxxx

defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

## FO Connectors

Type	MPO/MTP® Female Push Pull Locking (Magenta)
Ferrule	12 Fiber MM Elite® ferrule, PPS
Boot colour	Black
Temperature range	-40°C bis +75°C
Manufacturer	tde/US Conec

## Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM4	MPO/MTP®	850 nm	≤ 0.25 dB	0.45 dB	20 dB

## FO Cables

Standards	EN 50173-5
	IEC 60794-2-20
	ISO/IEC 24764
Flame resistance	IEC 60332-1-2
	IEC 60332-2-2
	IEC 60754-1
	IEC 60754-2
	IEC 61034

## Cable construction

Type	IVH12G50-OM4
Loose tube	12 coated fibers within PVC-core tube
Wall thickness PVC-tube	0.20 mm – 0.25 mm
Fiber type	MM-OM4, 50/125µ, Corning ClearCurve OM4
Strength members	Aramid yarn
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Magenta, RAL 4003
Identification	"t d e – IVH12G50-MPO-OM4 LSZH" and sequential meter marking + Lot number

# FO Patch cord MPO/MPO Female 12G50/125µ OM4 LSOH, Type A, Length: xxxxx

## Physical properties

Outer diameter cable	3.0 ± 0.1 mm
Diameter PVC-core tube	1.8 ± 0.1 mm
Max. tensile load	300 N
Min. bending radius	30 mm
Temperature range (storage, installation, operation)	-20°C to +70°C

## FO Fiber

Type	Corning ClearCurve® 50/125µ OM4 multimode fiber
Optimized Data Rate over Distance	40/100 Gb over 170 m* 10 Gb/s over 550 m 1 Gb/s over 1100 m
Standard Compliance	ISO/IEC 11801: type OM4 fiber** IEC 60793-2-10: type A1a.3 fiber** TIA/EIA: 492AAAD ITU: ITU G651.1
*	Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation ≤3.0 dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4)
**	Assumes IEC draft standard is harmonized with 492AAAD which was approved by TIA

## Optical Specifications

Bandwidth	High Performance EMB* (MHz.km): 4700 at 850 nm only Legacy Performance EMB** (MHz.km): 3500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 2.3 dB/km At 1300 nm max. ≤ 0.6 dB/km
Macrobend Loss	Mandrel Radius (mm): 37.2 / 15 / 7.5 Number of Turns: 100 / 2 / 2 Induced Attenuation (dB) at 850 nm: ≤ 0.05 / ≤ 0.1 / 0.2 Induced Attenuation (dB) at 1300 nm: ≤ 0.15 / ≤ 0.3 / ≤ 0.5
Numerical Aperture	0.200 ± 0.015
*	Ensured via miniEMBc, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10Gb/s)
**	OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s)

## Dimensional Specifications

Core Diameter	50.0 ± 2.5 µm
---------------	---------------

# FO Patch cord MPO/MPO Female 12G50/125µ OM4 LSOH, Type A, Length: xxxxx

Cladding Diameter	125.0 ± 1.0 µm
Core-Clad Concentricity	≤ 1.5 µm
Cladding Non-Circularity	≤ 1.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	242 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

## Environmental

Environmental Test	Test Condition	Induced Attenuation 850 nm & 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.10
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.10
Water Immersion	23°C ± 2°C	≤ 0.20
Heat Aging	85°C ± 2°C	≤ 0.20
Damp Heat	85°C at 85% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

## Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m <sup>2</sup> ).
Length	Fiber lengths available up to 17.6 km/spool.

## Performance Characterizations

Refractive Index Difference	1%
Effective Group Index of Refraction	850 nm: 1.480 1300 nm: 1.479
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength ( $\lambda_0$ ): 1295 nm ≤ $\lambda_0$ ≤ 1315 nm Zero Dispersion Slope ( $S_0$ ): ≤ 0.101 ps/(nm <sup>2</sup> *km)

Art.-No.	Description
L-MP/MP50112G4Axxxxx	FO Patch cord MPO/MPO Female 12G50/125µ OM4 LSOH, Type A, Length: xxxxx

# FO Patch cord MPO/MPO Female 12G50/125 $\mu$ OM4 LSOH, Type A, Length: xxxxx

Art.-No.	Description
L-MP/MP50I12G4Bxxx	FO Patch cord MPO/MPO Female 12G50/125 $\mu$ OM4 LSOH, Type B, Length: xxx
L-MP/MPP50I12G4Axxx	FO Patch cord MPO/MPO Female/Male 12G50/125 $\mu$ OM4 LSOH, Type A, Length: xxx
L-MP/MPP50I12G4Bxxx	FO Patch cord MPO/MPO Female/Male 12G50/125 $\mu$ OM4 LSOH, Type B, Length: xxx
L-MPP/MPP50I12G4Axxx	FO Patch cord MPO/MPO Male 12G50/125 $\mu$ OM4 LSOH, Type A, Length: xxx
L-MPP/MPP50I12G4Bxxx	FO Patch cord MPO/MPO Male 12G50/125 $\mu$ OM4 LSOH, Type B, Length: xxx