

tML® - Floor box frame for up to two FO or TP Modules with adjustable angle

Description

tML® is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP® and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 400G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML® cabling system as a proven tML® standard system and in the highly innovative variants tML® 12, tML® 24, tML® 32 and now tML® 24+ System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G, 400G and 800G and more.



tML® - Floor box frame is intended for the integration of up to two tML® - modules into a Ackermann GES9 Floor Box.

Technical Data

All existing tML® - FO or TP modules can be installed. Up to two equal or also different modules can be fastened at the frame with in each case two screws. The modules are then adjustable in a 15° angle.

Material	galvanized steel sheet
Colour	black
Inscription	Label strip self adhesive for free port inscription
Grounding	Grounding screw
Max. Angle	ca. 15°
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Art.-No.	Description
TML-BO-EINSATZ	tML® - Floor box frame for up to two FO or TP Modules with adjustable angle