

TP faceplate with 2x RJ45 (NewLine RJ)

Description

The NewLine system includes the NewLine MMC3000pro modular sockets for multimedia applications, NewLine RJ and NewLine RJpro for class EA applications, in line with ISO/IEC 11801 for 10 Gigabit Ethernet via copper, and NewLine RJ250 for class E applications in shielded and unshielded design. Because of the compact structure it is possible to integrate the high-performance sockets into connection units of the highest packing density. NewLine wall outlets accommodate up to 3 sockets. In addition to the standard panels with 16, 24 and 32 ports, we can also offer you a 48-port panel on only one rack unit.



Technical Data

| | |
|---------------|---|
| Dimensions | 50 x 50 mm |
| Color | White |
| Jack openings | 2x for NewLine with screw on dust cover |

NewLine RJ

| | |
|-----------------------|------------------------|
| Type | RJ45 (NewLine RJ) |
| Dimensions | 35x16x14mm (LxBxH) |
| Housing | ZN |
| Surface | Cu under Ni |
| Contact | Messing Ni / Ag 0.8 µm |
| Cutcontact | Beryllium Cu / Sn |
| Mating cycles | > 750 |
| Contact resistance | 4.3 mOhm typ. |
| Insulation resistance | > 500 MOhm |
| Operating current | 0.63 A max. |
| Core diameter | AWG24-AWG22 |
| Gland Radial | 360° |

xx stands for the color

TP faceplate with 2x RJ45 (NewLine RJ)

| Art.-No. | Description |
|---------------------|--|
| 413-7415WS9010-RJ45 | TP faceplate with 2x RJ45 (NewLine RJ) |