

1.25Gbps GBIC Module SM SC 70km data range (1550nm)

Description

The tde Small Form Pluggable Optical Transceiver are easy installed for enterprise and telecom applications. The tde SFP modular line provides a fully compatible, highly reliable and volume accessible supply of quality transceiver products with excellent performance for design-in manufacturing and end-user enterprise applications.



Technical Data

Features

- Operating data rate up to 1.25Gbps
- 1550nm DFB Transmitter
- Distance Up to 70km
- 3.3/5V Power supply and TTL Logic Interface
- Duplex SC Connector Interface
- Hot Pluggable
- Operating Case Temperature Standard: 0°C~+70°C, Industrial: -40°C~+85°C
- Compliant with GBIC Specification Rev. 5.5

Applications

- WDM Fast Ethernet Links
- SONET/SDH Equipment Interconnect
- Fiber Channel Links

Regulatory Compliance

Feature	Standard	Performance
Electrostatic Discharge (ESD) to the Electrical Pins	MIL-STD-883E Method 3015.7	Class 1(>500 V) Isolation with the case
Electromagnetic Interference (EMI)	FCC Part 15 Class B	Compatible with standards
Laser Eye Safety	FDA 21CFR 1040.10 and 1040.11 EN60950, EN (IEC) 60825-1,2	Compatible with Class I laser product. Compatible with T üV standards
Component Recognition	UL and CUL	UL file E317337
Green Products	RoHS	RoHS6

1.25Gbps GBIC Module SM SC 70km data range (1550nm)

Absolute Maximum Ratings

Parameter	Symbol	Min.	Max.	Unit
Storage Temperature	TS	-40	+85	°C
Supply Voltage	Vcc	-0.5	6	V

Recommended Operating Conditions

Parameter	Symbol	Min.	Typ.	Max.	Unit
Operating Case Temperature	TA / ASG-ZX	-40		+85	°C
Power Supply Voltage	Vcc	4.75 3.15	5 3.3	5.25 3.45	V V
Power Supply Current	Icc			300	mA
Surge Current	ISurge			+30	mA
Baud Rate			1.25		GBaud

Performance Specifications - Electrical

Parameter	Symbol	Min.	Typ.	Max.	Unit	Notes
Transmitter						
LVPECL Inputs (Differential)	Vin	400		2500	mVp	AC coupled inputs
Input Impedance (Differential)	Zin	85	100	115	ohms	Rin > 100 kohms @ DC
Tx_DISABLE Input Voltage - High		2		Vcc+0.3	V	
Tx_DISABLE Input Voltage - Low		0		0.8	V	
Tx_FAULT Output Voltage - High		2		Vcc+0.3	V	Io = 400µA; Host Vcc
Tx_FAULT Output Voltage - Low		0		0,5	V	Io = -4.0mA
Receiver						
LVPECL Outputs (Differential)	Vout	400	800	1200	mVpp	AC coupled outputs
Output Impedance (Differential)	Zout	85	100	115	ohms	

1.25Gbps GBIC Module SM SC 70km data range (1550nm)

Rx_LOS Output Voltage - High	2	Vcc+0.3	V	Io = 400µA; Host Vcc
Rx_LOS Output Voltage - Low	0	0.8	V	Io = -4.0mA
MOD_DEF (0:2) VoH	2.5		V	With Serial ID
VoL	0	0.5	V	

Optical and Electrical Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit
9µm Core Diameter SMF / ASG-ZX			80		km
Data Rate			1.25		Gbps
Transmitter					
Centre Wavelength	λ_c	1500	1550	1580	nm
Spectral Width (-20dB)	σ			1	nm
Average Output Power / ASG-ZX	P Out	0		+5	dBm
Extinction Ratio	EX	9			dB
Rise/Fall Time (20%~80%)	tr/tf			260	ns
Output Optical Eye	ITU-T G.957 Compliant				
Data Input Swing Differential	V IN	500		2000	mV
Input Differential Impedance	ZIN	90	100	110	Ω
TX Disable - Disable - Enable		2.0 0		VCC+0.3 0.8	V V
TX_Fault - Fault - Normal		2.0 0		VCC+0.3 0.8	V V
TX_Disable Assert Time	t _{off}			10	us
Receiver					
Centre Wavelength	λ_c	1100		1600	nm
Sensitivity / ASG-ZX	PIN			-24	dBm
Output Differential Impedance	P IN	90	100	110	Ω
Data Output Swing Differential	VOUT	370		2000	mV

1.25Gbps GBIC Module SM SC 70km data range (1550nm)

Rise/Fall Time	Tr/tf			2.2	ns
LOS De-Assert	LOSD			-25	dBm
LOS Assert	LOSA	-40			dBm
LOS - High		2.0		VCC+0.3	V
- Low		0		0.8	V

Art.-No.	Description
TDE-ASG-ZX	1.25Gbps GBIC Module SM SC 70km data range (1550nm)