


FO Duplex cord 62,5/125µ OM1 LSOH 1,8mm for MTRJ assembly



tde - Standard FO Cables

The standard fiber optic cable types of tde specifically for the assembling of patch and adapter cables, pigtails and trunk cables has been developed. Also the use in FTTD applications inside buildings is possible. The breakout cables have up to 24 individual elements with a 2mm diameter. The overall cable diameter is very slim.

These cables are characterized by very good termination properties. The cable jacket and the secondary coating are easy removable.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

FO Duplex cord 62,5/125μ OM1 LSOH 1,8mm for MTRJ assembly

Technical Data

Flame resistance	IEC 60332-3
	IEC 60754
	IEC 61034-1
	IEC 61034-2

Cable construction

Tight buffer	2x 600μ coated fibers (free movable in the compound)
Fiber type	MM-OM1, 62.5/125μ, Corning
Strength members	Aramid yarn (free movable in the compound)
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Orange, RAL 2003
Identification	"t d e – IVH02G62-1.8 LSZH" and sequential meter marking + Lot number

Physical properties

Outer diameter cable	2x 1.8 ± 0.1 mm
Temperature range	-20°C to +70°C

FO Fiber

Type	Corning 62.5/125μ OM1 multimode fiber
Manufacturer	Corning

Optical Specifications

Bandwidth	160/200 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 3.0 dB/km At 1300 nm max. ≤ 0.7 dB/km
Numerical Aperture	0.275 ± 0.015

Dimensional Specifications

Core Diameter	62.5 ± 3.0 μm
Cladding Diameter	125.0 ± 2.0 μm
Core-Clad Concentricity	≤ 3.0 μm
Cladding Non-Circularity	< 2.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	245 ± 5 μm
Coating-Cladding Concentricity	< 12 μm

FO Duplex cord 62,5/125μ OM1 LSOH 1,8mm for MTRJ assembly

Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m²).
Length	Fiber lengths available up to 17.6 km/spool.

Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.496 1300 nm: 1.491
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength (λ ₀): 1332 nm ≤ λ ₀ ≤ 1354 nm Zero Dispersion Slope (S ₀): ≤ 0.097 ps/(nm²*km)

Product variants & accessories

Art.-No.	Description
L-IVH02G62-1.8	FO Duplex cord 62,5/125μ OM1 LSOH 1,8mm for MTRJ assembly