
FO Simplex cord 62,5/125µ OM1 LSOH 1,8mm



tde - Standard FO Cables

The standard fiber optic cable types of tde specifically for the assembling of patch and adapter cables, pigtails and trunk cables has been developed. Also the use in FTTD applications inside buildings is possible. The breakout cables have up to 24 individual elements with a 2mm diameter. The overall cable diameter is very slim.

These cables are characterized by very good termination properties. The cable jacket and the secondary coating are easy removable.

tde® trans data elektronik GmbH

Headquarter address:
Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:
Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

 © tde GmbH, all rights reserved, errors excepted.

FO Simplex cord 62,5/125µ OM1 LSOH 1,8mm

Technical Data

Cable Data

Fiber Amount	1
Fiber Type	MM-OM1, 62.5/125µ, Corning InfiniCor
Secondary Coating	600µ, easy strippable
Strength Members	Aramid yarns
Outer Jacket	LSOH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket Colour	Orange
Outer Diameter	1.8 (± 0.1mm)
Standard printing	“t d e – IVH01G62/125-1.8” and sequential meter marking + Lot number
Apllications	Patchcords/ Pigtails

Mechanical/ Thermal Characteristics

Weight	6 kg/km
Operational tensile load	105 N
Bending radius	15 x outer diamter
Operating temperature	-5°C to + 60°C
Fire resistance	Pass (EN 50266, IEC 60332-3)
Halogen content	Free (EN 50267, IEC 60754)
Smoke density	Low (EN 50268, IEC 61034-1/2)

Special features

Characteristics	Fiber and aramid yarn free movable in the compound

FO Fiber

Type	Corning 62.5/125µ OM1 multimode fiber
Manufacturer	Corning

Optical Specifications

Bandwidth	160/200 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 3.0 dB/km At 1300 nm max. ≤ 0.7 dB/km
Numerical Aperture	0.275 ± 0.015

Dimensional Specifications

Core Diameter	62.5 ± 3.0 µm
Cladding Diameter	125.0 ± 2.0 µm
Core-Clad Concentricity	≤ 3.0 µm

© tde GmbH, all rights reserved, errors excepted.

FO Simplex cord 62,5/125µ OM1 LSOH 1,8mm

Cladding Non-Circularity	< 2.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	245 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

Environmental Specifications

Enviromental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m²).
Length	Fiber lengths available up to 17.6 km/spool.

Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.496 1300 nm: 1.491
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Cromatic Dispersion	Zero Dispersion Wavelength (λ0): 1332 nm ≤λ0 ≤ 1354 nm Zero Dispersion Slope (S0): ≤ 0.097 ps/(nm²*km)

Product variants & accessories

Art.-No.	Description
L-IVH01E09-1.8	FO Simplex cord 9/125µ G.652.D LSOH 1,8mm
L-IVH01G50-1.8	FO Simplexcord 50/125µ OM2 LSOH 1,8mm
L-IVH01G50-OM3-1.8	FO Simplex cord 50/125µ OM3 LSOH 1,8mm
L-IVH01G50-OM4-1.8	FO Simplex cord 50/125µ OM4 LSOH 1,8mm
L-IVH01G62-1.8	FO Simplex cord 62,5/125µ OM1 LSOH 1,8mm

© tde GmbH, all rights reserved, errors excepted.