


tML® - TP Patch Cord Management 19" Panel 1U Vario, 10 rings, grey



tML® - tde Modular Link

tML® is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP® and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML® cabling system as a proven tML® standard system and in the highly innovative variants tML® Xtended, tML® 24 System and now tML® 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

tML® - TP Patch Cord Management 19" Panel for the regulatory horizontal cable run of patch cords.



tde® trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML® - TP Patch Cord Managment 19" Panel 1U Vario, 10 rings, grey

Technical Data

Front plate	grey
Assembly	10 rings can be put and engaged separately from the front Stepless adjustment from 5.0mm to 110.0mm Number of rings can vary from 1 to 10
Cable entry	Patch cords are from the front inserted
Size	19", 1U
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Product variants & accessories

Art.-No.	Description
TML-RP-TP-V-GR	tML® - TP Patch Cord Managment 19" Panel 1U Vario, 10 rings, grey
TML-RP-TP-V-S	tML® - TP Patch Cord Managment 19" Panel 1U Vario, 10 rings, black