


## Military B-Series Breakout Mil-Tac Cable 2G50/125μ



### tde - Mil-Tac Cable

Applications: Mil-Tac cables are ideal for use in harsh environments where deployment and retrieval for reuse is required.

- Extremely strong, lightweight, rugged, survivable tight-buffered cables designed for military tactical field use and commercial applications
- Compact, round cable design for ease of transportation and deployment
- Designed for use in adverse environments where reduced size and weight are important
- Helically stranded cable core for flexibility, deployment survivability and exceptional mechanical protection for the optical fibers
- Cables have been tested and are in use in military data communications applications worldwide
- Can be used outdoors for temporary deployment directly on the ground in all terrains, including severe environments
- Suitable for industrial, mining and petrochemical environments
- Crush-resistant and resilient with a thick layer of aramid strength members
- Polyurethane jacketed for abrasion, cut and chemical resistance



**tde<sup>®</sup>** trans data elektronik GmbH

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## Military B-Series Breakout Mil-Tac Cable 2G50/125µ

### Technical Data

#### General Characteristics

Impact Resistance	200 Impacts
Crush Resistance	440 N/cm
Flex Resistance	2.000 Cycles
Operating Temperature	-55°C to +85°C
Storage Temperature	-70°C to +85°C

#### Specifications

Fiber Count	2
Diameter	6.5 mm
Weight	36 kg/km
Installation Tensile Load	2.200 N
Operational Tensile Load	550 N
Minimum Bend Radius Installation	6.5 cm
Minimum Bend Radius Operational	3.3 cm

#### FO Fiber

Type	Multimode OM2 ISO/IEC 11801
Core diameter	50 µm
Cladding diameter	125 µm
Numeric aperture	0.20
Wavelength	850/1310 nm
Gigabit Ethernet	550/550 m
10-Gigabit Ethernet	82/300 m (1310 CWDM lasers (10GBASE-LX4))
Maximum cabled attenuation	3.5/1.5 dB/km
Minimum Laser EMB bandwidth	500/500 MHz-km
Minimum OFL LED bandwidth	500/500 MHz-km

### Product variants & accessories

Art.-No.	Description
MILTAC-B02G50	Military B-Series Breakout Mil-Tac Cable 2G50/125µ
MILTAC-B04G50	Military B-Series Breakout Mil-Tac Cable 4G50/125µ
MILTAC-B06G50	Military B-Series Breakout Mil-Tac Cable 6G50/125µ
MILTAC-B08G50	Military B-Series Breakout Mil-Tac Cable 8G50/125µ
MILTAC-B10G50	Military B-Series Breakout Mil-Tac Cable 10G50/125µ
MILTAC-B12G50	Military B-Series Breakout Mil-Tac Cable 12G50/125µ
MILTAC-B18G50	Military B-Series Breakout Mil-Tac Cable 18G50/125µ
MILTAC-B24G50	Military B-Series Breakout Mil-Tac Cable 24G50/125µ