

## tML® - RJ45 DC 6fold Module Cat.6<sub>A</sub> ISO/IEC with LID



## tML® - tde Modular Link

tML® is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP® and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML® cabling system as a proven tML® standard system and in the highly innovative variants tML® Xtended, tML® 24 System and now tML® 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.



### **tde®** trans data elektronik GmbH

#### **Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

#### **Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## tML® - RJ45 DC 6fold Module Cat.6<sub>A</sub> ISO/IEC with LID

### Technical Data

System platforms	tML®/ tSML
	4x tBL® - 6fold Modules can be integrated in a tSML - TP Module.
	1x tBL® - 6fold Module can be integrated in a tML® - TP Module.
Equipping	6x tBL® RJ45 DC Module Cat.6 <sub>A</sub>

### tBL® - RJ45 DC-Module Cat.6<sub>A</sub> ISO/IEC with LID w/o termination block

#### Mechanical properties

Type	RJ45 Jack shielded LID
Connector standard	IEC 60603-7-5-1
Installation dimension	19.3 x 14.7 mm
Mating force	≤30 N
Mating cycles (RJ45 side)	≥750
Mating cycles (opposite side)	≥100
Housing material	nickel-plated die-cast zinc
Insulation components material	PC aqua opak
Gold plating in contact area	30 μ"
Contacting	AWG 27-22
Cable diameter	5-10 mm

#### Environmental requirements

Connection class	IP20
Temperature range	-40°C to +70°C

#### Electrical properties

Contact resistance	≤20 mΩ
Insulation resistance between contacts	≥500 MΩ
Dielectric withstanding voltage contact – contact	≥1000 V DC/AC
Dielectric withstanding voltage contact – screen	--
Current-carrying capacity at 50°C	1.25 A
PoE+ per IEEE 802.3at	PoE+

#### Transmission characteristics

10 GbE	supported
Cat.6 <sub>A</sub>	ISO/IEC 11801 AM1 and AMD2, Link length: >1 m

## tML<sup>®</sup> - RJ45 DC 6fold Module Cat.6<sub>A</sub> ISO/IEC with LID

### LiD Function

supply voltage	12 V DC
lightdetection	≥200 m
light exits	≤20

### Product variants & accessories

Art.-No.	Description
TML-RJ45DCLX6	tML <sup>®</sup> - RJ45 DC 6fold Module Cat.6 <sub>A</sub> ISO/IEC with LID
TML-RJ45DCX6	tML <sup>®</sup> - RJ45 DC 6fold Module Cat.6 <sub>A</sub> ISO/IEC