


100Mbps to 2.5Gbps fiber repeater with two open SFP slots, any-rate to same-rate. ION Chassis Card  
media converter



## Direct Attach Cables / Active Optical Cables

A simple to install, cost-effective and interoperable solution

Often used for data center short-reach interconnects, Direct Attach, Active Copper and Active Optical Cables are an indispensable part of any network.

Terminated with transceiver-style connectors, they are designed to be used in the same ports as a typical SFP+ or QSFP transceiver, with no need for adapters or converters. Our DAC and AOC cables offer compatibility with a huge range of vendors, enabling the connectivity you need within the Top of Rack and End of Row environments.

- 10G, 25G, 40G & 100G product solutions
- Seamless interoperability with network equipment
- Multi-code options enabling different OEM vendors at each end of the cable
- 4x breakout cables, 40G QSFP+ to 4x 10G SFP and 100G QSFP28 to 4x 25G SFP28
- Fast Delivery, Custom solutions
- Compatible with Over 90 Systems
- Savings of up to 70%



**tde®** trans data elektronik GmbH

### Hausanschrift:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Vertriebsbüro:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## 100Mbps to 2.5Gbps fiber repeater with two open SFP slots, any-rate to same-rate. ION Chassis Card media converter

The ION C3100 is a fiber to fiber media converter module. It is protocol independent and supports data rates from 100Mbps to 2.5Gbps through two open SFP slots. This any-rate to same-rate converter can be used to perform reliable and cost-effective single mode to multimode fiber conversion or it can be used to provide wavelength conversion in CWDM applications. The ION C3100 is a manageable device when installed in a managed ION chassis.

### Features

- Protocol Transparent
- Supports data rates from 100Mbps to 2.5Gbps
- Any-rate to same-rate conversion
- SFP to SFP Fiber Repeater
- Specific wavelength CWDM Transponder
- Supported protocols: Fast Ethernet, Gigabit Ethernet, SONET (OC-3/12/48), 1 & 2 Gig Fiber Channel, 2.5G InfiniBand, FDDI, ESCON/SBCON
- DMI, Digital diagnostics statistics available through ION Management Module
- Link Pass Through
- Automatic Link Restoration

### Technische Daten

#### Standards

- Multi-Source Agreement (MSA)
- Small Form Factor Pluggable (SFP)

#### Data Rate

- Protocol Independent
- 100 Mbps to 2.5 Gbps

#### Max Frame Size

- 16384 bytes Jumbo Frames Supported

#### Status LEDs

- PWR ON (Green) = Power
- Port 1 Link ON = Fiber Signal Detected

100Mbps to 2.5Gbps fiber repeater with two open SFP slots, any-rate to same-rate. ION Chassis Card  
media converter

- Port 2 Link ON = Fiber Signal Detected

## Dimensions

- Width: 0.86" [22 mm]
- Depth: 6.5" [165 mm]
- Height: 3.4" [86 mm]

## Power Consumption

- 2-3 Watts, based on the SFP modules used

## Power Supply

- External AC/DC required: 12VDC

## Environment

- Environment specs are dependent on the chassis chosen
- Operating: 0°C to 50°C
- Humidity: 5% to 95% (non-condensing)
- Altitude: 0 – 10,000 ft.

## Weight

- 1 lb. [0.45 kg]

## MTBF

- Greater than 250,000 hours (MIL-HDBK-217F)
- Greater than 687,000 hours (Bellcore)

## Certifications

- FCC Class A, EN55022 Class A, EN55024, CE Mark

## Warranty

100Mbps to 2.5Gbps fiber repeater with two open SFP slots, any-rate to same-rate. ION Chassis Card media converter

- Lifetime

## Artikelvarianten & Zubehör

Art.-Nr.	Beschreibung
C3100-4040	100Mbps to 2.5Gbps fiber repeater with two open SFP slots, any-rate to same-rate. ION Chassis Card media converter