

EOL - Finisar - SFP 4G Transceiver, Singlemode LC, 4.25 Gb/s, 4km



Finisar - Transceiver

Finisar's broad product selection and innovative technology have made Finisar the optical module manufacturer of choice for all major networking equipment vendors worldwide. The products are fully compliant with Ethernet, Fiber Channel, Infiniband, SONET/SDH/OTN and PON standards and operate at data rates up to 100 Gb/s. They are capable of distances ranging from very short reach within a datacenter to campus, access, metro, and long-haul reaches. They feature outstanding performance over extended voltage and temperature ranges, while minimizing jitter, electromagnetic interference (EMI) and power dissipation.

Finisar's FTLF1324P2xTy Small Form Factor Pluggable (SFP) transceivers are compatible with the Small Form Factor Pluggable Multi-Sourcing Agreement (MSA). They are compatible with Fiber Channel FC-PI-2 10.0 standard for 4km distances at 4.25 Gb/s and 10km distances at 2.125 and 1.06 Gb/s. Rate selectable versions are also simultaneously compatible with Gigabit Ethernet 1000Base-LX as specified in IEEE Std 802.3 and 1000Base-LX10 as specified in IEEE Draft P802.3ah/D2.0. The product is RoHS compliant and lead-free per Directive 2002/95/EC and Finisar Application Note AN-2038.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

EOL - Finisar - SFP 4G Transceiver, Singlemode LC, 4.25 Gb/s, 4km

Technical Data

Key Features	Up to 4.25 Gb/s bi-directional data links
	Hot-pluggable SFP footprint
	Built-in digital diagnostic functions
	1310nm Fabry-Perot laser transmitter
	Duplex LC connector
	RoHS compliant and Lead-Free
	Up to 4 km at 4.25 Gb/s and 10 km at ≤ 2.125 Gb/s on 9/125 µm SMF
	Metal enclosure, for lower EMI
	Single 3.3 V power supply
	Industrial operating temperature range: -40°C to +85°C

Applications	1.25Gb/s 1000Base-LX Ethernet and 1000Base-LX10
	Tri Rate 1.06/2.125/4.25 Gb/s Fiber Channel

On request also available for	Brocade - XBR-000142
-------------------------------	----------------------

Weblink	https://www.finisar.com/optical-transceivers
---------	---

Product variants & accessories

Art.-No.	Description
FTLF1324P2BTV	EOL - Finisar - SFP 4G Transceiver, Singlemode LC, 4.25 Gb/s, 4km
FTLF1424P2BCD	EOL - Finisar - SFP 4G Transceiver, Singlemode LC, 4.25 Gb/s, 10km
FTLF1424P2BCV	EOL - Finisar - SFP 4G Transceiver, Singlemode LC, 4.25 Gb/s, 30km
FTLF8524P2BNV	EOL - Finisar - SFP 4G Transceiver, Multimode LC, 4.25 Gb/s, 300m/500m