

FO attenuator FC/UPC plug/jack, 06dB, 1310/1550nm



## tde - FO Attenuators

A fiber optic attenuator is a passive device used to reduce the amplitude of a light signal without significantly changing the wave form itself. This is often a requirement in DWDM and EDFA applications where the receiver cannot accept the signal generated from a high-power light source.

tde attenuators feature a proprietary type of metal-ion doped fiber which reduces the light signal as it passes through. This method of attenuation allows for higher performance than fiber splices or fiber offsets, which function by misdirecting rather than absorbing the light signal. tde attenuators are capable of performing in the 1310, C and L Bands. tde attenuators are capable of withstanding over 1W of high power light exposure for extended periods of time, making them well-suited to EDFA and other high-power applications. Low Polarization Dependent Loss (PDL) and a stable and independent wavelength distribution makes them ideal for DWDM.

### Applications

- Erbium Doped Fiber Amplifiers (EDFA)

**tde<sup>®</sup>** trans data elektronik GmbH**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## FO attenuator FC/UPC plug/jack, 06dB, 1310/1550nm

- Dense Wave Division Multiplexers (DWDM)
- Overpowered fiber optic systems

### Features

- Metal ion doped fiber
- High-power light source durability
- Wavelength independence
- Attenuation levels ranging from 1dB to 30dB
- 1310nm, 1550nm, 1250-1625nm and 1350/1550nm dual wave lengths

### Technical Data

Return Loss	≥ 55 dB (UPC)
Attenuation Tolerance	± 0.5%
Operational Wavelengths	1310, 1490, and 1550 nm
Operating Temperature	-40 to +75°C
Maximum Power	500mw

### Product variants & accessories

Art.-No.	Description
L-ATT-FC/UPC-MF-06	FO attenuator FC/UPC plug/jack, 06dB, 1310/1550nm