tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 50/125µ OM2





tML® - tde Modular Link

tML® is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP® and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML® cabling system as a proven tML® standard system and in the highly innovative variants tML® Xtended, tML® 24 System and now tML® 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML® - FO Module 5HP MPO/MTP®is intended for the installation in the tML® Rack Mount Enclosure 3U (for 17 x Modules).

tde® trans data elektronik GmbH

Headquarter address:
Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:
Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

 © tde GmbH, all rights reserved, errors excepted.

tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 50/125µ OM2

Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP®plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number. The modules are ROHS compliant.

Entry	1 x MPO/MTP®Male Adapter (beige) back
Exit	6 x E2000 Compact Adapter (beige/orange) front
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Box	Galvanized steel sheet
Front Panel	Stainless steel

FO Adapters

Type	MPO/MTP®
Application	Multimode OM1/OM2
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Beige
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

FO Adapters

Standardisation	acc. to IEC61754-15, DIN EN 186270
Mating cycles	min. 1000
Pull-out force	min. 70 N
Number of connectors (A)	1
Connector type (A)	E2000™ Compact
Protection class (IP) connector (A)	20
Polishing connector (A)	PC
Attenuation grade IL - connector (A)	≤ 0.2 dB, testing method acc. to IEC 61300-3-4
Connector color (A)	beige
Lever- frame-coding connector (A)	color

© tde GmbH, all rights reserved, errors excepted.

tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 50/125µ OM2

Frame color connector (A)	orange-orange
Sleeve material	Zirkonia Staight Split
Holder for connector / module	support plate
Fiber type	Multimode (MM)
Dimensions	74.7 / 42 x 14.7 / 22.95 x 13 / 16.6 mm
Material	steel: X10CrNi18-8 (1.4310) / plastic: PBT, fiber-glass reinforced (halogen-free)
Manufacturer	R&M

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

Connector

Type	MPO/MTP® Male Push Pull Locking with Elite Pins (beige)
Ferrule	12 Fiber MM Elite® ferrule, PPS
Boot colour	Black
Temperature range	-40°C to +75°C
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM2	MPO/MTP®	850 nm	≤ 0.25 dB	0.45 dB	20 dB
62.5/125µ OM1	MPO/MTP®	850 nm	≤ 0.25 dB	0.45 dB	

FO Connectors

Type	E2000
Ferrule	Ceramic
Ferrule Hole	126 µ
Connector colour	Beige
Lever colour	Black
Boot colour	Black
Manufacturer	RDM

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM2	E2000	850 nm	≤ 0.25 dB	0.45 dB	30 dB
62.5/125µ OM1	E2000	850 nm	≤ 0.25 dB	0.45 dB	

© tde GmbH, all rights reserved, errors excepted.

tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 50/125µ OM2

FO Fiber

Type	Corning 50/125µ OM2 multimode fiber
Manufacturer	Corning

Optical Specifications

Bandwidth	500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 2.5 dB/km At 1300 nm max. ≤ 0.8 dB/km
Numerical Aperture	0.200 ± 0.015

Dimensional Specifications

Core Diameter	50.0 ± 3.0 µm
Cladding Diameter	125.0 ± 2.0 µm
Core-Clad Concentricity	≤ 3.0 µm
Cladding Non-Circularity	< 2.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	245 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

Environmental Specifications

Enviromental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m²).
Length	Fiber lengths available up to 8.8 km/spool.

Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.490 1300 nm: 1.486
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Cromatic Dispersion	Zero Dispersion Wavelength (λ0): 1300 nm ≤λ0 ≤ 1320 nm Zero Dispersion Slope (S0): ≤ 0.101 ps/(nm²*km)

© tde GmbH, all rights reserved, errors excepted.

tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 50/125µ OM2

Product variants & accessories

Art.-No.	Description
TML-T06E2AC/MPP09E	tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 APC Compact 9/125µ OS2
TML-T06E2C/MPP09E	tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 9/125µ OS2
TML-T06E2C/MPP50G	tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 50/125µ OM2
TML-T06E2C/MPP50G3	tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 50/125µ OM3
TML-T06E2C/MPP50G4	tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 50/125µ OM3
TML-T06E2C/MPP62G	tML® - FO Module 5HP MPO/MTP® with Pins/6x E2000 Compact 62,5/125µ OM1

© tde GmbH, all rights reserved, errors excepted.