

tML[®] - FO Trunk Cable 1x MPO Female/1x MPO Female 12E9/125µ OS2 LSHF, Type C, Length: xxx



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®] Xtended, tML[®] 24 System and now tML[®] 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML[®] - FO trunk cable is intended for the connection of two tML[®]- FO Modules.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML® - FO Trunk Cable 1x MPO Female/1x MPO Female 12E9/125µ OS2 LSHF, Type C, Length: xxx

Technical Data

The tML®- FO trunk cable is preterminated with MPO/MTP® connectors on both ends. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The fan-out unit is optimized for tML® - Cable Mounting Bracket for Fan-out Units. The module is marked with sequential serial number and article number.

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

Connector

Type	MPO/MTP® Female Push Pull Locking (Green)
Ferrule	12 Fiber SM Elite® ferrule, PPS
Boot colour	Black
Temperature range	-40°C bis +75°C
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125µ OS2	MPO/MTP®APC	1310 / 1550 nm	≤ 0.10 dB	0.20 dB	75 dB

FO Fan-Out

Fan-out length	50 mm
Ø Fan-out	16 mm
Ø Single unit	3.0 mm
Single unit length	78 ± 5 cm (not stepped)

FO Cables

Mechanical characteristics

Temperature range	Storage -25°C to +70°C
	Pulling in -10°C to +50°C
	Operation -25°C to +70°C
Tensile performance	IEC 60794-1-21 E1
Crush resistance	IEC 60794-1-21 E3
Impact	IEC 60794-1-21 E4
Repeated bending	IEC 60794-1-21 E6
Torsion	IEC 60794-1-21 E7

tML® - FO Trunk Cable 1x MPO Female/1x MPO Female 12E9/125µ OS2 LSHF, Type C, Length: xxx

Bend	IEC 60794-1-21 E11
Water penetration	IEC 60794-1-22 F5

General characteristics

Sheath colour	green, similar to RAL 6016
Zero halogen, non corrosive gases	IEC 60754-1/-2, EN 60754-1/-2, VDE 0482-754-1/-2
Flame propagation	IEC 60332-1-2, EN 60332-1-2, VDE 0482-332-1-2
Flame spread	IEC 60332-3-24, EN 60332-3-24, VDE 0482-332-3-24
Smoke density	IEC 61034-1/-2, EN 61034-1/-2, VDE 0482-1034-1/-2
Reaction to fire (Euroclasses)	EN 13501-6: D _{ca} -s2,d1,a1

Cabletype	Universal U-DQ(ZN)BH for indoor and outdoor use
	non metallic, dry interstices, rodent protection, flame retardant, in accordance with IEC 60332-1-2 and IEC 60332-3-24
Fibertype	E9/125 G.652.D
No. of fibers	12
Loose tube	1
Sheath ø	7.6 mm
Weight	67 kg/km
Bending radius	115 mm
Tensile load	1000 N continuous
	3000 N short term
Crush resistance	3000 N continuous
	5000 N short term
Fire load	275 kWh/km

Length tolerances (prefabricated with plugs)

Tolerances for lengths up to 40m	± 100 cm
Tolerances for lengths up to 100m	± 100 cm
Tolerances for lengths from 100m	± 2%

FO Fiber

Optical properties

Maximum attenuation (cabled)	1310 nm: 0.34 / 1383 nm: 0.34* dB/km (*post hydrogen aging performance)
Maximum Chromatic Dispersion	3.5 ps/(nm x km)
Zero Dispersion Wavelength λ ₀	1304 ≤ λ ₀ ≤ 1324 nm
Maximim Zero Dispersion Slope S ₀	0.092 ps/(nm² x km)
Mode-Filed Diameter	9.2 +/- 0,4 µm
Maximum Cable Cut-off Wavelength λ _{CC}	1260 nm
PDM Link Design Value	≤ 0.04 ps/√km

tML® - FO Trunk Cable 1x MPO Female/1x MPO Female 12E9/125µ OS2 LSHF, Type C, Length: xxx

Max. individual fibre PMD	≤ 0.1 ps/√km
Max. individual cable PMD	≤ 0.2 ps/√km
Refractive Index	1.4676

Mechanical properties

Cladding diameter	125.0 +/- 1.0 µm
Maximum Core/Cladding Concentricity Error	0.5 µm
Maximum Cladding Non-Circularity	0.7 %
Coating diameter	245 +/- 5 µm
Maximum Cladding/Coating Concentricity Error	12 µm
Operating temperature range	-60 to +85°C
Test load	100 kpsi

Product variants & accessories

Art.-No.	Description
TML-MP/MP09B12Exxx	tML® - FO Trunk Cable 1x MPO Female/1x MPO Female 12E9/125µ OS2 LSHF, Type C, Length: xxx
TML-MP/MP09B24Exxx	tML® - FO Trunk Cable 2x MPO Female/2x MPO Female 24E9/125µ OS2 LSHF, Type C, Length: xxx
TML-MP/MP09B48Exxx	tML® - FO Trunk Cable 4x MPO Female/4x MPO Female 48E9/125µ OS2 LSHF, Type C, Length: xxx
TML-MP/MP09B72Exxx	tML® - FO Trunk Cable 6x MPO Female/6x MPO Female 72E9/125µ OS2 LSHF, Type C, Length: xxx
TML-MP/MP09B96Exxx	tML® - FO Trunk Cable 8x MPO Female/8x MPO Female 96E9/125µ OS2 LSHF, Type C, Length: xxx