

tML[®] - FO Module 5HP MPO/MTP[®] with Pins/6x E2000 Compact 62,5/125µ OM1



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®] Xtended, tML[®] 24 System and now tML[®] 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML[®] - FO Module 5HP MPO/MTP[®] is intended for the installation in the tML[®] Rack Mount Enclosure 3U (for 17 x Modules).



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML[®] - FO Module 5HP MPO/MTP[®] with Pins/6x E2000 Compact 62,5/125μ OM1

Technical Data

Entry	1 x MPO/MTP [®] Male
Exit	6 x LWL-Ports E2000 Compact
Strain relief	Integrated
Tests	Interferometer check, OTDR check and visuell Endcheck

Box	Galvanized steel sheet
Front Panel	Stainless steel

FO Adapters

Type	MPO/MTP [®]
Application	Multimode OM1/OM2
Design	without Flange
Connector style	SC Simplex
Key Orientation	Type A, Key up/down
Color	Beige
Material	Plastic
Sleeve	--
Shutter	--
Standards	IEC 61754-7 TIA 604-5
Manufacturer	US Conec

FO Adapters

Standardisation	acc. to IEC61754-15, DIN EN 186270
Mating cycles	min. 1000
Pull-out force	min. 70 N
Number of connectors (A)	1
Connector type (A)	E2000 [™] Compact
Protection class (IP) connector (A)	20
Polishing connector (A)	PC
Attenuation grade IL - connector (A)	≤ 0.2 dB, testing method acc. to IEC 61300-3-4
Connector color (A)	beige
Lever- frame-coding connector (A)	color
Frame color connector (A)	orange-orange
Sleeve material	Zirkonia Straight Split
Holder for connector / module	support plate
Fiber type	Multimode (MM)
Dimensions	74.7 / 42 x 14.7 / 22.95 x 13 / 16.6 mm
Material	steel: X10CrNi18-8 (1.4310) / plastic: PBT, fiber-glass reinforced (halogen-free)
Manufacturer	R&M

tML[®] - FO Module 5HP MPO/MTP[®] with Pins/6x E2000 Compact 62,5/125μ OM1

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5μ. The max. adjacent fiber height difference is 0.2μm and for all fibers 0.3μm.

Connector

Type	MPO/MTP [®] Male Push Pull Locking with Elite Pins (beige)
Ferrule	12 Fiber MM Elite [®] ferrule, PPS
Boot colour	Black
Temperature range	-40°C to +75°C
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM2	MPO/MTP [®]	850 nm	≤ 0.25 dB	0.45 dB	20 dB
62.5/125μ OM1	MPO/MTP [®]	850 nm	≤ 0.25 dB	0.45 dB	20 dB

FO Connectors

Type	E2000
Ferrule	Ceramic
Ferrule Hole	126 μ
Connector colour	Black
Boot colour	Black
Manufacturer	RDM

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM2	E2000	850 nm	≤ 0.25 dB	0.45 dB	30 dB
62.5/125μ OM1	E2000	850 nm	≤ 0.25 dB	0.45 dB	

FO Fiber

Type	Corning 62.5/125μ OM1 multimode fiber
Manufacturer	Corning

Optical Specifications

Bandwidth	160/200 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 3.0 dB/km At 1300 nm max. ≤ 0.7 dB/km

tML[®] - FO Module 5HP MPO/MTP[®] with Pins/6x E2000 Compact 62,5/125μ OM1

Numerical Aperture	0.275 ± 0.015
--------------------	---------------

Dimensional Specifications

Core Diameter	62.5 ± 3.0 μm
Cladding Diameter	125.0 ± 2.0 μm
Core-Clad Concentricity	≤ 3.0 μm
Cladding Non-Circularity	< 2.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	245 ± 5 μm
Coating-Cladding Concentricity	< 12 μm

Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m²).
Length	Fiber lengths available up to 17.6 km/spool.

Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.496 1300 nm: 1.491
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength (λ ₀): 1332 nm ≤ λ ₀ ≤ 1354 nm Zero Dispersion Slope (S ₀): ≤ 0.097 ps/(nm²*km)

Product variants & accessories

Art.-No.	Description
TML-T06E2AC/MPP09E	tML [®] - FO Module 5HP MPO/MTP [®] with Pins/6x E2000 APC Compact 9/125μ OS2
TML-T06E2C/MPP09E	tML [®] - FO Module 5HP MPO/MTP [®] with Pins/6x E2000 Compact 9/125μ OS2
TML-T06E2C/MPP50G	tML [®] - FO Module 5HP MPO/MTP [®] with Pins/6x E2000 Compact 50/125μ OM2
TML-T06E2C/MPP50G3	tML [®] - FO Module 5HP MPO/MTP [®] with Pins/6x E2000 Compact 50/125μ OM3
TML-T06E2C/MPP50G4	tML [®] - FO Module 5HP MPO/MTP [®] with Pins/6x E2000 Compact 50/125μ OM3
TML-T06E2C/MPP62G	tML [®] - FO Module 5HP MPO/MTP [®] with Pins/6x E2000 Compact 62,5/125μ OM1