

tML[®] - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125µ OM3 LSHF, Type C, Length: xxx



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®] Xtended, tML[®] 24 System and now tML[®] 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML[®] - FO trunk cable is intended for the connection of two tML[®]- FO Modules.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML[®] - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125μ OM3 LSHF, Type C, Length: xxx

Technical Data

The tML[®]- FO trunk cable is preterminated with MPO/MTP[®]connectors on both ends. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®]plug has a defined fiber height of 1 - 3.5μ. The max. adjacent fiber height difference is 0.2μm and for all fibers 0.3μm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The fan-out unit is optimized for tML[®] - Cable Mounting Bracket for Fan-out Units. The module is marked with sequential serial number and article number.

FO Connectors

Connector

Type	MPO/MTP [®] Female Push Pull Locking (aqua)
Ferrule	12 Fiber MM Elite [®] ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM3	MPO/MTP [®]	850 nm	≤ 0.14 dB	0.25 dB	35 dB

FO Fan-Out

Ø Single unit length	3.0 mm
Shortest Single unit length	68 ± 5 cm
Highest Single unit length	78 ± 5 cm
Number of stepping	1

FO Cables

Mechanical characteristics

Temperature range	Storage -25 to +70°C, IEC 60794-1-22 F1
	Pulling in -10 to +50°C
	Operation -25 to +60°C
Tensile performance	IEC 60794-1-21 E1
Crush resistance	IEC 60794-1-21 E3
Impact	IEC 60794-1-21 E4
Repeated bending	IEC 60794-1-21 E6
Torsion	IEC 60794-1-21 E7
Bend	IEC 60794-1-21 E11
Water penetration	IEC 60794-1-22 F5

tML[®] - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125μ OM3 LSHF, Type C, Length: xxx

General characteristics

Sheath colour	green, similar to RAL 6016
Zero halogen, no corrosive gases	IEC 60754-1/-2, EN 60754-1/-2, VDE 0482-754-1/-2
Flame propagation	IEC 60332-1-2, EN 60332-1-2, VDE 0482-332-1-2
Flame spread	IEC 60332-3-24, EN 50266-2-4, VDE 0482-266-2-4
Smoke density	IEC 61034-1/-2, EN 61034-1/-2, VDE 0482-1034-1/-2
Reaction to fire (Euroclasses)	EN 13501-6: E _{ca}

Cabletype	Universal U-DQ(ZN)BH for indoor and outdoor use
	non metallic, dry interstices, rodent protection, flame retardant, in accordance with IEC 60332.1 and IEC 60332.3 C
Fibertype	Corning G50/125 OM3
No. of fibers	96
Loose tube	8
Sheath ø	13.5 mm
Weight	186 kg/km
Bending radius	205 mm
Tensile load short term	9.000 N
Tensile load continuous	5.000 N
Crush resistance short term	5.000 N
Crush resistance continuous	3.000 N
Fire load	808 kWh/km
	3200 MJ/km

Length tolerances (prefabricated with plugs)

Tolerances for lengths up to 40m	± 100 cm
Tolerances for lengths up to 100m	± 100 cm
Tolerances for lengths up to 100m	± 2%

FO Fiber

Optical properties

Attenuation typical (cabled)	850 nm: 2.5 / 1300 nm: 0.5 dB/km
Attenuation maximum (cabled)	850 nm: 2.7 / 1300 nm: 0.7 dB/km
OFL bandwidth as per TIA/EIA 455-204 and IEC 60793-1-41	850 nm: 3500 / 1300 nm: 500 MHz x km
High-Performance EMB bandwidth as per TIA/EIA 455-220A and IEC 60793-1-49	850 nm: 4700 / 1300 nm: 4700 MHz x km
Refractive Index	850 nm: 1.480 / 1300 nm: 1.479

tML[®] - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125μ OM3 LSHF, Type C, Length: xxx

Technical properties

Bending radius	No. of windings (turns)	Max. induced attenuation
37.5 mm	100	850 nm: ≤ 0.05 / 1300 nm: ≤ 0.15 dB/km
15 mm	2	850 nm: ≤ 0.1 / 1300 nm: ≤ 0.3 dB/km
7.5 mm	2	850 nm: ≤ 0.2 / 1300 nm: ≤ 0.5 dB/km

Geometrical and mechanical characteristics

Numerical Aperture	0.200 +/- 0.015
Core Ø	50.0 +/- 2.5 μm
Maximum Core Non-Circularity	5 %
Cladding Ø	125.0 +/- 1.0 μm
Maximum Cladding Non-Circularity	1.0 %
Maximum Cladding/Core Concentricity Error	1.5 μm
Maximum Coating Concentricity Error	12 μm
Coating Ø	242 +/- 5 μm
Test load	100 kpsi

Product variants & accessories

Art.-No.	Description
TML-MP/MP50B12G3-xxx	tML [®] - FO Trunk Cable 1x MPO Female/1x MPO Female 12G50/125μ OM3 LSHF, Type C, Length: xxx
TML-MP/MP50B24G3-xxx	tML [®] - FO Trunk Cable 2x MPO Female/2x MPO Female 24G50/125μ OM3 LSHF, Type C, Length: xxx
TML-MP/MP50B48G3-xxx	tML [®] - FO Trunk Cable 4x MPO Female/4x MPO Female 48G50/125μ OM3 LSHF, Type C, Length: xxx
TML-MP/MP50B72G3-xxx	tML [®] - FO Trunk Cable 6x MPO Female/6x MPO Female 72G50/125μ OM3 LSHF, Type C, Length: xxx
TML-MP/MP50B96G3-xxx	tML [®] - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125μ OM3 LSHF, Type C, Length: xxx