

## Draka - UC FUTURE COMPACT AWG26 Cat.7 S/FTP 4P LSHF



### UC FUTURE - Draka Datacom Solution

The solution for Data Centre cabling. A dependable, fast and always available part of Draka Datacom Solution!

For this application Draka has developed the new UCFuture program which contains slim cable designs based on existing work area cable standards, which are perfect for zone cabling in data centres because of these characteristics:

- Up to 100% higher packing density in cable trays
- Fully compliant with established cable standards
- PIMF design to eliminate any Alien-Xtalk interferences
- Full 10GBase-T performance over a channel distance of 70m

Data centre cabling 10Gbit solution. Pair screened 100 Ohms cable especially for Zone Distribution Area and Equipment Distribution Area.



**tde<sup>®</sup>** trans data elektronik GmbH

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## Draka - UC FUTURE COMPACT AWG26 Cat.7 S/FTP 4P LSHF

### Technical Data

#### Application

IEEE 802.3: 10Base-T; 100Base-T; 10GBase-T, ISDN; xDSL

IEEE 802.5 16 MB; ISDN; TPDDI; ATM155Mbit/s

The conductor diameter is smaller compared to the standard installation cables. This leads to an increased attenuation and therefore the operating distance is reduced (60 m instead of 90 m installation cable in standard permanent link).

#### Standards

IEC 61156-6 work area cable

ISO/IEC 11801 2<sup>nd</sup> ed.

EN 50173-5

EN 50288-4-2

#### Flame resistance

PVC IEC 60332-1

LSHF IEC 60332-1, IEC 60754-2, IEC 61034; EN 50399 Class E<sub>ca</sub>

#### Construction

Conductor	Bare copper wire, diamter 0.4 mm (AWG26)
Insulation	Foam-skin PP, diameter 1.0 mm (+/-0.05)
Twisting	2 cores to the pair
Pair screening	Pet-Al foil around each pair
Screen	Tinned copper braid approx. 60% coverage
Sheath	LSHF, orange RAL 2003

#### Mechanical properties

Minimum bending radius	Without load	45.6 mm
	With load	22.8 mm
Temperature range	During operation	-20°C up to +60°C
	During installation	10°C up to +40°C

#### Electrical properties at 20°C

Loop resistance		≤ 280 Ω/km
Resistance unbalance		≤ 2%
Test voltage	core/core	1000 V <sub>DC</sub> 1 min
	core/screen	1000 V <sub>DC</sub> 1 min
Capacitance	800 Hz	Nom. 44 nF/km
Capacitance unbalance		≤ 1600 pF/km
Impedance	100 MHz	100 Ω± 5 Ω
Nominal velocity of propagation		ca. 76%

## Draka - UC FUTURE COMPACT AWG26 Cat.7 S/FTP 4P LSHF

Insulation resistance	500 V	≥ 2000 MΩkm
Coupling attenuation		≥ 85 dB

### Electrical Data (nominal) acc. to Cat.7 (at 20°C)

f	Attenuation	NEXT	PS-NEXT	ELFEXT	PS-ELFEXT	Return loss
MHZ	dB/10m	dB	dB	dB/100m	dB/100m	dB
1.0	0.3	90	87	80	77	23
4.0	0.6	90	87	80	77	24
10.0	1.0	90	87	80	77	25
16.0	1.3	90	87	76	73	25
20.0	1.4	90	87	74	71	25
31.2	1.8	90	87	70	67	25
62.5	2.6	90	87	64	61	23
100.0	3.2	87	84	60	57	21
125.0	3.6	85	82	58	55	20
155.5	4.0	84	81	56	53	19
175.0	4.3	83	80	55	52	19
200.0	4.6	82	79	54	51	18
250.0	5.1	81	78	52	49	18
300.0	5.6	80	77	50	47	17
450.0	6.9	77	74	47	44	17
600.0	7.9	75	72	44	41	17

### Technical Data

Designation	J-09YS(ST)CH
Type	4x2x0.4 PiMF
Outer diameter	5.7 mm
Fire load	282 MJ/km
Fire load	0.08 kWh/m
Weight	33 kg/km
Copper content	21 kg/km
Tensile force	100 N

## Product variants & accessories

Art.-No.	Description
UC-COMPACT26X4P	Draka - UC FUTURE COMPACT AWG26 Cat.7 S/FTP 4P LSHF