


Military D-Series Distribution Mil-Tac Cable 6G50/125μ



tde - Mil-Tac Cable

Applications: Mil-Tac cables are ideal for use in harsh environments where deployment and retrieval for reuse is required.

- Extremely strong, lightweight, rugged, survivable tight-buffered cables designed for military tactical field use and commercial applications
- Compact, round cable design for ease of transportation and deployment
- Designed for use in adverse environments where reduced size and weight are important
- Helically stranded cable core for flexibility, deployment survivability and exceptional mechanical protection for the optical fibers
- Cables have been tested and are in use in military data communications applications worldwide
- Can be used outdoors for temporary deployment directly on the ground in all terrains, including severe environments
- Suitable for industrial, mining and petrochemical environments
- Crush-resistant and resilient with a thick layer of aramid strength members
- Polyurethane jacketed for abrasion, cut and chemical resistance



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

Military D-Series Distribution Mil-Tac Cable 6G50/125µ

Technical Data

General Characteristics

Impact Resistance	200 Impacts
Crush Resistance	440 N/cm
Flex Resistance	2.000 Cycles
Operating Temperature	-55°C to +85°C
Storage Temperature	-70°C to +85°C

Specifications

Fiber Count	6
Diameter	6.0 mm (0.24 in)
Weight	32 kg/km (22 lbs/1.000')
Installation Tensile Load	1.800 N (400 lbs)
Operational Tensile Load	600 N (130 lbs)
Minimum Bend Radius Installation	9.6 cm (3.8 in)
Minimum Bend Radius Operational	4.8 cm (1.9 in)

FO Fiber

Type	Multimode OM2 ISO/IEC 11801
Core diameter	50 µm
Cladding diameter	125 µm
Numeric aperture	0.20
Wavelength	850/1310 nm
Gigabit Ethernet	550/550 m
10-Gigabit Ethernet	82/300 m (1310 CWDM lasers (10GBASE-LX4))
Maximum cabled attenuation	3.5/1.5 dB/km
Minimum Laser EMB bandwidth	500/500 MHz-km
Minimum OFL LED bandwidth	500/500 MHz-km

Product variants & accessories

Art.-No.	Description
MILTAC-D02G50	Military D-Series Distribution Mil-Tac Cable 2G50/125µ
MILTAC-D04G50	Military D-Series Distribution Mil-Tac Cable 4G50/125µ
MILTAC-D06G50	Military D-Series Distribution Mil-Tac Cable 6G50/125µ
MILTAC-D08G50	Military D-Series Distribution Mil-Tac Cable 8G50/125µ
MILTAC-D10G50	Military D-Series Distribution Mil-Tac Cable 10G50/125µ
MILTAC-D12G50	Military D-Series Distribution Mil-Tac Cable 12G50/125µ
MILTAC-D18G50	Military D-Series Distribution Mil-Tac Cable 18G50/125µ
MILTAC-D24G50	Military D-Series Distribution Mil-Tac Cable 24G50/125µ