


## Military B-Series Breakout Mil-Tac Cable 4E9/125μ



### tde - Mil-Tac Cable

Applications: Mil-Tac cables are ideal for use in harsh environments where deployment and retrieval for reuse is required.

- Extremely strong, lightweight, rugged, survivable tight-buffered cables designed for military tactical field use and commercial applications
- Compact, round cable design for ease of transportation and deployment
- Designed for use in adverse environments where reduced size and weight are important
- Helically stranded cable core for flexibility, deployment survivability and exceptional mechanical protection for the optical fibers
- Cables have been tested and are in use in military data communications applications worldwide
- Can be used outdoors for temporary deployment directly on the ground in all terrains, including severe environments
- Suitable for industrial, mining and petrochemical environments
- Crush-resistant and resilient with a thick layer of aramid strength members
- Polyurethane jacketed for abrasion, cut and chemical resistance



**tde<sup>®</sup>** trans data elektronik GmbH

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

## Military B-Series Breakout Mil-Tac Cable 4E9/125μ

### Technical Data

#### General Characteristics

|                       |                |
|-----------------------|----------------|
| Impact Resistance     | 200 Impacts    |
| Crush Resistance      | 440 N/cm       |
| Flex Resistance       | 2.000 Cycles   |
| Operating Temperature | -55°C to +85°C |
| Storage Temperature   | -70°C to +85°C |

#### Specifications

|                                  |          |
|----------------------------------|----------|
| Fiber Count                      | 4        |
| Diameter                         | 7.5 mm   |
| Weight                           | 47 kg/km |
| Installation Tensile Load        | 2.200 N  |
| Operational Tensile Load         | 550 N    |
| Minimum Bend Radius Installation | 7.5 cm   |
| Minimum Bend Radius Operational  | 3.8 cm   |

#### FO Fiber

|                             |  |
|-----------------------------|--|
| Type                        | Singlemode ITU-T G.652.A   |
| Core diameter               | 9 μm (typical mode field diameter at 1310 nm)                          |
| Cladding diameter           | 125 μm   |
| Numeric aperture            | -  |
| Wavelength                  | 1310/1550 nm   |
| Gigabit Ethernet            | 5 km (10 km für 1310 nm 1000BASE-LH, und 5 km für 1310 nm 1000BASE-LR) |
| 10-Gigabit Ethernet         | 10 km (10 km für 1310 nm 10GBASE-LR, und 40 km für 1550 nm 10GBASE-ER) |
| Maximum cabled attenuation  | 0.5/0.5 dB/km  |
| Minimum Laser EMB bandwidth | -  |
| Minimum OFL LED bandwidth   | -  |

### Product variants & accessories

| Art.-No.      | Description  |
|---------------|--|
| MILTAC-B02E09 | Military B-Series Breakout Mil-Tac Cable 2E9/125μ  |
| MILTAC-B04E09 | Military B-Series Breakout Mil-Tac Cable 4E9/125μ  |
| MILTAC-B06E09 | Military B-Series Breakout Mil-Tac Cable 6E9/125μ  |
| MILTAC-B08E09 | Military B-Series Breakout Mil-Tac Cable 8E9/125μ  |
| MILTAC-B10E09 | Military B-Series Breakout Mil-Tac Cable 10E9/125μ |
| MILTAC-B12E09 | Military B-Series Breakout Mil-Tac Cable 12E9/125μ |
| MILTAC-B18E09 | Military B-Series Breakout Mil-Tac Cable 18E9/125μ |
| MILTAC-B24E09 | Military B-Series Breakout Mil-Tac Cable 24E9/125μ |