


Military B-Series Breakout Mil-Tac Cable 6G62,5/125μ



tde - Mil-Tac Cable

Applications: Mil-Tac cables are ideal for use in harsh environments where deployment and retrieval for reuse is required.

- Extremely strong, lightweight, rugged, survivable tight-buffered cables designed for military tactical field use and commercial applications
- Compact, round cable design for ease of transportation and deployment
- Designed for use in adverse environments where reduced size and weight are important
- Helically stranded cable core for flexibility, deployment survivability and exceptional mechanical protection for the optical fibers
- Cables have been tested and are in use in military data communications applications worldwide
- Can be used outdoors for temporary deployment directly on the ground in all terrains, including severe environments
- Suitable for industrial, mining and petrochemical environments
- Crush-resistant and resilient with a thick layer of aramid strength members
- Polyurethane jacketed for abrasion, cut and chemical resistance



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

Military B-Series Breakout Mil-Tac Cable 6G62,5/125μ

Technical Data

General Characteristics

Impact Resistance	200 Impacts
Crush Resistance	440 N/cm
Flex Resistance	2.000 Cycles
Operating Temperature	-55°C to +85°C
Storage Temperature	-70°C to +85°C

Specifications

Fiber Count	6
Diameter	8.5 mm (0.33 in)
Weight	56 kg/km (37 lbs/1.000')
Installation Tensile Load	2.400 N (540 lbs)
Operational Tensile Load	600 N (130 lbs)
Minimum Bend Radius Installation	13.6 cm (5.4 in)
Minimum Bend Radius Operational	6.8 cm (2.7 in)

FO Fiber

Type	Multimode OM1 ISO/IEC 11801
Core diameter	62.5 μm
Cladding diameter	125 μm
Numeric aperture	0.275
Wavelength	850/1310 nm
Gigabit Ethernet	275/550 m
10-Gigabit Ethernet	33/300 m (1310 CWDM lasers (10GBASE-LX4))
Maximum cabled attenuation	3.5/1.5 dB/km
Minimum Laser EMB bandwidth	200/500 MHz-km
Minimum OFL LED bandwidth	200/500 MHz-km

Product variants & accessories

Art.-No.	Description
MILTAC-B02G62	Military B-Series Breakout Mil-Tac Cable 2G62,5/125μ
MILTAC-B04G62	Military B-Series Breakout Mil-Tac Cable 4G62,5/125μ
MILTAC-B06G62	Military B-Series Breakout Mil-Tac Cable 6G62,5/125μ
MILTAC-B08G62	Military B-Series Breakout Mil-Tac Cable 8G62,5/125μ
MILTAC-B10G62	Military B-Series Breakout Mil-Tac Cable 10G62,5/125μ
MILTAC-B12G62	Military B-Series Breakout Mil-Tac Cable 12G62,5/125μ
MILTAC-B18G62	Military B-Series Breakout Mil-Tac Cable 18G62,5/125μ
MILTAC-B24G62	Military B-Series Breakout Mil-Tac Cable 24G62,5/125μ