


## Military D-Series Distribution Mil-Tac Cable 18E9/125μ



### tde - Mil-Tac Cable

Applications: Mil-Tac cables are ideal for use in harsh environments where deployment and retrieval for reuse is required.

- Extremely strong, lightweight, rugged, survivable tight-buffered cables designed for military tactical field use and commercial applications
- Compact, round cable design for ease of transportation and deployment
- Designed for use in adverse environments where reduced size and weight are important
- Helically stranded cable core for flexibility, deployment survivability and exceptional mechanical protection for the optical fibers
- Cables have been tested and are in use in military data communications applications worldwide
- Can be used outdoors for temporary deployment directly on the ground in all terrains, including severe environments
- Suitable for industrial, mining and petrochemical environments
- Crush-resistant and resilient with a thick layer of aramid strength members
- Polyurethane jacketed for abrasion, cut and chemical resistance



**tde<sup>®</sup>** trans data elektronik GmbH

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## Military D-Series Distribution Mil-Tac Cable 18E9/125μ

### Technical Data

#### General Characteristics

|                       |                |
|-----------------------|----------------|
| Impact Resistance     | 200 Impacts    |
| Crush Resistance      | 440 N/cm       |
| Flex Resistance       | 2.000 Cycles   |
| Operating Temperature | -55°C to +85°C |
| Storage Temperature   | -70°C to +85°C |

#### Specifications

|                                  |                          |
|----------------------------------|--------------------------|
| Fiber Count                      | 18                       |
| Diameter                         | 7.5 mm (0.30 in)         |
| Weight                           | 49 kg/km (33 lbs/1.000') |
| Installation Tensile Load        | 2.400 N (540 lbs)        |
| Operational Tensile Load         | 800 N (180 lbs)          |
| Minimum Bend Radius Installation | 12.0 cm (4.7 in)         |
| Minimum Bend Radius Operational  | 6.0 cm (2.4 in)          |

#### F0 Fiber

|                             |                                                                        |
|-----------------------------|------------------------------------------------------------------------|
| Type                        | Singlemode ITU-T G.652.A                                               |
| Core diameter               | 9 μm (typical mode field diameter at 1310 nm)                          |
| Cladding diameter           | 125 μm                                                                 |
| Numeric aperture            | -                                                                      |
| Wavelength                  | 1310/1550 nm                                                           |
| Gigabit Ethernet            | 5 km (10 km für 1310 nm 1000BASE-LH, und 5 km für 1310 nm 1000BASE-LR) |
| 10-Gigabit Ethernet         | 10 km (10 km für 1310 nm 10GBASE-LR, und 40 km für 1550 nm 10GBASE-ER) |
| Maximum cabled attenuation  | 0.5/0.5 dB/km                                                          |
| Minimum Laser EMB bandwidth | -                                                                      |
| Minimum OFL LED bandwidth   | -                                                                      |

### Product variants & accessories

| Art.-No.      | Description                                            |
|---------------|--------------------------------------------------------|
| MILTAC-D02E09 | Military D-Series Distribution Mil-Tac Cable 2E9/125μ  |
| MILTAC-D04E09 | Military D-Series Distribution Mil-Tac Cable 4E9/125μ  |
| MILTAC-D06E09 | Military D-Series Distribution Mil-Tac Cable 6E9/125μ  |
| MILTAC-D08E09 | Military D-Series Distribution Mil-Tac Cable 8E9/125μ  |
| MILTAC-D10E09 | Military D-Series Distribution Mil-Tac Cable 10E9/125μ |
| MILTAC-D12E09 | Military D-Series Distribution Mil-Tac Cable 12E9/125μ |
| MILTAC-D18E09 | Military D-Series Distribution Mil-Tac Cable 18E9/125μ |
| MILTAC-D24E09 | Military D-Series Distribution Mil-Tac Cable 24E9/125μ |