


Military B-Series Breakout Mil-Tac Cable 8G50/125μ



tde - Mil-Tac Cable

Applications: Mil-Tac cables are ideal for use in harsh environments where deployment and retrieval for reuse is required.

- Extremely strong, lightweight, rugged, survivable tight-buffered cables designed for military tactical field use and commercial applications
- Compact, round cable design for ease of transportation and deployment
- Designed for use in adverse environments where reduced size and weight are important
- Helically stranded cable core for flexibility, deployment survivability and exceptional mechanical protection for the optical fibers
- Cables have been tested and are in use in military data communications applications worldwide
- Can be used outdoors for temporary deployment directly on the ground in all terrains, including severe environments
- Suitable for industrial, mining and petrochemical environments
- Crush-resistant and resilient with a thick layer of aramid strength members
- Polyurethane jacketed for abrasion, cut and chemical resistance



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

Military B-Series Breakout Mil-Tac Cable 8G50/125μ

Technical Data

General Characteristics

| | |
|-----------------------|----------------|
| Impact Resistance | 200 Impacts |
| Crush Resistance | 440 N/cm |
| Flex Resistance | 2.000 Cycles |
| Operating Temperature | -55°C to +85°C |
| Storage Temperature | -70°C to +85°C |

Specifications

| | |
|----------------------------------|--------------------------|
| Fiber Count | 8 |
| Diameter | 10.0 mm (0.39 in) |
| Weight | 75 kg/km (51 lbs/1.000') |
| Installation Tensile Load | 3.200 N (720 lbs) |
| Operational Tensile Load | 800 N (180 lbs) |
| Minimum Bend Radius Installation | 16.0 cm (6.3 in) |
| Minimum Bend Radius Operational | 8.0 cm (3.1 in) |

FO Fiber

| | |
|-----------------------------|---|
| Type | Multimode OM2 ISO/IEC 11801 |
| Core diameter | 50 μm |
| Cladding diameter | 125 μm |
| Numeric aperture | 0.20 |
| Wavelength | 850/1310 nm |
| Gigabit Ethernet | 550/550 m |
| 10-Gigabit Ethernet | 82/300 m (1310 CWDM lasers (10GBASE-LX4)) |
| Maximum cabled attenuation | 3.5/1.5 dB/km |
| Minimum Laser EMB bandwidth | 500/500 MHz-km |
| Minimum OFL LED bandwidth | 500/500 MHz-km |

Product variants & accessories

| Art.-No. | Description |
|---------------|---|
| MILTAC-B02G50 | Military B-Series Breakout Mil-Tac Cable 2G50/125μ |
| MILTAC-B04G50 | Military B-Series Breakout Mil-Tac Cable 4G50/125μ |
| MILTAC-B06G50 | Military B-Series Breakout Mil-Tac Cable 6G50/125μ |
| MILTAC-B08G50 | Military B-Series Breakout Mil-Tac Cable 8G50/125μ |
| MILTAC-B10G50 | Military B-Series Breakout Mil-Tac Cable 10G50/125μ |
| MILTAC-B12G50 | Military B-Series Breakout Mil-Tac Cable 12G50/125μ |
| MILTAC-B18G50 | Military B-Series Breakout Mil-Tac Cable 18G50/125μ |
| MILTAC-B24G50 | Military B-Series Breakout Mil-Tac Cable 24G50/125μ |