

FO Breakout cable 24E9/125μ G.652.D LSOH 2,0mm



tde - Standard FO Cables

The standard fiber optic cable types of tde specifically for the assembling of patch and adapter cables, pigtails and trunk cables has been developed. Also the use in FTTH applications inside buildings is possible. The breakout cables have up to 24 individual elements with a 2mm diameter. The overall cable diameter is very slim.

These cables are characterized by very good termination properties. The cable jacket and the secondary coating are easy removable.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

FO Breakout cable 24E9/125 μ G.652.D LSOH 2,0mm

Technical Data

Cable Data

Type	IVHH24E9/125
Fiber Amount	24
Construction	4 x 6
Outer Diameter	17.4 mm
Tolerance	± 0.5 mm

Subcable Diameter	2.0 (± 0.1 mm)
Strength Members	Aramid yarns
Outer Jacket	LSOH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket Colour	Yellow
Standard printing	"t d e – IVHH24E09-2.0" and sequential meter marking + Lot number

Mechanical/Thermal Characteristics

Fiber Amount	24
Weight	235 kg/km
Tensile load	3200 N
Bending radius	20 x outer diameter
Operating temperature	-5°C to + 60°C
Fire resistance	Pass EN 50266, IEC 60332-3
Halogen content	Free EN 50267, IEC 60754
Smoke density	Low EN 50268, IEC 61034-1/2

Special features

Characteristics	Fiber and aramid yarn free movable in the compound
Identification	Numbers, min. every 25cm on subcables

FO Fiber

Type	Corning SMF-28e+ [®] 09/125 μ OS2 G.652.D singlemode fiber
Maximum Attenuation	At 1310 nm max. 0.33 - 0.35 dB/km At 1383 $\pm$ 3 nm max. 0.31 - 0.35 dB/km At 1490 nm max. 0.21 - 0.24 dB/km At 1550 nm max. 0.19 - 0.20 dB/km At 1625 nm max. 0.20 - 0.23 dB/km
Attenuation vs. Wavelength	Range: 1285 - 1330 nm; Ref. λ : 1310 nm; Max. Difference: 0.03 dB/km Range: 1525 - 1575 nm; Ref. λ : 1550 nm; Max. Difference: 0.02 dB/km
Macrobend Loss	Mandrel Diameter:32mm; Number of Turns: 1; Wavelength: 1550nm; Induced Attenuation: ≤ 0.03 dB Mandrel Diameter:50mm; Number of Turns: 100; Wavelength: 1310nm; Induced Attenuation: ≤ 0.03 dB Mandrel Diameter:50mm; Number of Turns: 100; Wavelength: 1550nm; Induced Attenuation: ≤ 0.03 dB Mandrel Diameter:60mm; Number of Turns: 100; Wavelength: 1625nm; Induced Attenuation: ≤ 0.03 dB

FO Breakout cable 24E9/125µ G.652.D LSOH 2,0mm

Point Discontinuity	Wavelength: 1310 nm; Point Discontinuity: ≤ 0.05 dB Wavelength: 1550 nm; Point Discontinuity: ≤ 0.05 dB
Cable Cutoff Wavelength (λ_{ccf})	$\lambda_{ccf} \leq 1260$ nm
Mode-Field Diameter	At 1310 nm = 9.2 ± 0.4 µm At 1550 nm = 10.4 ± 0.5 µm
Dispersion	At 1550 nm = ≤ 18.0 [ps/(nm*km)] At 1625 nm = ≤ 22.0 [ps/(nm*km)]
	Zero Dispersion Wavelength (λ_0): 1310 nm $\leq \lambda_0 \leq 1324$ nm Zero Dispersion Slope (S_0): ≤ 0.092 ps/(nm ² *km)
Polarization Mode Dispersion (PMD)	PMD Link Design Value = ≤ 0.06 ps/√km Maximum Individual Fiber = ≤ 0.1 ps/√km
Norm	ITU-T Recommendation G.652 (Tables A, B, C, and D) IEC Specifications 60793-2-50 Type B1.3 TIA/EIA 492-CAAB Telcordia Generic Requirements GR-20-CORE ISO 11801 OS2

Dimensional Specifications

Fiber Curl	≥ 4.0 m radius of curvature
Cladding Diameter	125.0 ± 0.7 µm
Core-Clad Concentricity	≤ 0.5 µm
Cladding Non-Circularity	$\leq 0.7\%$
Coating Diameter	242 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm & 1625 nm
Temperature Dependence	-60°C to +85°C	≤ 0.05
Temperature Humidity Cycling	-10°C to +85°C up to 98% RH	≤ 0.05
Water Immersion	23°C $\pm$ 2°C	≤ 0.05
Heat Aging	85°C $\pm$ 2°C	≤ 0.05
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GPa).
Length	Fiber lengths available up to 63.0 km/spool.

Performance Characterizations

Core Diameter	8.2 µm
Numerical Aperture	0.14
Zero Dispersion Wavelength (λ_0)	1317 nm
Zero Dispersion Slope (S_0)	0.088 ps/(nm ² *km)

FO Breakout cable 24E9/125μ G.652.D LSOH 2,0mm

Effective Group Index of Refraction	1310 nm: 1.4676 1550 nm: 1.4682
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (3N) Wet: 14 days room temperature: 0.6 lbs (3N)
Rayleigh Backscatter Coefficient (for 1 ns Pulse Width)	1310 nm: -77 dB 1550 nm: -82 dB

Product variants & accessories

Art.-No.	Description
L-IVHH04E09X-2.0	FO Breakout cable 4E9/125μ G.657.A1 Ultra LSOH 2,0mm
L-IVHH08E09-2.0	FO Breakout cable 8E9/125μ G.652.D LSOH 2,0mm
L-IVHH12E09-2.0	FO Breakout cable 12E9/125μ G.652.D LSOH 2,0mm
L-IVHH24E09-2.0	FO Breakout cable 24E9/125μ G.652.D LSOH 2,0mm