


FO-Patch cord E2000 APC/LC PC RDM/tde 9/125µ OS2 Duplex LSOH Length: xxxxx



## tde - Fiber Optic Assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards, and the company has one of the most up-to-date fiber optic assembly houses in Europe. Fiber optic patch cables and trunk cables are manufactured in many different configurations using highly automated processes on two independent mass production lines. The range of products on offer encompasses the entire spectrum of connector types available on the market. Production capacity is around 100,000 fiber optic connectors per month, and this can be ramped up easily whenever required. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment such as laser cleavers and glue-dispensing robots.

Each cable application is subjected to a full test procedure comprising interferometer measurements, insertion loss and return loss measurements and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.

**tde<sup>®</sup>** trans data elektronik GmbH**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

FO-Patch cord E2000 APC/LC PC RDM/tde 9/125μ OS2 Duplex LSOH Length: xxxxx

## Technical Data

### FO Connectors

Type	E2000 APC
Ferrule	Ceramic
Ferrule Hole	125.5 μ
Ferrule Concentricity	≤ 0.6 μ
Connector colour	Green
Lever Colour	Green
Boot colour	Green
Manufacturer	RDM

### Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125μ	E2000 APC	1550 nm	≤ 0.20 dB	0.45 dB	70 dB

### FO Connectors

Connector Type	LC PC Duplex
Housing	Plastic, Blue
Ferrule	Zirkonia Staight Split, Spring-loaded Axially
Ferrule Hole	126 μ
Ferrule Concentricity	≤ 0.6 μ
Mating Cycles	500
Operating Temperature	-40°C up to +75°C
Strain Relief to	100 N
Manufacturer	tde
Simplex / Duplex Clip	with Duplex Clip

### Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125μ	LC	1550 nm	≤ 0.20 dB	0.45 dB	45 dB

### FO Cables

Flame resistance	IEC 60332-3
	IEC 60754
	IEC 61034-1
	IEC 61034-2

FO-Patch cord E2000 APC/LC PC RDM/tde 9/125μ OS2 Duplex LSOH Length: xxxxx

## Cable construction

Type	IVH02E9
Tight buffer	2x 900μ coated fibers (free movable in the compound)
Fiber type	SM 9/125μ, Corning G.657.A1 Ultra Fiber
Strength members	Aramid yarn (free movable in the compound)
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Yellow, RAL 1021
Identification	"t d e – IVH02E09 - 2.4mm Ultra LSZH" and sequential meter marking + Lot number

## Physical properties

Outer diameter cable	2x 2.4 ± 0.1 mm
Temperature range	-20°C to +70°C

## FO Fiber

Type	Corning Ultra SMF-28 <sup>®</sup> 09/125μ OS2 singlemode fiber
Maximum Attenuation	At 1310 nm max. 0.32 dB/km At 1383 nm max. 0.32 dB/km At 1490 nm max. 0.21 dB/km At 1550 nm max. 0.18 dB/km At 1625 nm max. 0.20 dB/km
Attenuation vs. Wavelength	Range: 1285 - 1330 nm; Ref. λ: 1310 nm; Max. Difference: 0.03 dB/km Range: 1525 - 1575 nm; Ref. λ: 1550 nm; Max. Difference: 0.02 dB/km
Macrobend Loss	Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1550nm; Induced Attenuation: ≤ 0.50 dB Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1625nm; Induced Attenuation: ≤ 1.5 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1550nm; Induced Attenuation: ≤ 0.05 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1625nm; Induced Attenuation: ≤ 0.30 dB Mandrel Radius: 25mm; Number of Turns: 100; Wavelength: 1310nm, 1550nm, 1625nm; Induced Attenuation: ≤ 0.01 dB
Point Discontinuity	Wavelength: 1310 nm; Point Discontinuity: ≤ 0.05 dB Wavelength: 1550 nm; Point Discontinuity: ≤ 0.05 dB
Cable Cutoff Wavelength (λ <sub>ccf</sub> )	λ <sub>ccf</sub> ≤ 1260 nm
Mode-Field Diameter	At 1310 nm = 9.2 ± 0.4 μm At 1550 nm = 10.4 ± 0.5 μm
Dispersion	At 1550 nm = ≤ 18.0 [ps/(nm*km)] At 1625 nm = ≤ 22.0 [ps/(nm*km)]
	Zero Dispersion Wavelength (λ <sub>0</sub> ): 1304 nm ≤ λ <sub>0</sub> ≤ 1324 nm Zero Dispersion Slope (S <sub>0</sub> ): ≤ 0.092 ps/(nm <sup>2</sup> *km)
Polarization Mode Dispersion (PMD)	PMD Link Design Value = ≤ 0.04 ps/√km Maximum Individual Fiber = ≤ 0.1 ps/√km

## Dimensional Specifications

Fiber Curl	≥ 4.0 m radius of curvature
Cladding Diameter	125.0 ± 0.7 μm
Core-Clad Concentricity	≤ 0.5 μm
Cladding Non-Circularity	≤ 0.7%
Coating Diameter	242 ± 5 μm

FO-Patch cord E2000 APC/LC PC RDM/tde 9/125μ OS2 Duplex LSOH Length: xxxxx

Coating-Cladding Concentricity	< 12 μm
--------------------------------	---------

## Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm & 1625 nm
Temperature Dependence	-60°C to +85°C	≤ 0.05
Temperature Humidity Cycling	-10°C to +85°C up to 98% RH	≤ 0.05
Water Immersion	23°C ± 2°C	≤ 0.05
Heat Aging	85°C ± 2°C	≤ 0.05
Operating Temperature Range	-60°C to +85°C	

## Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.69 GPa).
Length	Fiber lengths available up to 63.0 km/spool.

## Performance Characterizations

Core Diameter	8.2 μm
Numerical Aperture	0.14
Effective Group Index of Refraction	1310 nm: 1.4676 1550 nm: 1.4682
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (3N) Wet: 14 days room temperature: 0.6 lbs (3N)
Rayleigh Backscatter Coefficient (for 1 ns Pulse Width)	1310 nm: -77 dB 1550 nm: -82 dB

## Product variants & accessories

Art.-No.	Description
L-E2A/LC09Dxxxxx	FO-Patch cord E2000 APC/LC PC RDM/tde 9/125μ OS2 Duplex LSOH Length: xxxxx
L-E2A/LCA09Dxxxxx	FO-Patch cord E2000 APC/LC APC RDM/tde 9/125μ OS2 Duplex LSOH Length: xxxxx
L-E2/LC50D3-xxxxx	FO-Patch cord E2000/LC RDM/tde 50/125μ OM3 Duplex LSOH Length: xxxxx
L-E2/LC50D4-xxxxx	FO-Patch cord E2000/LC RDM/tde 50/125μ OM4 Duplex LSOH Length: xxxxx
L-E2/LC50Dxxxxx	FO-Patch cord E2000/LC RDM/tde 50/125μ OM2 Duplex LSOH Length: xxxxx