


FO-Patch cord LC/SC tde 50/125µ OM2 Duplex MiniZip LSOH Length: xxxxx



## tde - Fiber Optic Assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards, and the company has one of the most up-to-date fiber optic assembly houses in Europe. Fiber optic patch cables and trunk cables are manufactured in many different configurations using highly automated processes on two independent mass production lines. The range of products on offer encompasses the entire spectrum of connector types available on the market. Production capacity is around 100,000 fiber optic connectors per month, and this can be ramped up easily whenever required. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment such as laser cleavers and glue-dispensing robots.

Each cable application is subjected to a full test procedure comprising interferometer measurements, insertion loss and return loss measurements and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.

**tde<sup>®</sup>** trans data elektronik GmbH**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

FO-Patch cord LC/SC tde 50/125μ OM2 Duplex MiniZip LSOH Length: xxxxx

## Technical Data

### FO Connectors

Connector Type	LC Unibody Duplex
Housing	Plastic, Beige
Ferrule	Zirkonia Straight Split, Spring-loaded Axially
Ferrule Hole	126 μ
Mating Cycles	1.000
Operating Temperature	-40°C up to +75°C
Strain Relief to	100 N
Manufacturer	tde
Simplex / Duplex Clip	with Duplex Clip

### Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM2	LC	850 nm	≤ 0.25 dB	0.45 dB	30 dB
62.5/125μ OM1	LC	850 nm	≤ 0.25 dB	0.45 dB	

### FO Connectors

Connector Type	SC Duplex
Housing	Plastic, Beige
Ferrule	Zirconia Straight Split, Spring-loaded Axially
Ferrule Hole	126 μ
Mating Cycles	1.000
Operating Temperature	-40°C up to +75°C
Strain Relief to	150 N
Manufacturer	tde
Simplex / Duplex Clip	with Duplex Clip

### Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM2	SC	850 nm	≤ 0.25 dB	0.45 dB	30 dB
62.5/125μ OM1	SC	850 nm	≤ 0.25 dB	0.45 dB	

## FO Cables

### Cable Data

Type	IVH02G50 OM2
Fiber Amount	2
Fiber Type	MM-OM2, 50/125μ, Corning

FO-Patch cord LC/SC tde 50/125μ OM2 Duplex MiniZip LSOH Length: xxxxx

Secondary Coating	600μ, easy strippable
Strength Members	Aramid yarns
Outer Jacket	LSOH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket Colour	Orange
Outer Diameter	2x 1.8 (± 0.1mm)
Standard printing	"t d e – IVH02G50-1.8 LSZH" and sequential meter marking + Lot number
Applications	Patchcords/ Pigtails

## Mechanical/ Thermal Characteristics

Weight	12 kg/km
Operational tensile load	210 N
Bending radius	15 x outer diameter
Operating temperature	-5°C to + 60°C
Fire resistance	Pass (EN 50266, IEC 60332-3)
Halogen content	Free (EN 50267, IEC 60754)
Smoke density	Low (EN 50268, IEC 61034-1/2)

## Special features

Characteristics	Fiber and aramid yarn free movable in the compound
-----------------	--

## FO Fiber

Type	Corning 50/125μ OM2 multimode fiber
Manufacturer	Corning

## Optical Specifications

Bandwidth	500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 2.5 dB/km At 1300 nm max. ≤ 0.8 dB/km
Numerical Aperture	0.200 ± 0.015

## Dimensional Specifications

Core Diameter	50.0 ± 3.0 μm
Cladding Diameter	125.0 ± 2.0 μm
Core-Clad Concentricity	≤ 3.0 μm
Cladding Non-Circularity	< 2.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	245 ± 5 μm
Coating-Cladding Concentricity	< 12 μm

FO-Patch cord LC/SC tde 50/125µ OM2 Duplex MiniZip LSOH Length: xxxxx

## Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

## Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m²).
Length	Fiber lengths available up to 8.8 km/spool.

## Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.490 1300 nm: 1.486
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength ( $\lambda_0$ ): 1300 nm $\leq \lambda_0 \leq$ 1320 nm Zero Dispersion Slope (S0): $\leq 0.101$ ps/(nm²*km)

## Product variants & accessories

Art.-No.	Description
L-LC/SC09D-Mxxxxx	FO Patch cord LC/SC tde 9/125µ OS2 Duplex MiniZip LSOH Length: xxxxx
L-LC/SC50D3Mxxxxx	FO Patch cord LC/SC tde 50/125µ OM3 Duplex MiniZip LSOH Length: xxxxx
L-LC/SC50D4Mxxxxx	FO Patch cord LC/SC tde 50/125µ OM4 Duplex MiniZip LSOH Length: xxxxx
L-LC/SC50D-Mxxxxx	FO-Patch cord LC/SC tde 50/125µ OM2 Duplex MiniZip LSOH Length: xxxxx
L-LC/SC62D-Mxxxxx	FO-Patch cord LC/SC tde 62,5/125µ OM1 Duplex MiniZip LSOH Length: xxxxx