
FO Patch cord LC/MTRJ w/o Pins tde 62,5/125µ OM1 Duplex MiniZip LSOH Length: xxxxx



tde - Fiber Optic Assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards, and the company has one of the most up-to-date fiber optic assembly houses in Europe. Fiber optic patch cables and trunk cables are manufactured in many different configurations using highly automated processes on two independent mass production lines. The range of products on offer encompasses the entire spectrum of connector types available on the market. Production capacity is around 100,000 fiber optic connectors per month, and this can be ramped up easily whenever required. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment such as laser cleavers and glue-dispensing robots.
Each cable application is subjected to a full test procedure comprising interferometer measurements, insertion loss and return loss measurements and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.

tde® trans data elektronik GmbH

Headquarter address:
Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:
Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

 © tde GmbH, all rights reserved, errors excepted.

FO Patch cord LC/MTRJ w/o Pins tde 62,5/125µ OM1 Duplex MiniZip LSOH Length: xxxxx

Technical Data

FO Connectors

Connector Type	LC Unibody Duplex
Housing	Plastic, Beige
Ferrule	Zirkonia Staight Split, Spring-loaded Axially
Ferrule Hole	126 µ
Mating Cycles	1.000
Operating Temperature	-40°C up to +75°C
Strain Relief to	100 N
Manufacturer	tde
Simplex / Duplex Clip	with Duplex Clip

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM2	LC	850 nm	≤ 0.25 dB	0.45 dB	30 dB
62.5/125µ OM1	LC	850 nm	≤ 0.25 dB	0.45 dB	

FO Connectors

Type	MTRJ w/o pins
Ferrule	MT-Ferrule
Ferrule Hole	126 µ
Connector colour	Black
Boot colour	Beige
Manufacturer	tde

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM2	MTRJ	850 nm	≤ 0.35 dB	0.45 dB	20 dB
62.5/125µ OM1	MTRJ	850 nm	≤ 0.35 dB	0.45 dB	

FO Cables

Flame resistance	IEC 60332-3
	IEC 60754
	IEC 61034-1
	IEC 61034-2

© tde GmbH, all rights reserved, errors excepted.

FO Patch cord LC/MTRJ w/o Pins tde 62,5/125µ OM1 Duplex MiniZip LSOH Length: xxxxx

Cable construction

Tight buffer	2x 600µ coated fibers (free movable in the compound)
Fiber type	MM-OM1, 62.5/125µ, Corning
Strength members	Aramid yarn (free movable in the compound)
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Orange, RAL 2003
Identification	"t d e – IVH02G62-1.8 LSZH" and sequential meter marking + Lot number

Physical properties

Outer diameter cable	2x 1.8 ± 0.1 mm
Temperature range	-20°C to +70°C

FO Fiber

Type	Corning 62.5/125µ OM1 multimode fiber
Manufacturer	Corning

Optical Specifications

Bandwidth	160/200 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 3.0 dB/km At 1300 nm max. ≤ 0.7 dB/km
Numerical Aperture	0.275 ± 0.015

Dimensional Specifications

Core Diameter	62.5 ± 3.0 µm
Cladding Diameter	125.0 ± 2.0 µm
Core-Clad Concentricity	≤ 3.0 µm
Cladding Non-Circularity	< 2.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	245 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

Environmental Specifications

Enviromental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

© tde GmbH, all rights reserved, errors excepted.

FO Patch cord LC/MTRJ w/o Pins tde 62,5/125µ OM1 Duplex MiniZip LSOH Length: xxxxx

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m²).
Length	Fiber lengths available up to 17.6 km/spool.

Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.496 1300 nm: 1.491
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Cromatic Dispersion	Zero Dispersion Wavelength (λ0): 1332 nm ≤λ0 ≤ 1354 nm Zero Dispersion Slope (S0): ≤ 0.097 ps/(nm²*km)

Product variants & accessories

Art.-No.	Description
L-LC/MT09D-Mxxxxx	FO Patch cord LC/MTRJ w/o. Pins tde 9/125µ OS2 Duplex MiniZip LSOH Length: xxxxx
L-LC/MT50D3Mxxxxx	FO Patch cord LC/MTRJ w/o. Pins tde 50/125µ OM3 Duplex MiniZip LSOH Length: xxxxx
L-LC/MT50D-Mxxxxx	FO Patch cord LC/MTRJ w/o. Pins tde 50/125µ OM2 Duplex MiniZip LSOH Length: xxxxx
L-LC/MT62D-Mxxxxx	FO Patch cord LC/MTRJ w/o Pins tde 62,5/125µ OM1 Duplex MiniZip LSOH Length: xxxxx

© tde GmbH, all rights reserved, errors excepted.