

1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible



GBIC-, SFP-, XFP-, XENPAK-Transceiver

The tde Small Form Pluggable Optical Transceiver are easy installed for enterprise and telecom applications. The tde SFP modular line provides a fully compatible, highly reliable and volume accessible supply of quality transceiver products with excellent performance for design-in manufacturing and end-user enterprise applications.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible

Technical Data

Features

- Operating data rate up to 1.25Gbps
- 1310nm LD Transmitter
- Distance Up to 10Km
- 3.3/5V Power supply and TTL Logic Interface
- Duplex SC Connector Interface
- Hot Pluggable
- Operating Case Temperature Industrial: -40°C~+85°C
- Compliant with GBIC Specification Rev. 5.5

Applications

- WDM GBE Links
- SONET/SDH Equipment Interconnect
- Fiber Channel Links

Regulatory Compliance

Feature	Standard	Performance
Electrostatic Discharge (ESD) to the Electrical Pins	MIL-STD-883E Method 3015.7	Class 1(>500 V) Isolation with the case
Electromagnetic Interference (EMI)	FCC Part 15 Class B	Compatible with standards
Laser Eye Safety	FDA 21CFR 1040.10 and 1040.11 EN60950, EN (IEC) 60825-1,2	Compatible with Class I laser product. Compatible with T üV standards
Component Recognition	UL and CUL	UL file E317337
Green Products	RoHS	RoHS6

Absolute Maximum Ratings

Parameter	Symbol	Min.	Max.	Unit
Storage Temperature	Ts	-40	+85	°C
Supply Voltage	Vcc	0	6	V

Recommended Operating Conditions

Parameter	Symbol	Min.	Typ.	Max.	Unit
Operating Case Temperature	TA	-40		+85	°C
Power Supply Voltage	Vcc	4.75 3.15	5 3.3	5.25 4.45	V
Power Supply Current	Icc			300	mA
Surge Current	ISurge			+30	mA
Baud Rate			1.25		GBaud

1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible

Performance Specifications - Electrical

Parameter	Symbol	Min.	Typ.	Max.	Unit	Notes
Transmitter						
LVPECL Inputs (Differential)	V _{in}	400		2500	mVp	AC coupled inputs
Input Impedance (Differential)	Z _{in}	85	100	115	ohms	R _{in} > 100 kohms @ DC
Tx_DISABLE Input Voltage - High		2		V _{cc} +0.3	V	
Tx_DISABLE Input Voltage - Low		0		0.8	V	
Tx_FAULT Output Voltage - High		V _{cc} -0.5		V _{cc} +0.3	V	I _o = 400µA; Host V _{cc}
Tx_FAULT Output Voltage - Low		0		0.5	V	I _o = -4.0mA
Receiver						
LVPECL Outputs (Differential)	V _{out}	400	800	1200	mVpp	AC coupled outputs
Output Impedance (Differential)	Z _{out}	85	100	115	ohms	
Rx_LOS Output Voltage - High		V _{cc} -0.5		V _{cc} +0.3	V	I _o = 400µA; Host V _{cc}
Rx_LOS Output Voltage - Low		0		0.8	V	I _o = -4.0mA
MOD_DEF (0:2)	VoH VoL	2.5 0		0.5	V V	With Serial ID

Optical and Electrical Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit
9µm Core Diameter SMF			10		km
Data Rate			1.25		Gbps
Transmitter					
Centre Wavelength	λ _c	1270	1310	1350	nm
Spectral Width (RMS)	σ			3	nm
Average Output Power	P _{Out}	-9		-3	dBm
Extinction Ratio	EX	9			dB
Rise/Fall Time (20% – 80%)	t _{r/tf}			260	ns
Output Optical Eye	ITU-T G.957 Compliant				
Data Input Swing Differential	V _{IN}	500		2000	mV
Input Differential Impedance	Z _{IN}	90	100	110	Ω
TX Disable - Disable		2.0		V _{CC} +0.3	V
- Enable		0		0.8	V
TX_Fault - Fault		2.0		V _{CC} +0.3	V
- Normal		0		0.8	V
TX_Disable Assert Time	t _{off}			10	us

1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible

Receiver

Centre Wavelength	λ_c	1100		1600	nm
Receiver Sensitivity	PIN			-20	dBm
Output Differential Impedance	P IN	90	100	110	Ω
Data Output Swing Differential	VOUT	370		2000	mV
Rise/Fall Time	Tr/tf			2.2	ns
LOS De-Assert	LOSD			-25	dBm
LOS Assert	LOSA	-40			dBm
LOS - High		2.0		VCC+0.3	V
- Low		0		0.8	V

Product variants & accessories

Art.-No.	Description
TDE-ONS-GC-GE-LX	1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible