

1000BASE-BX10 SFP Module SM LC 10km range (1310nm Tx/1490nm Rx) Cisco compatible



GBIC-, SFP-, XFP-, XENPAK-Transceiver

The tde Small Form Pluggable Optical Transceiver are easy installed for enterprise and telecom applications. The tde SFP modular line provides a fully compatible, highly reliable and volume accessible supply of quality transceiver products with excellent performance for design-in manufacturing and end-user enterprise applications.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

1000BASE-BX10 SFP Module SM LC 10km range (1310nm Tx/1490nm Rx) Cisco compatible

Technical Data

Features

- Operating data rate up to 1.25Gbps
- 1310nmFP Tx/1490nmRx
- Distance up to 10km
- Single 3.3V Power supply and TTL Logic Interface
- Simplex LC Connector Interface
- Hot Pluggable
- Operating Case Temperature
Standard: 0°C~+70°C
Industrial:-40°C~+85°C
- Compliant with MSA SFP Specification
- Digital diagnostic monitor interface Compatible with SFF-8472

Applications

- SONET/SDH Equipment Interconnect
- Fiber Channel Links
- WDM Gigabit Ethernet Links

Regulatory Compliance

Features	Standard	Performance
Electrostatic Discharge (ESD) to the Electrical Pins	MIL-STD-883E Method 3015.7	Class 1(>500 V) Isolation with the case
Electromagnetic Interference (EMI)	FCC Part 15 Class B	Compatible with standards
Laser Eye Safety	FDA 21CFR 1040.10 and 1040.11 EN60950, EN (IEC) 60825-1,2	Compatible with Class I laser product. Compatible with T üV standards
Component Recognition	UL and CUL	UL file E317337
Green Products	RoHS	RoHS6

Absolute Maximum Ratings

Parameter	Symbol	Min.	Max.	Unit
Storage Temperature	TS	-40	+85	°C
Supply Voltage	VCC	-0.5	3.6	V

Recommended Operating Conditions

Parameter	Symbol	Min.	Typ.	Max.	Unit
Operating Case Temperature	TA GLC-BX-U TA GLC-BX-U-I	0 -40		+70 +85	°C
Power Supply Voltage	VCC	3.15	3.3	3.45	V
Power Supply Current	ICC			300	mA

1000BASE-BX10 SFP Module SM LC 10km range (1310nm Tx/1490nm Rx) Cisco compatible

Surge Current	ISurge		+30	mA
Baud Rate		1.25		GBaud

Performance Specifications - Electrical

Parameter	Symbol	Min.	Typ.	Max.	Unit	Notes
Transmitter						
LVPECL Inputs (Differential)	Vin	400		2500	mVp	AC coupled inputs
Input Impedance (Differential)	Zin	85	100	115	ohms	Rin > 100 kohms @ DC
Tx_DISABLE Input Voltage - High		2		3.45	V	
Tx_DISABLE Input Voltage - Low		0		0.8	V	
Tx_FAULT Output Voltage - High		2		Vcc+0.3	V	Io = 400µA; Host Vcc
Tx_FAULT Output Voltage - Low		0		0.5	V	Io = -4.0mA
Receiver						
LVPECL Outputs (Differential)	Vout	400	800	1200	mVpp	AC coupled outputs
Output Impedance (Differential)	Zout	85	100	115	ohms	
Rx_LOS Output Voltage - High		2		Vcc+0.3	V	Io = 400µA; Host Vcc
Rx_LOS Output Voltage - Low		0		0.8	V	Io = -4.0mA
MOD_DEF (0:2)	VoH VoL	2.5 0		0.5	V V	With Serial ID

Optical and Electrical Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit
9µm Core Diameter SMF			10		km
Data Rate			1.25		Gbps
Transmitter					
Centre Wavelength	λc	1270	1310	1350	nm
Spectral Width (RMS)	σ			4	nm
Average Output Power	P Out	-8		3	dBm
Extinction Ratio	EX	9			dB
Rise/Fall Time (20% – 80%)	tr/tf			90	ps
Total Jitter	TJ			1	ns
Output Optical Eye	ITU-T G.957 Compliant				
Data Input Swing Differential	V IN	500		2000	mV

1000BASE-BX10 SFP Module SM LC 10km range (1310nm Tx/1490nm Rx) Cisco compatible

Input Differential Impedance	ZIN	90	100	110	Ω
TX Disable - Disable		2.0		VCC+0.3	V
- Enable		0		0.8	V
TX_Fault - Fault		2.0		VCC+0.3	V
- Normal		0		0.8	V
TX_Disable Assert Time	t _{off}			10	us
Receiver					
Centre Wavelength	λ _c	1480	1490	1500	nm
Receiver Sensitivity	PIN			-22	dBm
Output Differential Impedance	P IN	90	100	110	Ω
Data Output Swing Differential	VOUT	370		2000	mV
Rise/Fall Time	Tr/tf			2.2	ns
LOS De-Assert	LOSD			-24	dBm
LOS Assert	LOSA	-40			dBm
LOS - High		2.0		VCC+0.3	V
- Low		0		0.8	V

Product variants & accessories

Art.-No.	Description
TDE-GLC-BX-U	1000BASE-BX10 SFP Module SM LC 10km range (1310nm Tx/1490nm Rx) Cisco compatible