

1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible



GBIC-, SFP-, XFP-, XENPAK-Transceiver

The tde Small Form Pluggable Optical Transceiver are easy installed for enterprise and telecom applications. The tde SFP modular line provides a fully compatible, highly reliable and volume accessible supply of quality transceiver products with excellent performance for design-in manufacturing and end-user enterprise applications.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible

Technical Data

Features

- Operating data rate up to 1.25Gbps
- 1310nm LD Transmitter
- Distance Up to 10Km
- 3.3/5V Power supply and TTL Logic Interface
- Duplex SC Connector Interface
- Hot Pluggable
- Operating Case Temperature Industrial: -40°C~+85°C
- Compliant with GBIC Specification Rev. 5.5

Applications

- WDM GBE Links
- SONET/SDH Equipment Interconnect
- Fiber Channel Links

Regulatory Compliance

Feature	Standard	Performance
Electrostatic Discharge (ESD) to the Electrical Pins	MIL-STD-883E Method 3015.7	Class 1(>500 V) Isolation with the case
Electromagnetic Interference (EMI)	FCC Part 15 Class B	Compatible with standards
Laser Eye Safety	FDA 21CFR 1040.10 and 1040.11 EN60950, EN (IEC) 60825-1,2	Compatible with Class I laser product. Compatible with T üV standards
Component Recognition	UL and CUL	UL file E317337
Green Products	RoHS	RoHS6

Absolute Maximum Ratings

Parameter	Symbol	Min.	Max.	Unit
Storage Temperature	Ts	-40	+85	°C
Supply Voltage	Vcc	0	6	V

Recommended Operating Conditions

Parameter	Symbol	Min.	Typ.	Max.	Unit
Operating Case Temperature	TA	-40		+85	°C
Power Supply Voltage	Vcc	4.75 3.15	5 3.3	5.25 4.45	V V
Power Supply Current	Icc			300	mA
Surge Current	ISurge			+30	mA
Baud Rate			1.25		GBaud

1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible

Performance Specifications - Electrical

Parameter	Symbol	Min.	Typ.	Max.	Unit	Notes
Transmitter						
LVPECL Inputs (Differential)	Vin	400		2500	mVp	AC coupled inputs
Input Impedance (Differential)	Zin	85	100	115	ohms	Rin > 100 kohms @ DC
Tx_DISABLE Input Voltage - High		2		Vcc+0.3	V	
Tx_DISABLE Input Voltage - Low		0		0.8	V	
Tx_FAULT Output Voltage - High		Vcc-0.5		Vcc+0.3	V	Io = 400µA; Host Vcc
Tx_FAULT Output Voltage - Low		0		0.5	V	Io = -4.0mA
Receiver						
LVPECL Outputs (Differential)	Vout	400	800	1200	mVpp	AC coupled outputs
Output Impedance (Differential)	Zout	85	100	115	ohms	
Rx_LOS Output Voltage - High		Vcc-0.5		Vcc+0.3	V	Io = 400µA; Host Vcc
Rx_LOS Output Voltage - Low		0		0.8	V	Io = -4.0mA
MOD_DEF (0:2)	VoH VoL	2.5 0		0.5	V V	With Serial ID

Optical and Electrical Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit
9µm Core Diameter SMF			10		km
Data Rate			1.25		Gbps
Transmitter					
Centre Wavelength	λc	1270	1310	1350	nm
Spectral Width (RMS)	σ			3	nm
Average Output Power	P Out	-9		-3	dBm
Extinction Ratio	EX	9			dB
Rise/Fall Time (20% – 80%)	tr/tf			260	ns
Output Optical Eye	ITU-T G.957 Compliant				
Data Input Swing Differential	V IN	500		2000	mV
Input Differential Impedance	ZIN	90	100	110	Ω
TX Disable - Disable - Enable		2.0 0		VCC+0.3 0.8	V V
		2.0 0		VCC+0.3 0.8	V V
TX_Fault - Fault - Normal		2.0 0		VCC+0.3 0.8	V V
		2.0 0		VCC+0.3 0.8	V V
TX_Disable Assert Time	t_off			10	us

1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible

Receiver

Centre Wavelength	λ_c	1100		1600	nm
Receiver Sensitivity	PIN			-20	dBm
Output Differential Impedance	P IN	90	100	110	Ω
Data Output Swing Differential	VOUT	370		2000	mV
Rise/Fall Time	Tr/tf			2.2	ns
LOS De-Assert	LOSD			-25	dBm
LOS Assert	LOSA	-40			dBm
LOS - High		2.0		VCC+0.3	V
- Low		0		0.8	V

Product variants & accessories

Art.-No.	Description
TDE-ONS-GC-GE-LX	1000BASE-LX GBIC Module SM SC 10km data range (1310nm) Cisco compatible