


100BASE-EX SFP Module Singlemode LC 40km data range (1310nm) Cisco compatible



## GBIC-, SFP-, XFP-, XENPAK-Transceiver

The tde Small Form Pluggable Optical Transceiver are easy installed for enterprise and telecom applications. The tde SFP modular line provides a fully compatible, highly reliable and volume accessible supply of quality transceiver products with excellent performance for design-in manufacturing and end-user enterprise applications.



**tde<sup>®</sup>** trans data elektronik GmbH

### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## 100BASE-EX SFP Module Singlemode LC 40km data range (1310nm) Cisco compatible

### Technical Data

#### Features

- Operating data rate up to 100M/155Mbps
- 1310nm FP LD Transmitter
- Distance up to 40km
- Single 3.3V Power supply and TTL Logic Interface
- Duplex LC Connector Interface
- Hot Pluggable
- Operating Case Temperature  
Standard: 0°C~+70°C  
Industrial: -40°C~+85°C
- Compliant with MSA SFP Specification
- Digital diagnostic monitor interface Compatible with SFF-8472

#### Applications

- ATM Switches and Routers
- SONET/SDH Switch Infrastructure
- Fast Ethernet Applications

#### Regulatory Compliance

| Feature                                              | Standard                                                  | Performance                                                              |
|------------------------------------------------------|-----------------------------------------------------------|--------------------------------------------------------------------------|
| Electrostatic Discharge (ESD) to the Electrical Pins | MIL-STD-883E Method 3015.7                                | Class 1(>500 V) Isolation with the case                                  |
| Electromagnetic Interference (EMI)                   | FCC Part 15 Class B                                       | Compatible with standards                                                |
| Laser Eye Safety                                     | FDA 21CFR 1040.10 and 1040.11 EN60950, EN (IEC) 60825-1,2 | Compatible with Class I laser product.<br>Compatible with T üV standards |
| Component Recognition                                | UL and CUL                                                | UL file E317337                                                          |
| Green Products                                       | RoHS                                                      | RoHS6                                                                    |

#### Absolute Maximum Ratings

| Parameter           | Symbol | Min. | Max. | Unit |
|---------------------|--------|------|------|------|
| Storage Temperature | TS     | -40  | +85  | °C   |
| Supply Voltage      | Vcc    | -0.5 | 3.6  | V    |

#### Recommended Operating Conditions

| Parameter                  | Symbol       | Min. | Typ. | Max. | Unit |
|----------------------------|--------------|------|------|------|------|
| Operating Case Temperature | GLC-FE-100EX | -40  |      | +85  | °C   |
| Power Supply Voltage       | Vcc          | 3.15 | 3.3  | 3.45 | V    |
| Power Supply Current       | Icc          |      |      | 190  | mA   |
| Surge Current              | ISurge       |      |      | +30  | mA   |

## 100BASE-EX SFP Module Singlemode LC 40km data range (1310nm) Cisco compatible

Baud Rate

155

MBaud

### Performance Specifications - Electrical

| Parameter                       | Symbol           | Min.     | Typ. | Max.                 | Unit   | Notes                                        |
|---------------------------------|------------------|----------|------|----------------------|--------|----------------------------------------------|
| <b>Transmitter</b>              |                  |          |      |                      |        |                                              |
| LVPECL Inputs (Differential)    | V <sub>in</sub>  | 400      |      | 2500                 | mVp    | AC coupled inputs                            |
| Input Impedance (Differential)  | Z <sub>in</sub>  | 85       | 100  | 115                  | ohms   | R <sub>in</sub> > 100 kohms @ DC             |
| Tx_DISABLE Input Voltage - High |                  | 2        |      | 3.45                 | V      |                                              |
| Tx_DISABLE Input Voltage - Low  |                  | 0        |      | 0.8                  | V      |                                              |
| Tx_FAULT Output Voltage - High  |                  | 2        |      | V <sub>cc</sub> +0.3 | V      | I <sub>o</sub> = 400μA; Host V <sub>cc</sub> |
| Tx_FAULT Output Voltage - Low   |                  | 0        |      | 0.5                  | V      | I <sub>o</sub> = -4.0mA                      |
| <b>Receiver</b>                 |                  |          |      |                      |        |                                              |
| LVPECL Outputs (Differential)   | V <sub>out</sub> | 400      | 800  | 1200                 | mVpp   | AC coupled outputs                           |
| Output Impedance (Differential) | Z <sub>out</sub> | 85       | 100  | 115                  | ohms   |                                              |
| Rx_LOS Output Voltage - High    |                  | 2        |      | V <sub>cc</sub> +0.3 | V      | I <sub>o</sub> = 400μA; Host V <sub>cc</sub> |
| Rx_LOS Output Voltage - Low     |                  | 0        |      | 0.8                  | V      | I <sub>o</sub> = -4.0mA                      |
| MOD_DEF ( 0:2 )                 | VoH<br>VoL       | 2.5<br>0 |      | 0.5                  | V<br>V | With Serial ID                               |

### Optical and Electrical Characteristics

| Parameter                     | Symbol                | Min. | Typ. | Max. | Unit |
|-------------------------------|-----------------------|------|------|------|------|
| 9μm Core Diameter SMF         |                       |      | 40   |      | km   |
| Data Rate                     |                       |      | 155  |      | Mbps |
| <b>Transmitter</b>            |                       |      |      |      |      |
| Centre Wavelength             | λ <sub>c</sub>        | 1260 | 1310 | 1360 | nm   |
| Spectral Width (RMS)          | σ                     |      |      | 4    | nm   |
| Average Output Power          | P <sub>Out</sub>      | -15  |      | -8   | dBm  |
| Extinction Ratio              | EX                    | 9    |      |      | dB   |
| Rise/Fall Time (20% – 80%)    | tr/ta                 |      |      | 2    | ns   |
| Total Jitter                  | TJ                    |      |      | 56.5 | ps   |
| Output Optical Eye            | ITU-T G.957 Compliant |      |      |      |      |
| Data Input Swing Differential | V <sub>IN</sub>       | 500  |      | 2000 | mV   |
| Input Differential Impedance  | Z <sub>IN</sub>       | 90   | 100  | 110  | Ω    |

## 100BASE-EX SFP Module Singlemode LC 40km data range (1310nm) Cisco compatible

|                                     |      |         |              |
|-------------------------------------|------|---------|--------------|
| TX Disable - Disable                | 2.0  | VCC+0.3 | V            |
| - Enable                            | 0    | 0.8     | V            |
| TX_Fault - Fault                    | 2.0  | VCC+0.3 | V            |
| - Normal                            | 0    | 0.8     | V            |
| TX_Disable Assert Time t_off        | 10   |         | us           |
| <b>Receiver</b>                     |      |         |              |
| Centre Wavelength $\lambda_c$       | 1100 | 1600    | nm           |
| Receiver Sensitivity PIN            |      | -31     | dBm          |
| Output Differential Impedance P IN  | 90   | 100     | 110 $\Omega$ |
| Data Output Swing Differential VOUT | 370  | 2000    | mV           |
| Rise/Fall Time Tr/tf                |      | 2.2     | ns           |
| LOS De-Assert LOSD                  |      | -35     | dBm          |
| LOS Assert LOSA                     | -40  |         | dBm          |
| LOS - High                          | 2.0  | VCC+0.3 | V            |
| - Low                               | 0    | 0.8     | V            |

## Product variants & accessories

| Art.-No.         | Description                                                                   |
|------------------|-------------------------------------------------------------------------------|
| TDE-GLC-FE-100EX | 100BASE-EX SFP Module Singlemode LC 40km data range (1310nm) Cisco compatible |