


FO-Patch cord SC APC 9°/SC APC 9° tde 9/125µ OS2 Simplex LSOH Length: xxxxx



tde - Fiber Optic Assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards, and the company has one of the most up-to-date fiber optic assembly houses in Europe. Fiber optic patch cables and trunk cables are manufactured in many different configurations using highly automated processes on two independent mass production lines. The range of products on offer encompasses the entire spectrum of connector types available on the market. Production capacity is around 100,000 fiber optic connectors per month, and this can be ramped up easily whenever required. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment such as laser cleavers and glue-dispensing robots.

Each cable application is subjected to a full test procedure comprising interferometer measurements, insertion loss and return loss measurements and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.

**tde[®]** trans data elektronik GmbH**Headquarter address:**

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

FO-Patch cord SC APC 9°/SC APC 9° tde 9/125µ OS2 Simplex LSOH Length: xxxxx

Technical Data

FO Connectors

| | |
|-----------------------|--|
| Connector Type | SC APC 9° Simplex |
| Housing | Plastic, Green |
| Ferrule | Zirconia Straight Split, Spring-loaded Axially |
| Ferrule Hole | 125.5 µ |
| Ferrule Concentricity | ≤ 0.6 µ |
| Mating Cycles | 500 |
| Operating Temperature | -40°C up to +75°C |
| Strain Relief to | 150 N |
| Manufacturer | tde |

Optical performance

| Fiber | Type | Wavelength | Insertion loss typ. | Insertion loss max. | Return loss min. |
|--------|-----------|------------|---------------------|---------------------|------------------|
| 9/125µ | SC APC 9° | 1550 nm | < 0.20 dB | 0.45 dB | 70 dB |

FO Cables

| | |
|------------------|-------------|
| Flame resistance | IEC 60332-3 |
| | IEC 60754 |
| | IEC 61034-1 |
| | IEC 61034-2 |

Cable construction

| | |
|------------------|--|
| Type | IVH01E9 |
| Tight buffer | 1x 900µ coated fiber (free movable in the compound) |
| Fiber type | 9/125µ, Corning G.657.A1 Ultra |
| Strength members | Aramid yarn (free movable in the compound) |
| Outer jacket | LSZH (Halogen free, low smoke, flame retardant thermoplastic compound) |
| Jacket color | Yellow, RAL 1021 |
| Identification | "t d e – I-V(ZN)H 1E G652.D / G657.A1 2,4mm" and sequential meter marking + Lot number |

Physical properties

| | |
|----------------------|----------------|
| Outer diameter cable | 2.4 ± 0.1 mm |
| Temperature range | -20°C to +70°C |

FO Fiber

| | |
|------|--|
| Type | Corning Ultra SMF-28® 09/125µ OS2 singlemode fiber |
|------|--|

FO-Patch cord SC APC 9°/SC APC 9° tde 9/125µ OS2 Simplex LSOH Length: xxxxx

| | |
|---|--|
| Maximum Attenuation | At 1310 nm max. 0.32 dB/km At 1383 nm max. 0.32 dB/km At 1490 nm max. 0.21 dB/km At 1550 nm max. 0.18 dB/km At 1625 nm max. 0.20 dB/km |
| Attenuation vs. Wavelength | Range: 1285 - 1330 nm; Ref. λ : 1310 nm; Max. Difference: 0.03 dB/km Range: 1525 - 1575 nm; Ref. λ : 1550 nm; Max. Difference: 0.02 dB/km |
| Macrobend Loss | Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1550nm; Induced Attenuation: ≤ 0.50 dB Mandrel Radius: 10mm; Number of Turns: 1; Wavelength: 1625nm; Induced Attenuation: ≤ 1.5 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1550nm; Induced Attenuation: ≤ 0.05 dB Mandrel Radius: 15mm; Number of Turns: 10; Wavelength: 1625nm; Induced Attenuation: ≤ 0.30 dB Mandrel Radius: 25mm; Number of Turns: 100; Wavelength: 1310nm, 1550nm, 1625nm; Induced Attenuation: ≤ 0.01 dB |
| Point Discontinuity | Wavelength: 1310 nm; Point Discontinuity: ≤ 0.05 dB Wavelength: 1550 nm; Point Discontinuity: ≤ 0.05 dB |
| Cable Cutoff Wavelength (λ_{ccf}) | $\lambda_{ccf} \leq 1260$ nm |
| Mode-Field Diameter | At 1310 nm = 9.2 ± 0.4 μ m At 1550 nm = 10.4 ± 0.5 μ m |
| Dispersion | At 1550 nm = ≤ 18.0 [ps/(nm*km)] At 1625 nm = ≤ 22.0 [ps/(nm*km)] |
| | Zero Dispersion Wavelength (λ_0): $1304 \text{ nm} \leq \lambda_0 \leq 1324 \text{ nm}$ Zero Dispersion Slope (S_0): ≤ 0.092 ps/(nm ² *km) |
| Polarization Mode Dispersion (PMD) | PMD Link Design Value = ≤ 0.04 ps/ $\sqrt{\text{km}}$ Maximum Individual Fiber = ≤ 0.1 ps/ $\sqrt{\text{km}}$ |

Dimensional Specifications

| | |
|--------------------------------|----------------------------------|
| Fiber Curl | ≥ 4.0 m radius of curvature |
| Cladding Diameter | 125.0 ± 0.7 μ m |
| Core-Clad Concentricity | ≤ 0.5 μ m |
| Cladding Non-Circularity | $\leq 0.7\%$ |
| Coating Diameter | 242 ± 5 μ m |
| Coating-Cladding Concentricity | < 12 μ m |

Environmental Specifications

| Environmental Test | Test Condition | Induced Attenuation 1310 nm, 1550 nm & 1625 nm |
|------------------------------|-----------------------------|--|
| Temperature Dependence | -60°C to +85°C | ≤ 0.05 |
| Temperature Humidity Cycling | -10°C to +85°C up to 98% RH | ≤ 0.05 |
| Water Immersion | 23°C \pm 2°C | ≤ 0.05 |
| Heat Aging | 85°C \pm 2°C | ≤ 0.05 |
| Operating Temperature Range | -60°C to +85°C | |

Mechanical Specifications

| | |
|------------|--|
| Proof Test | The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.69 GPa). |
| Length | Fiber lengths available up to 63.0 km/spool. |

FO-Patch cord SC APC 9°/SC APC 9° tde 9/125μ OS2 Simplex LSOH Length: xxxxx

Performance Characterizations

| | |
|--|--|
| Core Diameter | 8.2 μm |
| Numerical Aperture | 0.14 |
| Effective Group Index of Refraction | 1310 nm: 1.4676 1550 nm: 1.4682 |
| Fatigue Resistance Parameter (nd) | 20 |
| Coating Strip Force | Dry: 0.6 lbs (3N) Wet: 14 days room temperature: 0.6 lbs (3N) |
| Rayleigh Backscatter Coefficient (for 1 ns Pulse Width) | 1310 nm: -77 dB 1550 nm: -82 dB |

Product variants & accessories

| Art.-No. | Description |
|--------------------|---|
| L-SC9/SC9-09Sxxxxx | FO-Patch cord SC APC 9°/SC APC 9° tde 9/125μ OS2 Simplex LSOH Length: xxxxx |
| L-SC/SC09Sxxxxx | FO-Patch cord SC/SC tde 9/125μ OS2 Simplex LSOH Length: xxxxx |
| L-SC/SC50S3-xxxxx | FO-Patch cord SC/SC tde 50/125μ OM3 Simplex LSOH Length: xxxxx |
| L-SC/SC50S4-xxxxx | FO-Patch cord SC/SC tde 50/125μ OM4 Simplex LSOH Length: xxxxx |
| L-SC/SC50Sxxxxx | FO-Patch cord SC/SC tde 50/125μ OM2 Simplex LSOH Length: xxxxx |
| L-SC/SC62Sxxxxx | FO-Patch cord SC/SC tde 62,5/125μ OM1 Simplex LSOH Length: xxxxx |