

tde - FO Cable Pigtail ST 62,5/125 μ OM1 Simplex LSOH Length: xxxxx



tde - Fiber Optic Assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards, and the company has one of the most up-to-date fiber optic assembly houses in Europe. Fiber optic patch cables and trunk cables are manufactured in many different configurations using highly automated processes on two independent mass production lines. The range of products on offer encompasses the entire spectrum of connector types available on the market. Production capacity is around 100,000 fiber optic connectors per month, and this can be ramped up easily whenever required. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment such as laser cleavers and glue-dispensing robots.

Each cable application is subjected to a full test procedure comprising interferometer measurements, insertion loss and return loss measurements and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tde - FO Cable Pigtail ST 62,5/125 μ OM1 Simplex LSOH Length: xxxxx

Technical Data

FO Connectors

Connector Type	ST
Housing	Metal
Ferrule	Zirconia Straight Split
Ferrule Hole	126 μ
Mating Cycles	1.000
Operating Temperature	-40°C up to +75°C
Strain Relief to	150 N
Manufacturer	tde

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 μ OM2	ST	850 nm	≤ 0.25 dB	0.45 dB	30 dB
62.5/125 μ OM1	ST	850 nm	≤ 0.25 dB	0.45 dB	

FO Cables

Flame resistance	IEC 60332-3
	IEC 60754
	IEC 61034-1
	IEC 61034-2

Cable construction

Tight buffer	1x 900 μ coated fiber (free movable in the compound)
Fiber type	MM-OM1, 62.5/125 μ , Corning
Strength members	Aramid yarn (free movable in the compound)
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Orange, RAL 2003
Identification	"t d e – IVH01G62-2.4 LSZH" and sequential meter marking + Lot number

Physical properties

Outer diameter cable	2.4 \pm 0.1 mm
Temperature range	-20°C to +70°C

FO Fiber

Type	Corning 62.5/125 μ OM1 multimode fiber
Manufacturer	Corning

tde - FO Cable Pigtail ST 62,5/125 μ OM1 Simplex LSOH Length: xxxxx

Optical Specifications

Bandwidth	160/200 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. \leq 3.0 dB/km At 1300 nm max. \leq 0.7 dB/km
Numerical Aperture	0.275 \pm 0.015

Dimensional Specifications

Core Diameter	62.5 \pm 3.0 μ m
Cladding Diameter	125.0 \pm 2.0 μ m
Core-Clad Concentricity	\leq 3.0 μ m
Cladding Non-Circularity	< 2.0%
Core Non-Circularity	\leq 5.0%
Coating Diameter	245 \pm 5 μ m
Coating-Cladding Concentricity	< 12 μ m

Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 850 nm and 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	\leq 0.20
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	\leq 0.20
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress \geq 100 kpsi (0.7 GN/m ²).
Length	Fiber lengths available up to 17.6 km/spool.

Performance Characterizations

Refractive Index Difference	2%
Effective Group Index of Refraction	850 nm: 1.496 1300 nm: 1.491
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength (λ_0): 1332 nm \leq λ_0 \leq 1354 nm Zero Dispersion Slope (S0): \leq 0.097 ps/(nm ² *km)

Product variants & accessories

Art.-No.	Description
L-ST/-09Sxxxxx	tde - FO Cable Pigtail ST 9/125 μ OS2 Simplex LSOH Length: xxxxx
L-ST/-50S3-xxxxx	tde - FO Cable Pigtail ST 50/125 μ OM3 Simplex LSOH Length: xxxxx

tde - FO Cable Pigtail ST 62,5/125 μ OM1 Simplex LSOH Length: xxxxx

Art.-No.	Description
L-ST/-50Sxxxxx	tde - FO Cable Pigtail ST 50/125 μ Simplex OM2 LSOH Length: xxxxx
L-ST/-62Sxxxxx	tde - FO Cable Pigtail ST 62,5/125 μ OM1 Simplex LSOH Length: xxxxx