

FO Universal Cable 24x SC/24x SC 24G50/125μ OM3 LSHF, Length: xxxx



tde - Fiber Optic Assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards, and the company has one of the most up-to-date fiber optic assembly houses in Europe. Fiber optic patch cables and trunk cables are manufactured in many different configurations using highly automated processes on two independent mass production lines. The range of products on offer encompasses the entire spectrum of connector types available on the market. Production capacity is around 100,000 fiber optic connectors per month, and this can be ramped up easily whenever required. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment such as laser cleavers and glue-dispensing robots.

Each cable application is subjected to a full test procedure comprising interferometer measurements, insertion loss and return loss measurements and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.

**tde[®]** trans data elektronik GmbH**Headquarter address:**

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

FO Universal Cable 24x SC/24x SC 24G50/125μ OM3 LSHF, Length: xxxx

Technical Data

FO Connectors

Connector Type	SC Simplex
Housing	Plastic, Aqua
Ferrule	Zirconia Straight Split, Spring-loaded Axially
Ferrule Hole	126 μ
Mating Cycles	1.000
Operating Temperature	-40°C up to +75°C
Strain Relief to	150 N
Manufacturer	tde

Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM3	SC	850 nm	≤ 0.25 dB	0.45 dB	30 dB

FO Fan-Out

Fan-out length	50 mm
Ø Fan-out	16 mm
Ø Single unit	1.7 - 2 mm
Single unit length	78 ± 5 cm (not stepped)

FO Cables

Mechanical characteristics

Temperature range	Storage -25 to +70°C, IEC 60794-1-22 F1
	Pulling in -10 to +50°C
	Operation -25 to +60°C
Tensile performance	IEC 60794-1-21 E1
Crush resistance	IEC 60794-1-21 E3
Impact	IEC 60794-1-21 E4
Repeated bending	IEC 60794-1-21 E6
Torsion	IEC 60794-1-21 E7
Bend	IEC 60794-1-21 E11
Water penetration	IEC 60794-1-22 F5

General characteristics

Sheath colour	green, similar to RAL 6016
Zero halogen, no corrosive gases	IEC 60754-1/-2, EN 60754-1/-2, VDE 0482-754-1/-2
Flame propagation	IEC 60332-1-2, EN 60332-1-2, VDE 0482-332-1-2

FO Universal Cable 24x SC/24x SC 24G50/125μ OM3 LSHF, Length: xxxx

Flame spread	IEC 60332-3-24, EN 50266-2-4, VDE 0482-266-2-4
Smoke density	IEC 61034-1/-2, EN 61034-1/-2, VDE 0482-1034-1/-2
Reaction to fire (Euroclasses)	EN 13501-6: D _{ca}

Cabletype	Universal U-DQ(ZN)BH for indoor and outdoor use
	non metallic, dry interstices, rodent protection, flame retardant, in accordance with IEC 60332.1 and IEC 60332.3 C
Fibertype	Corning G50/125 OM3
No. of fibers	24
Loose tube	1
Sheath ø	8.2 mm
Weight	72 kg/km
Bending radius	125 mm
Tensile load short term	3.500 N
Tensile load continuous	1.500 N
Crush resistance short term	5.000 N
Crush resistance continuous	3.000 N
Fire load	336 kWh/km

Length tolerances (prefabricated with plugs)

Tolerances for lengths up to 40m	± 100 cm
Tolerances for lengths up to 100m	± 100 cm
Tolerances for lengths from 100m	± 2%

FO Fiber

Optical properties

Attenuation typical (cabled)	850 nm: 2.5 / 1300 nm: 0.5 dB/km
Attenuation maximum (cabled)	850 nm: 2.7 / 1300 nm: 0.7 dB/km
OFL bandwidth as per TIA/EIA 455-204 and IEC 60793-1-41	850 nm: 3500 / 1300 nm: 500 MHz x km
High-Performance EMB bandwidth as per TIA/EIA 455-220A and IEC 60793-1-49	850 nm: 4700 / 1300 nm: 4700 MHz x km
Refractive Index	850 nm: 1.480 / 1300 nm: 1.479

Technical properties

Bending radius	No. of windings (turns)	Max. induced attenuation
37.5 mm	100	850 nm: ≤ 0.05 / 1300 nm: ≤ 0.15 dB/km
15 mm	2	850 nm: ≤ 0.1 / 1300 nm: ≤ 0.3 dB/km
7.5 mm	2	850 nm: ≤ 0.2 / 1300 nm: ≤ 0.5 dB/km

FO Universal Cable 24x SC/24x SC 24G50/125μ OM3 LSHF, Length: xxxx

Geometrical and mechanical characteristics

Numerical Aperture	0.200 +/- 0.015
Core Ø	50.0 +/- 2.5 μm
Maximum Core Non-Circularity	5 %
Cladding Ø	125.0 +/- 1.0 μm
Maximum Cladding Non-Circularity	1.0 %
Maximum Cladding/Core Concentricity Error	1.5 μm
Maximum Coating Concentricity Error	12 μm
Coating Ø	242 +/- 5 μm
Test load	100 kpsi

Product variants & accessories

Art.-No.	Description
L-SC/SC50B12G3-xxxx	FO Universal Cable 12x SC/12x SC 12G50/125μ OM3 LSHF, Length: xxxx
L-SC/SC50B24G3-xxxx	FO Universal Cable 24x SC/24x SC 24G50/125μ OM3 LSHF, Length: xxxx
L-SC/SC50B48G3-xxxx	FO Universal Cable 48x SC/48x SC 48G50/125μ OM3 LSHF, Length: xxxx
L-SC/SC50B72G3-xxxx	FO Universal Cable 72x SC/72x SC 72G50/125μ OM3 LSHF, Length: xxxx
L-SC/SC50B96G3-xxxx	FO Universal Cable 96x SC/96x SC 96G50/125μ OM3 LSHF, Length: xxxx