


S/FTP Patch cord RJ45/RJ45 Hirose w. tde boot Cat.6<sub>A</sub> UC900 LSHF Crossover Length: xxxx



## tde - TP cable assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards. The patch cables and trunk cables are manufactured in many different configurations using highly automated processes. The range of products on offer encompasses the entire spectrum of connector types available on the market. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment.

Each cable application is subjected to a full test procedure and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.

RJ45 Patch cord for the employment in the distribution frame or for the connection of terminals.



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

S/FTP Patch cord RJ45/RJ45 Hirose w. tde boot Cat.6<sub>A</sub> UC900 LSHF Crossover Length: xxxx

## Technical Data

|               |   |
|---------------|---|
| Cabletype     | Draka UC900 SS27 Cat.7  |
| Configuration | Crossover   |
| Tests         | 100% electrical test on short-circuit and visual final inspection |
|               | optional: Link Performance Tests                                  |
|               | QS-Managementsystem ISO 9001, ISO 14001 and TL 9000               |

xxxx = Length in cm

## Connectors

|                                     |   |
|-------------------------------------|---|
| Type                                | RJ45 (TM31), with integreted dwell lever protection |
| Shielding                           | shielded  |
| Dimensions Boot                     | 34 mm length  |
|                                     | 13.4 mm width                                       |
| Manufacturer                        | Hirose (connector)                                  |
|                                     | tde (boot)  |
| QS-Management Systems Certification | ISO 9001  |
|                                     | ISO 14001   |
|                                     | TL 9000   |
| YY - Boot color                     | BL - Blue   |
|                                     | GE - Yellow   |
|                                     | GN - Green  |
|                                     | GR - Grey   |
|                                     | OR - Orange   |
|                                     | RT - Red  |
|                                     | SW - Black  |
|                                     | VI - Violett  |

## TP Cable

|                                |                                |
|--------------------------------|--------------------------------|
| Standards                      | EN 50173-1                     |
|                                | EN 50288-4-2                   |
|                                | ISO/IEC 11801                  |
|                                | IEC 61156-6                    |
|                                | IEEE 802.3af / at / bt         |
| Flame resistance LSHF (FRNC)   | IEC 60332-1                    |
|                                | IEC 60754-2                    |
|                                | IEC 61034                      |
| Reaction to fire (Euroclasses) | Class D <sub>ca</sub> s2 d2 a1 |

S/FTP Patch cord RJ45/RJ45 Hirose w. tde boot Cat.6<sub>A</sub> UC900 LSHF Crossover Length: xxxx

## Construction

|                 |  |
|-----------------|--|
| Type            | DRAKA UC900 FLEX CAT.7 S/FTP 4P LSHF               |
| Conductor       | stranded bare copper wire AWG 26/7                 |
| Insulation      | Foam Skin Polyethylene, Ø 1,00 mm                  |
| Wire color code | blue/white; orange/white; green white; brown/white |
| Twisting        | 2 cores to the pair                                |
| Pair screen     | Al-laminated plastic foil                          |
| Cable lay up    | 4 pairs (PiMF) to the core                         |
| Screen          | Copper braid, tinned                               |
| Sheath          | LSHF, Color see type table                         |

## Mechanical properties

|                        |                     |                |
|------------------------|---------------------|----------------|
| Minimum bending radius | Without load        | 4 x D          |
|                        | With load           | 8 x D          |
| Temperature range      | During operation    | -20°C to +60°C |
|                        | During installation | 0°C to +50°C   |

## Electrical properties at 20°C ± 5°C

|                                 |                                       |               |
|---------------------------------|---------------------------------------|---------------|
| Loop resistance                 |                                       | 290 Ω /km     |
| Resistance unbalance            |                                       | ≤ 3%          |
| Insulation resistance           | 500 V                                 | ≥ 2000 MΩkm   |
| Mutual capacitance              | at 800 Hz                             | Nom. 43 nF/km |
| Capacitance unbalance           | (pair/ground)                         | ≤ 1500 pF/km  |
| Mean characteristic impedance   | 100 MHz                               | 100 ± 5 Ω     |
| Nominal velocity of propagation |                                       | ca. 79%       |
| Propagation delay               |                                       | 460 ns/100m   |
| Delay skew                      |                                       | 12 ns/100m    |
| Test voltage                    | (DC, 1 min) core/core and core/screen | 1000 V        |
| Transfer impedance              | at 1 MHz                              | 25 mΩ/m       |
|                                 | at 10 MHz                             | 25 mΩ/m       |
| Coupling attenuation            |                                       | 80 dB         |

## Electrical Data (nominal) acc. to Cat.7 (at 20°C)

| F    | Attenuation | NEXT | ACR     | ELFEXT  | Return loss |
|------|-------------|------|---------|---------|-------------|
| MHZ  | dB/10m      | dB   | dB/100m | dB/100m | dB          |
| 1,0  |             |      |         |         |             |
| 4,0  |             |      |         |         | 24          |
| 10,0 | 1,0         | 90   | 89      | 80      | 25          |
| 16,0 | 1,3         | 90   | 89      | 76      | 25          |
| 20,0 | 1,4         | 90   | 89      | 74      | 25          |
| 31,2 | 1,8         | 90   | 88      | 70      | 25          |

S/FTP Patch cord RJ45/RJ45 Hirose w. tde boot Cat.6<sub>A</sub> UC900 LSHF Crossover Length: xxxx

|        |      |    |    |    |    |
|--------|------|----|----|----|----|
| 62,5   | 2,6  | 90 | 87 | 64 | 23 |
| 100,0  | 3,2  | 87 | 84 | 60 | 21 |
| 155,5  | 4,0  | 84 | 80 | 56 | 19 |
| 200,0  | 4,6  | 82 | 77 | 54 | 18 |
| 250,0  | 5,1  | 81 | 76 | 52 | 18 |
| 300,0  | 5,6  | 80 | 74 | 50 | 17 |
| 600,0  | 7,9  | 75 | 67 | 44 | 17 |
| 750,0  | 8,7  | 73 | 64 | 42 |    |
| 900,0  | 9,7  | 72 | 62 | 41 |    |
| 1000,0 | 10,2 | 71 | 61 | 40 |    |

|                       |  |
|-----------------------|--|
| Outer diameter        | 5.9 mm   |
| Fire load             | 349 MJ/km  |
|                       | 0.097 kWh/m  |
| Weight                | 39 kg/km   |
| Copper content        | 24   |
| Tensile force         | 100 N  |
| Available colors (zz) | (GR) grey, (GN) green, (BL) blue, (GE) yellow, (RT) red, (OR) orange, (SW) black, (VI) magenta |

## Product variants & accessories

| Art.-No.           | Description  |
|--------------------|--|
| SS-H6AZyyE-Nzzxxxx | S/FTP Patch cord RJ45/RJ45 Hirose w. tde boot Cat.6 <sub>A</sub> UC900 LSHF Crossover Length: xxxx |
| SS-H6AZyy-Nzzxxxx  | S/FTP Patch cord RJ45 Hirose w. tde boot Cat.6 <sub>A</sub> UC900 LSHF Length: xxxx                |