

1.25Gbps SFP Module Multimode LC, 550m data range (850nm)



GBIC-, SFP-, XFP-, XENPAK-Transceiver

The tde Small Form Pluggable Optical Transceiver are easy installed for enterprise and telecom applications. The tde SFP modular line provides a fully compatible, highly reliable and volume accessible supply of quality transceiver products with excellent performance for design-in manufacturing and end-user enterprise applications.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

1.25Gbps SFP Module Multimode LC, 550m data range (850nm)

Technical Data

Features

- Operating data rate up to 1,25Gbps
- 850nm VCSEL Laser Transmitter
- 550m with 50/125µm MMF, 300m on 62,5/125µm MMF
- Single 3.3V Power supply and TTL Logic Interface
- Duplex LC Connector Interface
- Hot Pluggable
- Operating Case Temperature Industrial: -40°C~+85°C
- Compliant with MSA SFP Specification
- Digital diagnostic monitor interface Compatible with SFF-8472

Applications

- Gigabit Ethernet
- Fiber channel
- Switch to switch interface
- High speed I/O for file servers

Regulatory Compliance

Features	Standard	Performance
Electrostatic Discharge (ESD) to the Electrical Pins	MIL-STD-883E Method 3015.7	Class 1(>500 V) Isolation with the case
Electromagnetic Interference (EMI)	FCC Part 15 Class B	Compatible with standards
Laser Eye Safety	FDA 21CFR 1040.10 and 1040.11 EN60950, EN (IEC) 60825-1,2	Compatible with Class I laser product. Compatible with T üV standards
Component Recognition	UL and CUL	UL file E317337
Green Products	RoHS	RoHS6

Absolute Maximum Ratings

Parameter	Symbol	Min.	Max.	Unit
Storage Temperature	T _s	-40	+85	°C
Supply Voltage	V _{cc}	-0.5	3.6	V

Recommended Operating Conditions

Parameter	Symbol	Min.	Typ.	Max.	Unit
Operating Case Temperature	T _A	-40		+85	°C
Power Supply Voltage	V _{cc}	3.15	3.3	3.45	V
Power Supply Current	I _{cc}			300	mA
Surge Current	I _{Surge}			+30	mA

1.25Gbps SFP Module Multimode LC, 550m data range (850nm)

Baud Rate

1.25

GBaud

Performance Specifications - Electrical

Parameter	Symbol	Min.	Typ.	Max.	Unit	Notes
Transmitter						
LVPECL Inputs (Differential)	V _{in}	400		2500	mVp	AC coupled inputs
Input Impedance (Differential)	Z _{in}	85	100	115	ohms	R _{in} > 100 kohms at DC
Tx_DISABLE Input Voltage - High		2		3.45	V	
Tx_DISABLE Input Voltage - Low		0		0.8	V	
Tx_FAULT Output Voltage - High		2		V _{cc} +0.3	V	I _o = 400µA; Host V _{cc}
Tx_FAULT Output Voltage - Low		0		0,5	V	I _o = -4.0mA
Receiver						
LVPECL Outputs (Differential)	V _{out}	400	800	1200	mVpp	AC coupled outputs
Output Impedance (Differential)	Z _{out}	85	100	115	ohms	
Rx_LOS Output Voltage - High		2		V _{cc} +0.3	V	I _o = 400µA; Host V _{cc}
Rx_LOS Output Voltage - Low		0		0.8	V	I _o = -4.0mA
MOD_DEF (0:2)	VoH VoL	2.5 0		0.5	V V	With Serial ID

Optical and Electrical Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit
50µm Core Diameter MMF	L			550	m
Data Rate			1.25		Gbps
Transmitter					
Centre Wavelength	λ _c	820	850	860	nm
Spectral Width (RMS)	σ			0.85	nm
Average Output Power	P _{out}	-9		-4	dBm
Extinction Ratio	EX	9			dB
Rise/Fall Time (20% – 80%)	tr/tf			260	ps
Output Optical Eye	ITU-T G.957 Compliant				
Data Input Swing Differential	V _{IN}	500		2000	mV
Input Differential Impedance	Z _{IN}	90	100	110	Ω
Tx Disable - Disable		2.0		V _{CC} +0.3	V
- Enable		0		0.8	V

1.25Gbps SFP Module Multimode LC, 550m data range (850nm)

TX_Fault - Fault		2.0		VCC+0.3	V
- Normal		0		0.8	V
TX_Disable Assert Time	t _{off}			10	us
Receiver					
Centre Wavelength	λ _c	760		860	nm
Receiver Sensitivity	P _{IN}			-17	dBm
Output Differential Impedance	P _{IN}	90	100	110	Ω
Data Output Swing Differential	V _{OUT}	370		2000	mV
Rise/Fall Time	Tr/tf			2.2	ns
LOS De-Assert	LOS _D			-20	dBm
LOS Assert	LOS _A	-40			dBm
LOS -High		2.0		VCC+0.3	V
-Low		0		0.8	V

Product variants & accessories

Art.-No.	Description
TDE-AS-SX	1.25Gbps SFP Module Multimode LC, 550m data range (850nm)