

tBL<sup>®</sup> - RJ45 Keystone Module Cat.6<sub>A</sub> ISO/IEC with LID w/o termination block



## tBL<sup>®</sup> - tde Basic Link (TP)

tBL<sup>®</sup> tde Basic Link (TP) is a complete system solution for structured cabling in Cat6A for transfer rates of up to 10GbE in real time. The tBL<sup>®</sup> - cabling link corresponds to a permanent link in accordance with ISO / IEC 11801 (EN 50173). The RJ45 modules are available in the form factors Keystone (KS) and Data Center (DC). The compact design of the 6fold RJ45 DC module allows a high packing density of up to 48 RJ45 ports on 1U. The RJ45 module is connected to the tBL<sup>®</sup> - cable termination block by simply plugging. The slim cable termination block can be easily assembled on the cable by using the tBL<sup>®</sup> - crimp tool and is suitable for preterminated cables. The modular design of individual RJ45 modules are interchangeable at any time without termination. A cost effective alternative product is the RJ45 keystone module without cable termination block in the tool-less design.

The system solution is complemented by an extensive portfolio of carrier systems. These include design-capable data outlets, floor box frames, Consolidation points, DIN rail modules and patch panels in 1/2 and 1U.



**tde<sup>®</sup> trans data elektronik GmbH**

### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

## tBL® - RJ45 Keystone Module Cat.6<sub>A</sub> ISO/IEC with LID w/o termination block

### Technical Data

#### Mechanical properties

Type	RJ45 Jack shielded LID
Connector standard	IEC 60603-7-5-1
Installation dimension	19.3 x 14.7 mm
Mating force	≤ 30 N
Mating cycles (RJ45 side)	≥ 750
Mating cycles (opposite side)	≥ 100
Housing material	nickel-plated die-cast zinc
Insulation components material	PC aqua opak
Gold plating in contact area	50 μ"
Gold plating IDC	30 μ"
Cable diameter	5-10 mm

#### Environmental requirements

Connection class	IP20
Temperature range	-40°C to +70°C

#### Electrical properties

Contact resistance	≤ 20 mΩ
Insulation resistance between contacts	≥ 500 MΩ
Dielectric withstanding voltage contact – contact	≥ 1000 V DC/AC
Dielectric withstanding voltage contact – screen	--
Current-carrying capacity at 50°C	1.25 A
PoE+ per IEEE 802.3at	PoE+

#### Transmission characteristics

10 GbE	supported
Cat.6 <sub>A</sub>	ISO/IEC 11801 AM1 and AMD2, Link length: > 1 m

#### LiD Function

supply voltage	12 V DC
lightdetection	≥ 200 m
light exits	≤ 20

tBL<sup>®</sup> - RJ45 Keystone Module Cat.6<sub>A</sub> ISO/IEC with LID w/o termination block

## Product variants & accessories

Art.-No.	Description
TBL-KT22/24GE	tBL <sup>®</sup> - termination block AWG 22-24,transparent yellow for installation cables
TBL-KT26/27WS	tBL <sup>®</sup> - termination block AWG 26-27, transparent white for stranded cables
TBL-LID-TOOL	tBL <sup>®</sup> - Detector for RJ45 modules with LID function
TBL-RJ45KSL	tBL <sup>®</sup> - RJ45 Keystone Module Cat.6 <sub>A</sub> ISO/IEC with LID w/o termination block
TBL-RJ45KSL/KT22	tBL <sup>®</sup> - RJ45 Keystone Module Cat.6 <sub>A</sub> ISO/IEC with LID, termination block AWG 22-24
TBL-RJ45KSL/KT26	tBL <sup>®</sup> - RJ45 Keystone Module Cat.6 <sub>A</sub> ISO/IEC with LID, termination block AWG 26-27