

tSML - FO Micro Distribution Trunk Cable both sides 1x MPO Female 12E9/125 μ OS2 LSHF, Type C,

Length: xxx in m



tSML - tde Semi Modular Link

tSML is a modular developed cabling system, which consists of two core components: module and trunk cable. The system components, preterminated with connectors and tested ex works, facilitate very fast installation of both twisted pair and fiber-optic cables. Ready-made trunk cables, providing a high number of pairs or fibers, can simply be plugged together using patch panels. Up to 96x LC duplex and/or 48 x RJ45 of haven can be accommodated in such a way on 1U. At the heart of the System are MPO/MTP[®] and Telco connectors, with which 12 optical fibers or 24 copper pairs can be connected simultaneously. Fiber-optic and twisted pair modules can be combined on 1U within a panel without difficulty.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tSML - FO Micro Distribution Trunk Cable both sides 1x MPO Female 12E9/125µ OS2 LSHF, Type C,
Length: xxx in m

Technical Data

The tSML- FO trunk cable is preterminated with MPO/MTP®connectors on both ends. The Cable is very slim and flexible. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP®plug has a defined fiber height of 1 - 3,5µ. The max. adjacent fiber height difference is 0,2µm and for all fibers 0,3µm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number.

Cable	Round cable, loose tube, LSOH, yellow
Nominal diameter	3.0 mm
Connectors	MPO/MTP® APC Female Push Pull (green)
Pin out	Crossover (TIA/EIA-568-B.1 Methode C)
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

xxx - stands for the cable length in meters (every length available)

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP® plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

Connector

Type	MPO/MTP® Female Push Pull Locking (Green)
Ferrule	12 Fiber SM Elite® ferrule, PPS
Boot colour	Black
Temperature range	-40°C bis +75°C
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
9/125µ OS2	MPO/MTP®APC	1310 / 1550 nm	≤ 0.10 dB	0.20 dB	75 dB

FO Cables

Standards	EN 50173-5
	IEC 60794-2-20
	ISO/IEC 24764
Flame resistance	IEC 60332-1-2

tSML - FO Micro Distribution Trunk Cable both sides 1x MPO Female 12E9/125µ OS2 LSHF, Type C,
Length: xxx in m

	IEC 60332-2-2
	IEC 60754-1
	IEC 60754-2
	IEC 61034

Cable construction

Type	IVH12E09
Loose tube	12 coated fibers within PVC-core tube
Fiber type	SM-G652D, 9/125µ, Corning SMF-28e+, OS2
Strength members	Aramid yarn
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Yellow, RAL 1021
Identification	"t d e – IVH12E09–MPO LSZH" and sequential meter marking + Lot number

Physical properties

Outer diameter cable	3.0 ± 0.1 mm
Diameter PVC-core tube	1.8 ± 0.1 mm
Wall thickness PVC-core tube	0.35 mm – 0.40 mm
Max. tensile load	300 N
Min. bending radius	30 mm
Temperature range (storage, installation, operation)	-20°C to +70°C

FO Fiber

Type	Corning SMF-28e+® 09/125µ OS2 G.652.D singlemode fiber
Maximum Attenuation	At 1310 nm max. 0.33 - 0.35 dB/km At 1383 ± 3 nm max. 0.31 - 0.35 dB/km At 1490 nm max. 0.21 - 0.24 dB/km At 1550 nm max. 0.19 - 0.20 dB/km At 1625 nm max. 0.20 - 0.23 dB/km
Attenuation vs. Wavelength	Range: 1285 - 1330 nm; Ref. λ: 1310 nm; Max. Difference: 0.03 dB/km Range: 1525 - 1575 nm; Ref. λ: 1550 nm; Max. Difference: 0.02 dB/km
Macrobend Loss	Mandrel Diameter:32mm; Number of Turns: 1; Wavelength: 1550nm; Induced Attenuation: ≤0.03 dB Mandrel Diameter:50mm; Number of Turns: 100; Wavelength: 1310nm; Induced Attenuation: ≤0.03 dB Mandrel Diameter:50mm; Number of Turns: 100; Wavelength: 1550nm; Induced Attenuation: ≤0.03 dB Mandrel Diameter:60mm; Number of Turns: 100; Wavelength: 1625nm; Induced Attenuation: ≤0.03 dB
Point Discontinuity	Wavelength: 1310 nm; Point Discontinuity: ≤ 0.05 dB Wavelength: 1550 nm; Point Discontinuity: ≤ 0.05 dB
Cable Cutoff Wavelength (λ _{ccf})	λ _{ccf} ≤ 1260 nm
Mode-Field Diameter	At 1310 nm = 9.2 ± 0.4 µm At 1550 nm = 10.4 ± 0.5 µm
Dispersion	At 1550 nm = ≤ 18.0 [ps/(nm*km)] At 1625 nm = ≤ 22.0 [ps/(nm*km)]

tSML - FO Micro Distribution Trunk Cable both sides 1x MPO Female 12E9/125μ OS2 LSHF, Type C,

Length: xxx in m

	Zero Dispersion Wavelength (λ_0): 1310 nm $\leq \lambda_0 \leq$ 1324 nm Zero Dispersion Slope (S_0): ≤ 0.092 ps/(nm ² *km)
Polarization Mode Dispersion (PMD)	PMD Link Design Value = ≤ 0.06 ps/√km Maximum Individual Fiber = ≤ 0.1 ps/√km
Norm	ITU-T Recommendation G.652 (Tables A, B, C, and D) IEC Specifications 60793-2-50 Type B1.3 TIA/EIA 492-CAAB Telcordia Generic Requirements GR-20-CORE ISO 11801 OS2

Dimensional Specifications

Fiber Curl	≥ 4.0 m radius of curvature
Cladding Diameter	125.0 ± 0.7 μm
Core-Clad Concentricity	≤ 0.5 μm
Cladding Non-Circularity	$\leq 0.7\%$
Coating Diameter	242 ± 5 μm
Coating-Cladding Concentricity	< 12 μm

Environmental Specifications

Environmental Test	Test Condition	Induced Attenuation 1310 nm, 1550 nm & 1625 nm
Temperature Dependence	-60°C to +85°C	≤ 0.05
Temperature Humidity Cycling	-10°C to +85°C up to 98% RH	≤ 0.05
Water Immersion	23°C \pm 2°C	≤ 0.05
Heat Aging	85°C \pm 2°C	≤ 0.05
Operating Temperature Range	-60°C to +85°C	

Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GPa).
Length	Fiber lengths available up to 63.0 km/spool.

Performance Characterizations

Core Diameter	8.2 μm
Numerical Aperture	0.14
Zero Dispersion Wavelength (λ_0)	1317 nm
Zero Dispersion Slope (S_0)	0.088 ps/(nm ² *km)
Effective Group Index of Refraction	1310 nm: 1.4676 1550 nm: 1.4682
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (3N) Wet: 14 days room temperature: 0.6 lbs (3N)

tSML - FO Micro Distribution Trunk Cable both sides 1x MPO Female 12E9/125 μ OS2 LSHF, Type C,
Length: xxx in m

Rayleigh Backscatter Coefficient (for 1 ns Pulse Width)	1310 nm: -77 dB 1550 nm: -82 dB
--	------------------------------------

Product variants & accessories

Art.-No.	Description
TSML-MP/MP09I12Exxx	tSML - FO Micro Distribution Trunk Cable both sides 1x MPO Female 12E9/125 μ OS2 LSHF, Type C, Length: xxx in m
TSML-MP/MP50I12G3-xxx	tSML - FO Micro Distribution Trunk Cable both sides 1x MPO Female 12G50/125 μ OM3 LSHF, Type C, Length: xxx in m
TSML-MP/MP50I12G4-xxx	tSML - FO Micro Distribution Trunk Cable both sides 1x MPO Female 12G50/125 μ OM4 LSHF, Type C, Length: xxx in m