

tBL[®] - RJ45 DC 6fold Module Cat.6_A ISO/IEC



tBL[®] - tde Basic Link (TP)

tBL[®] tde Basic Link (TP) is a complete system solution for structured cabling in Cat6A for transfer rates of up to 10GbE in real time. The tBL[®] - cabling link corresponds to a permanent link in accordance with ISO / IEC 11801 (EN 50173). The RJ45 modules are available in the form factors Keystone (KS) and Data Center (DC). The compact design of the 6fold RJ45 DC module allows a high packing density of up to 48 RJ45 ports on 1U. The RJ45 module is connected to the tBL[®] - cable termination block by simply plugging. The slim cable termination block can be easily assembled on the cable by using the tBL[®] - crimp tool and is suitable for preterminated cables. The modular design of individual RJ45 modules are interchangeable at any time without termination. A cost effective alternative product is the RJ45 keystone module without cable termination block in the tool-less design.

The system solution is complemented by an extensive portfolio of carrier systems. These include design-capable data outlets, floor box frames, Consolidation points, DIN rail modules and patch panels in 1/2 and 1U.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 8805 61 13
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tBL[®] - RJ45 DC 6fold Module Cat.6_A ISO/IEC

Technical Data

System platforms	tML [®] / tSML
	4x tBL [®] - 6fold Modules can be integrated in a tSML - TP Module.
	1x tBL [®] - 6fold Module can be integrated in a tML [®] - TP Module.
Equipping	6x tBL [®] RJ45 DC Module Cat.6 _A

tBL[®] - RJ45 DC-Module Cat.6_A ISO/IEC w/o termination block, GHMT certified

Mechanical properties

Type	RJ45 Jack shielded
Connector standard	IEC 60603-7-5-1
Certification	GHMT
Installation dimension	19.3 x 14.7 mm
Mating force	≤30 N
Mating cycles (RJ45 side)	≥750
Mating cycles (opposite side)	≥100
Housing material	nickel-plated die-cast zinc
Insulation components material	PC aqua
Gold plating in contact area	30 μ"
Contacting	AWG 27-22
Cable diameter	5-10 mm

Environmental requirements

Connection class	IP20
Temperature range	-40°C to +70°C

Electrical properties

Contact resistance	≤20 mΩ
Insulation resistance between contacts	≥500 MΩ
Dielectric withstanding voltage contact – contact	≥1000 V DC/AC
Dielectric withstanding voltage contact – screen	≥1500 V DC/AC
Current-carrying capacity at 50°C	1.25 A
PoE+ per IEEE 802.3at	PoE+

Transmission characteristics

10 GbE	supported
Cat.6 _A	ISO/IEC 11801 AM1 and AMD2, Link length: >1 m

tBL[®] - RJ45 DC 6fold Module Cat.6_A ISO/IEC

Product variants & accessories

Art.-No.	Description
TBL-RJ45DCX6	tBL [®] - RJ45 DC 6fold Module Cat.6 _A ISO/IEC
TBL-RJ45DCX6/KT22	tBL [®] - RJ45 DC 6fold Module Cat.6 _A ISO/IEC, termination block AWG 22-24
TBL-RJ45DCX6/KT26	tBL [®] - RJ45 DC 6fold Module Cat.6 _A ISO/IEC, termination block AWG 26-27