

S/FTP Trunk-Patch cord both side 6xRJ45 TM31, UC Future FRNC Cat.6_A grey, Length: xxxx



tde - TP cable assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards. The patch cables and trunk cables are manufactured in many different configurations using highly automated processes. The range of products on offer encompasses the entire spectrum of connector types available on the market. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment.

Each cable application is subjected to a full test procedure and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

S/FTP Trunk-Patch cord both side 6xRJ45 TM31, UC Future FRNC Cat.6_A grey, Length: xxxx

Technical Data

Whip length	Side A (Patchfield-End): Increments according to customer specification
	Side B (Switch-End): Increments according to customer specification

Connectors

Type	RJ45 (TM31), with integreted dwell lever protection
Shielding	shielded
Dimensions Boot	34 mm length
	13.4 mm width
Manufacturer	Hirose (connector)
	tde (boot)
QS-Management Systems Certification	ISO 9001
	ISO 14001
	TL 9000

Connectors

Type	RJ45 (TM31), with integreted dwell lever protection
Shielding	shielded
Dimensions Boot	34 mm length
	13.4 mm width
Manufacturer	Hirose (connector)
	tde (boot)
QS-Management Systems Certification	ISO 9001
	ISO 14001
	TL 9000

Connectors

Type	RJ45 (TM31), with integreted dwell lever protection
Shielding	shielded
Dimensions Boot	34 mm length
	13.4 mm width
Manufacturer	Hirose (connector)
	tde (boot)
QS-Management Systems Certification	ISO 9001
	ISO 14001
	TL 9000

Connectors

S/FTP Trunk-Patch cord both side 6xRJ45 TM31, UC Future FRNC Cat.6_A grey, Length: xxxx

Type	RJ45 (TM31), with integreted dwell lever protection
Shielding	shielded
Dimensions Boot	34 mm length
	13.4 mm width
Manufacturer	Hirose (connector)
	tde (boot)
QS-Management Systems Certification	ISO 9001
	ISO 14001
	TL 9000

Connectors

Type	RJ45 (TM31), with integreted dwell lever protection
Shielding	shielded
Dimensions Boot	34 mm length
	13.4 mm width
Manufacturer	Hirose (connector)
	tde (boot)
QS-Management Systems Certification	ISO 9001
	ISO 14001
	TL 9000

Connectors

Type	RJ45 (TM31), with integreted dwell lever protection
Shielding	shielded
Dimensions Boot	34 mm length
	13.4 mm width
Manufacturer	Hirose (connector)
	tde (boot)
QS-Management Systems Certification	ISO 9001
	ISO 14001
	TL 9000

TP Cable

Application

IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T; 10GBase-T

IEEE 802.5 16 MB; ISDN; TPDDI; ATM

Standards

EN 50173-1; EN 50288-4-2

S/FTP Trunk-Patch cord both side 6xRJ45 TM31, UC Future FRNC Cat.6_A grey, Length: xxxx

ISO/IEC 11801; IEC 61156-6

Flame resistance

LSHF (FRNC): IEC 60332-1; IEC 60754-2; IEC 61034

Construction

Conductor	CU-wire, Ø 0.42 mm (AWG27/7)
Insulation	Foam skin PP, diameter 0.98 mm
Twisting	2 cores to the pair
Pair screening	Al-laminated plastic foil
Cable lay up	4x pimf to the core
Cable Screen	Tinned copper braid
Sheath	LSHF orange RAL 2003
Stranding (6x)	0+6 stranded to the cable core, filler in the centre

Mechanical properties

Minimum bending radius	Without load	≥ 25 mm
	With load	≥ 50 mm
Temperature range	During operation	-20°C to +60°C
	During installation	0°C to +50°C

Electrical properties at 20°C ± 5°C

Loop resistance		≤ 340 Ω/km
Resistance unbalance		≤ 3%
Insulation resistance	(500 V)	≥ 5000 MΩkm
Capacitance	at 800 Hz	Nom. 43 nF/km
Capacitance unbalance		≤ 1600 pF/km
Impedance	100 MHz	(100 ± 15) Ω
Nominal velocity of propagation		ca. 79%
Signal transit time		≤ 427 ns/100m
Delay skew		≤ 12 ns/100m
Test voltage	(DC, 1 min.) core/core & core/screen	1000 V
Coupling resistance	at 1 MHz	25 mΩ/m
	at 10 MHz	15 mΩ/m
	at 30 MHz	30 mΩ/m
Coupling attenuation		75 dB

Electrical Data (nominal) acc. to Cat.7 (at 20°C)

F	Attenuation	NEXT	PS-NEXT	ACR	ELFEXT	PS-ELFEXT	Return loss
MHZ	dB/10m	dB	dB	dB/100m	dB/100m	dB/100m	dB

S/FTP Trunk-Patch cord both side 6xRJ45 TM31, UC Future FRNC Cat.6_A grey, Length: xxxx

1.0	0.3	90	87	87	80	77	23
4.0	0.6	90	87	84	80	77	24
10.0	1.0	90	87	80	80	77	25
16.0	1.3	90	87	77	76	73	25
20.0	1.4	90	87	76	74	71	25
31.2	1.8	90	87	72	70	67	25
62.5	2.6	90	87	64	64	61	23
100.0	3.2	87	84	55	60	57	21
125.0	3.6	85	82	49	58	55	20
155.5	4.0	84	81	44	56	53	19
175.0	4.3	83	80	40	55	52	19
200.0	4.6	82	79	36	54	51	18
250.0	5.1	81	78	30	52	49	18
300.0	5.6	80	77	24	50	47	17
450.0	6.9	77	74	8	47	44	17
600.0	7.9	75	72	-4	44	41	17
750.0	8.7	73	70		42	39	
900.0	9.7	72	69		41	38	
1000.0	10.2	71	68		40	37	

Technical Data

Designation	Li-02YSCH
Type	4x2x0.42L PiMF FRNC
Outer diameter	17.8 mm
Fire load	2094 MJ/km
Fire load	0.582 kWh/m
Weight	272 kg/km
Copper number	144
Tensile force	600 N

Product variants & accessories

Art.-No.	Description
T-H6AZyyN27Mxxxx	S/FTP Trunk-Patch cord both side 6xRJ45 TM31, UC Future FRNC Cat.6 _A grey, Length: xxxx