


tML[®] - FO Trunk Cable MPO/MTP[®] Female/Male 12G50/125 μ OM3 LSOH, Type C, Length: xx



tML[®] - tde Modular Link

tML[®] is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP[®] and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML[®] cabling system as a proven tML[®] standard system and in the highly innovative variants tML[®] Xtended, tML[®] 24 System and now tML[®] 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML[®] - FO patch cord is intended for the connection of tML[®]- FO Modules for migration to 40GbE.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML[®] - FO Trunk Cable MPO/MTP[®] Female/Male 12G50/125 μ OM3 LSOH, Type C, Length: xx

Technical Data

The tML[®]- FO trunk cable is preterminated with MPO/MTP[®]connectors on both ends. The Cable is very slim and flexible. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®]plug has a defined fiber height of 1 - 3.5 μ . The max. adjacent fiber height difference is 0.2 μ m and for all fibers 0.3 μ m. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number.

| | |
|------------|--|
| Cable | Round cable 3 mm, loose tube, LSOH, aqua |
| Connectors | MPO/MTP [®] Female/Male Push Pull (aqua) |
| Pin out | Crossover (TIA/EIA-568-B.1 Methode C) |
| Tests | Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived |
| | QS-Managementsystem ISO 9001, ISO 14001 and TL 9000 |

xx - stands for the cable length in meters (every length available)

FO Connectors

Connector

| | |
|--------------|--|
| Type | MPO/MTP [®] Female Push Pull Locking (aqua) |
| Ferrule | 12 Fiber MM Elite [®] ferrule, PPS |
| Boot colour | Black |
| Manufacturer | tde/US Conec |

Optical Performance

| Fiber | Type | Wavelength | Insertion loss typ. | Insertion loss max. | Return loss min. |
|------------------|----------------------|------------|---------------------|---------------------|------------------|
| 50/125 μ OM3 | MPO/MTP [®] | 850 nm | ≤ 0.14 dB | 0.25 dB | 35 dB |

FO Connectors

Connector

| | |
|--------------|--|
| Type | MPO/MTP [®] Male Push Pull Locking (aqua) |
| Ferrule | 12 Fiber MM Elite [®] ferrule, PPS |
| Boot colour | Black |
| Manufacturer | tde/US Conec |

Optical Performance

| Fiber | Type | Wavelength | Insertion loss typ. | Insertion loss max. | Return loss min. |
|------------------|----------------------|------------|---------------------|---------------------|------------------|
| 50/125 μ OM3 | MPO/MTP [®] | 850 nm | ≤ 0.14 dB | 0.25 dB | 35 dB |

tML[®] - FO Trunk Cable MPO/MTP[®] Female/Male 12G50/125 μ OM3 LSOH, Type C, Length: xx

FO Cables

| | |
|------------------|----------------|
| Standards | EN 50173-5 |
| | IEC 60794-2-20 |
| | ISO/IEC 24764 |
| Flame resistance | IEC 60332-1-2 |
| | IEC 60332-2-2 |
| | IEC 60754-1 |
| | IEC 60754-2 |
| | IEC 61034 |

Cable construction

| | |
|-------------------------|---|
| Type | IVH12G50-OM3 |
| Loose tube | 12 coated fibers within PVC-core tube |
| Wall thickness PVC-tube | 0.20 mm – 0.25 mm |
| Fiber type | MM-OM3, 50/125 μ , Corning ClearCurve OM3 |
| Strength members | Aramid yarn |
| Outer jacket | LSZH (Halogen free, low smoke, flame retardant thermoplastic compound) |
| Jacket color | Aqua, RAL 6027 |
| Identification | "t d e – IVH12G50-MPO-OM3 LSZH" and sequential meter marking + Lot number |

Physical properties

| | |
|--|------------------|
| Outer diameter cable | 3.0 \pm 0.1 mm |
| Diameter PVC-core tube | 1.8 \pm 0.1 mm |
| Max. tensile load | 300 N |
| Min. bending radius | 30 mm |
| Temperature range (storage, installation, operation) | -20°C to +70°C |

FO Fiber

| | |
|-----------------------------------|---|
| Type | Corning ClearCurve [®] 50/125 μ OM3 multimode fiber |
| Optimized Data Rate over Distance | 40/100 Gb/s über 140 m* 10 Gb/s over 300 m 1 Gb/s over 1000 m |
| Standard Compliance | ISO/IEC 11801: type OM3 fiber IEC 60793-2-10: type A1a.2 fiber TIA/EIA: 492AAAC-B ITU: ITU G651.1 |
| * | Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation \leq 3.0 dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4). |

tML[®] - FO Trunk Cable MPO/MTP[®] Female/Male 12G50/125 μ OM3 LSOH, Type C, Length: xx

Optical Specifications

| | |
|--------------------|---|
| Bandwidth | High Performance EMB* (MHz.km): 2000 at 850 nm only Legacy Performance EMB* (MHz.km): 1500 at 850 nm / 500 at 1300 nm |
| Attenuation | At 850 nm max. \leq 2.3 dB/km At 1300 nm max. \leq 0.6 dB/km |
| Macrobend Loss | Mandrel Radius (mm): 37.5 / 15 / 7.5 Number of Turns: 100 / 2 / 2 Induced Attenuation (dB) at 850 nm: \leq 0.05 / \leq 0.1 / \leq 0.2 Induced Attenuation (dB) at 1300 nm: \leq 0.15 / \leq 0.3 / \leq 0.5 |
| Numerical Aperture | 0.200 \pm 0.015 |
| * | Ensured via miniEMBC, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10 Gb/s). |
| ** | OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s). |

Dimensional Specifications

| | |
|--------------------------------|-------------------------|
| Core Diameter | 50.0 \pm 2.5 μ m |
| Cladding Diameter | 125.0 \pm 1.0 μ m |
| Core-Clad Concentricity | \leq 1.5 μ m |
| Cladding Non-Circularity | \leq 1.0% |
| Core Non-Circularity | \leq 5.0% |
| Coating Diameter | 242 \pm 5 μ m |
| Coating-Cladding Concentricity | $<$ 12 μ m |

Environmental

| Environmental Test | Test Condition | Induced Attenuation 850 nm & 1300 nm (dB/km) |
|------------------------------|---------------------------------|--|
| Temperature Dependence | -60°C to +85°C | \leq 0.10 |
| Temperature Humidity Cycling | -10°C to +85°C and 4% to 98% RH | \leq 0.10 |
| Water Immersion | 23°C \pm 2°C | \leq 0.20 |
| Heat Aging | 85°C \pm 2°C | \leq 0.20 |
| Damp Heat | 85°C at 85% RH | \leq 0.20 |
| Operating Temperature Range | -60°C to +85°C | |

Mechanical Specifications

| | |
|------------|--|
| Proof Test | The entire fiber length is subjected to a tensile stress \geq 100 kpsi (0.7 GN/m ²). |
| Length | Fiber lengths available up to 17.6 km/spool. |

Performance Characterizations

| | |
|-------------------------------------|---------------------------------|
| Refractive Index Difference | 1% |
| Effective Group Index of Refraction | 850 nm: 1.480 1300 nm: 1.479 |
| Fatigue Resistance Parameter (nd) | 20 |

tML[®] - FO Trunk Cable MPO/MTP[®] Female/Male 12G50/125 μ OM3 LSOH, Type C, Length: xx

| | |
|----------------------|--|
| Coating Strip Force | Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N) |
| Chromatic Dispersion | Zero Dispersion Wavelength (λ_0): 1295 nm $\leq \lambda_0 \leq$ 1315 nm Zero Dispersion Slope (S0): ≤ 0.101 ps/(nm ² *km) |

Product variants & accessories

| Art.-No. | Description |
|----------------------|---|
| TML-MP/MPP50I12G3Bxx | tML [®] - FO Trunk Cable MPO/MTP [®] Female/Male 12G50/125 μ OM3 LSOH, Type B, Length: xx |
| TML-MP/MPP50I12G3Cxx | tML [®] - FO Trunk Cable MPO/MTP [®] Female/Male 12G50/125 μ OM3 LSOH, Type C, Length: xx |
| TML-MP/MPP50I12G4Bxx | tML [®] - FO Trunk Cable MPO/MTP [®] Female/Male 12G50/125 μ OM4 LSOH, Type B, Length: xx |
| TML-MP/MPP50I12G4Cxx | tML [®] - FO Trunk Cable MPO/MTP [®] Female/Male 12G50/125 μ OM4 LSOH, Type C, Length: xx |