


tML<sup>®</sup> - FO Trunk Cable MPO/MTP<sup>®</sup> Female/Male 12G50/125μ OM3 LSOH, Type C, Length: xx



## tML<sup>®</sup> - tde Modular Link

tML<sup>®</sup> is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup> Xtended, tML<sup>®</sup> 24 System and now tML<sup>®</sup> 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.

The tML<sup>®</sup> - FO patch cord is intended for the connection of tML<sup>®</sup>- FO Modules for migration to 40GbE.



**tde<sup>®</sup> trans data elektronik GmbH**

### Headquarter address:

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

### Sales office address:

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

tML<sup>®</sup> - FO Trunk Cable MPO/MTP<sup>®</sup> Female/Male 12G50/125μ OM3 LSOH, Type C, Length: xx

## Technical Data

The tML<sup>®</sup>- FO trunk cable is preterminated with MPO/MTP<sup>®</sup>connectors on both ends. The Cable is very slim and flexible. The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup>plug has a defined fiber height of 1 - 3.5μ. The max. adjacent fiber height difference is 0.2μm and for all fibers 0.3μm. All system components (modules, trunk cables and patch cords) are co-ordinated for the reaching of the performance particularly. The module is marked with sequential serial number and article number.

Cable	Round cable 3 mm, loose tube, LSOH, aqua
Connectors	MPO/MTP <sup>®</sup> Female/Male Push Pull (aqua)
Pin out	Crossover (TIA/EIA-568-B.1 Methode C)
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

xx - stands for the cable length in meters (every length available)

## FO Connectors

### Connector

Type	MPO/MTP <sup>®</sup> Female Push Pull Locking (aqua)
Ferrule	12 Fiber MM Elite <sup>®</sup> ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

### Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM3	MPO/MTP <sup>®</sup>	850 nm	≤ 0.14 dB	0.25 dB	35 dB

## FO Connectors

### Connector

Type	MPO/MTP <sup>®</sup> Male Push Pull Locking (aqua)
Ferrule	12 Fiber MM Elite <sup>®</sup> ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

### Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125μ OM3	MPO/MTP <sup>®</sup>	850 nm	≤ 0.14 dB	0.25 dB	35 dB

tML<sup>®</sup> - FO Trunk Cable MPO/MTP<sup>®</sup> Female/Male 12G50/125 $\mu$  OM3 LSOH, Type C, Length: xx

## FO Cables

Standards	EN 50173-5
	IEC 60794-2-20
	ISO/IEC 24764
Flame resistance	IEC 60332-1-2
	IEC 60332-2-2
	IEC 60754-1
	IEC 60754-2
	IEC 61034

## Cable construction

Type	IVH12G50-OM3
Loose tube	12 coated fibers within PVC-core tube
Wall thickness PVC-tube	0.20 mm – 0.25 mm
Fiber type	MM-OM3, 50/125 $\mu$ , Corning ClearCurve OM3
Strength members	Aramid yarn
Outer jacket	LSZH (Halogen free, low smoke, flame retardant thermoplastic compound)
Jacket color	Aqua, RAL 6027
Identification	"t d e – IVH12G50-MPO-OM3 LSZH" and sequential meter marking + Lot number

## Physical properties

Outer diameter cable	3.0 $\pm$ 0.1 mm
Diameter PVC-core tube	1.8 $\pm$ 0.1 mm
Max. tensile load	300 N
Min. bending radius	30 mm
Temperature range (storage, installation, operation)	-20°C to +70°C

## FO Fiber

Type	Corning ClearCurve <sup>®</sup> 50/125 $\mu$ OM3 multimode fiber
Optimized Data Rate over Distance	40/100 Gb/s über 140 m* 10 Gb/s over 300 m 1 Gb/s over 1000 m
Standard Compliance	ISO/IEC 11801: type OM3 fiber IEC 60793-2-10: type A1a.2 fiber TIA/EIA: 492AAAC-B ITU: ITU G651.1
*	Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation $\leq$ 3.0 dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4).

tML<sup>®</sup> - FO Trunk Cable MPO/MTP<sup>®</sup> Female/Male 12G50/125 $\mu$  OM3 LSOH, Type C, Length: xx

## Optical Specifications

Bandwidth	High Performance EMB* (MHz.km): 2000 at 850 nm only Legacy Performance EMB* (MHz.km): 1500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. $\leq 2.3$ dB/km At 1300 nm max. $\leq 0.6$ dB/km
Macrobend Loss	Mandrel Radius (mm): 37.5 / 15 / 7.5 Number of Turns: 100 / 2 / 2 Induced Attenuation (dB) at 850 nm: $\leq 0.05$ / $\leq 0.1$ / $\leq 0.2$ Induced Attenuation (dB) at 1300 nm: $\leq 0.15$ / $\leq 0.3$ / $\leq 0.5$
Numerical Aperture	$0.200 \pm 0.015$
*	Ensured via miniEMBc, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10 Gb/s).
**	OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s).

## Dimensional Specifications

Core Diameter	$50.0 \pm 2.5 \mu\text{m}$
Cladding Diameter	$125.0 \pm 1.0 \mu\text{m}$
Core-Clad Concentricity	$\leq 1.5 \mu\text{m}$
Cladding Non-Circularity	$\leq 1.0\%$
Core Non-Circularity	$\leq 5.0\%$
Coating Diameter	$242 \pm 5 \mu\text{m}$
Coating-Cladding Concentricity	$< 12 \mu\text{m}$

## Environmental

Environmental Test	Test Condition	Induced Attenuation 850 nm & 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	$\leq 0.10$
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	$\leq 0.10$
Water Immersion	23°C $\pm$ 2°C	$\leq 0.20$
Heat Aging	85°C $\pm$ 2°C	$\leq 0.20$
Damp Heat	85°C at 85% RH	$\leq 0.20$
Operating Temperature Range	-60°C to +85°C	

## Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress $\geq 100$ kpsi (0.7 GN/m <sup>2</sup> ).
Length	Fiber lengths available up to 17.6 km/spool.

## Performance Characterizations

Refractive Index Difference	1%
Effective Group Index of Refraction	850 nm: 1.480 1300 nm: 1.479
Fatigue Resistance Parameter (nd)	20

tML<sup>®</sup> - FO Trunk Cable MPO/MTP<sup>®</sup> Female/Male 12G50/125μ OM3 LSOH, Type C, Length: xx

Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength ( $\lambda_0$ ): 1295 nm $\leq \lambda_0 \leq$ 1315 nm Zero Dispersion Slope (S0): $\leq 0.101$ ps/(nm <sup>2</sup> *km)

## Product variants & accessories

Art.-No.	Description
TML-MP/MPP50I12G3Bxx	tML <sup>®</sup> - FO Trunk Cable MPO/MTP <sup>®</sup> Female/Male 12G50/125μ OM3 LSOH, Type B, Length: xx
TML-MP/MPP50I12G3Cxx	tML <sup>®</sup> - FO Trunk Cable MPO/MTP <sup>®</sup> Female/Male 12G50/125μ OM3 LSOH, Type C, Length: xx
TML-MP/MPP50I12G4Bxx	tML <sup>®</sup> - FO Trunk Cable MPO/MTP <sup>®</sup> Female/Male 12G50/125μ OM4 LSOH, Type B, Length: xx
TML-MP/MPP50I12G4Cxx	tML <sup>®</sup> - FO Trunk Cable MPO/MTP <sup>®</sup> Female/Male 12G50/125μ OM4 LSOH, Type C, Length: xx