

tSML - Module 19"/0.5U angled blank w/o cover f. 4x FO partial front panels or 4x RJ45 DC 6fold



tSML - tde Semi Modular Link

tSML is a modular developed cabling system, which consists of two core components: module and trunk cable. The system components, preterminated with connectors and tested ex works, facilitate very fast installation of both twisted pair and fiber-optic cables. Ready-made trunk cables, providing a high number of pairs or fibers, can simply be plugged together using patch panels. Up to 96x LC duplex and/or 48 x RJ45 of haven can be accommodated in such a way on 1U. At the heart of the System are MPO/MTP[®] and Telco connectors, with which 12 optical fibers or 24 copper pairs can be connected simultaneously. Fiber-optic and twisted pair modules can be combined on 1U within a panel without difficulty.

For equipping up to four tSML FO partial front panels or four tBL[®] - RJ45 DC 6fold Modules 10GbE.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tSML - Module 19"/0.5U angled blank w/o cover f. 4x FO partial front panels or 4x RJ45 DC 6fold

Technical Data

Box	stainless steel
Front plate	stainless steel
Mounting	Snap-In (4x FO partial front panels or 4x RJ45 DC 6fold)
Cable strain relief	Breakout cable entries, by cable ties
Dimensions	19", 0.5 U, depth: 10.5 cm (outside) / 20.5 cm (centered)
Identification	silk screen at the front
	19" mounting set enclosed
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

Product variants & accessories

Art.-No.	Description
TSML-M-BLIND	tSML - blind plate Snap-In for module 19"/0.5U
TSML-MS-19/0.5HE-CO	tSML - Cover for Module 19"/0.5U angled
TSML-MS-19/0.5HE-KB	tSML - Module 19"/0.5U angled blank w/o cover f. 4x FO partial front panels or 4x RJ45 DC 6fold