

tBL[®] - TP Installation Cable both ends 2x termination block Cat.6_A UC900 SS23 duplex



tBL[®] - tde Basic Link (TP)

tBL[®] tde Basic Link (TP) is a complete system solution for structured cabling in Cat6A for transfer rates of up to 10GbE in real time. The tBL[®] - cabling link corresponds to a permanent link in accordance with ISO / IEC 11801 (EN 50173). The RJ45 modules are available in the form factors Keystone (KS) and Data Center (DC). The compact design of the 6fold RJ45 DC module allows a high packing density of up to 48 RJ45 ports on 1U. The RJ45 module is connected to the tBL[®] - cable termination block by simply plugging. The slim cable termination block can be easily assembled on the cable by using the tBL[®] - crimp tool and is suitable for preterminated cables. The modular design of individual RJ45 modules are interchangeable at any time without termination. The RJ45 modules are optional with a LID - Light ID function available. This feature facilitates searching of related ports within a cable link. A cost effective alternative product is the RJ45 keystone module without cable termination block in the tool-less design.

The system solution is complemented by an extensive portfolio of carrier systems. These include design-capable data outlets, floor box frames, Consolidation points, DIN rail modules and patch panels in 1/2 and 1U.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tBL[®] - TP Installation Cable both ends 2x termination block Cat.6_A UC900 SS23 duplex

Technical Data

xxxx	Length in cm
------	--------------

TP Termination Block

Construction	plastic with insulation displacement connection
Gold plating termination block	30 μ"
Color	transparent yellow
Application	Installation cable with solid wire, AWG 22 to AWG 24 and flex.
	Plug bears small flag-like installation guide with color codes for pin-out according to EIA/TIA 568 A and B.

TP Cable

Construction

Conductor	bare copper wire, Ø 0.56 mm (AWG 23/1)
Insulation	foamskin PE, Ø 1.38 mm
Twisting	2 cores to the pair
Pair screen	Al-laminated plastic foil
Cable lay up	4 pairs (PiMF) to the core
Screen	copper braid, tinned
Sheath	LSHF orange RAL 2003

Mechanical properties

Minimum bending radius	Without load	≥ 30 mm
	With load	≥ 60 mm
Temperature range	During operation	-20°C up to +60°C
	During installation	0°C up to +50°C

Electrical properties at 20°C

Loop resistance		≤ 154 Ω/km
Resistance unbalance		≤ 2%
Insulation resistance	(500 V)	≥ 5000 MΩ*km
Mutual capacitance	at 800 Hz	Nom. 43 nF/km
Capacitance unbalance	(pair/ground)	≤ 1500 pF/km
Characteristic impedance	100 MHz	(100 ± 5) Ω
Nominal velocity of propagation		ca. 79%
Propagation delay		≤ 425 ns/100m
Delay skew		≤ 9 ns/100m
Test voltage	(DC, 1 min) core/core and core/screen	1000 V
Transfer impedance	at 1 MHz	5 mΩ/m
	at 10 MHz	5 mΩ/m

tBL[®] - TP Installation Cable both ends 2x termination block Cat.6_A UC900 SS23 duplex

	at 30 MHz	10 mΩ/m
Coupling attenuation		85 dB
Segregation classification acc. EN 50174-2		"d"

Electrical Data (nominal) acc. to Cat.7 (at 20°C)

F	Attenuation	NEXT	PS-NEXT	ACR	PS-ACR	ELFEXT	PS-ELFEXT	Return loss
MHZ	dB/10m	dB	dB	dB/100m	dB/100m	dB/100m	dB/100m	dB
1.0	1.8	104	101	102	99	105	105	-
4.0	3.4	100	97	97	94	105	102	27
10.0	5.4	100	97	95	92	97	94	30
16.0	6.8	100	97	93	90	93	90	30
20.0	7.7	100	97	92	89	91	88	30
31.2	9.6	100	97	90	87	87	84	30
62.5	13.7	100	97	86	83	81	78	30
100.0	17.4	100	97	83	80	77	74	30
125.0	19.5	95	92	75	72	75	72	26
155.5	21.9	94	91	72	69	73	70	26
175.0	23.3	93	90	70	67	72	69	25
200.0	25.0	92	89	67	64	71	68	25
250.0	28.1	90	87	62	59	69	66	24
300.0	30.9	89	86	58	55	67	64	24
450.0	38,3	87	84	48	45	64	61	23
600.0	44,8	85	82	40	37	61	58	22
750.0	52,0	83	80	31	28	59	56	21
900.0	59,4	82	79	23	20	59	55	20
1000.0	63,1	80	77	17	14	57	54	20

Outer diameter	7.5/15.0 mm
Fire load	1170 MJ/km
	0.326 kWh/m
Weight	150 kg/km
Copper content	76
Tensile force	300 N

Product variants & accessories

Art.-No.	Description
T-T6K/T6K-N23Dxxxx	tBL [®] - TP Installation Cable both ends 2x RJ45 Keystone Modules Cat.6 _A UC900 SS23 duplex
T-T6K/T6K-N23DxxxxL	tBL [®] - TP Installation Cable both ends 2x RJ45 Keystone Modules w. LID Cat.6 _A UC900 SS23 duplex
T-T6K/T6K-N23DxxxxLU	tBL [®] - TP Installation Cable both ends 2x RJ45 Keystone Modules w. LID (one enclosed) Cat.6 _A UC900 SS23 duplex
T-T6K/T6K-N23DxxxxU	tBL [®] - TP Installation Cable both ends 2x RJ45 Keystone Modules (one enclosed) Cat.6 _A UC900 SS23 duplex

tBL[®] - TP Installation Cable both ends 2x termination block Cat.6_A UC900 SS23 duplex

Art.-No.	Description
T-TKT/TKT-N23Dxxxx	tBL [®] - TP Installation Cable both ends 2x termination block Cat.6 _A UC900 SS23 duplex