

tML<sup>®</sup> - TP Trunk Cable both ends RJ45 DC 6fold Module Cat.6<sub>A</sub> UC Future 24x2xAWG26 LSHF



## tML<sup>®</sup> - tde Modular Link

tML<sup>®</sup> is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup> Xtended, tML<sup>®</sup> 24 System and now tML<sup>®</sup> 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML<sup>®</sup> - TP Trunk Cable both ends RJ45 DC 6fold Module Cat.6<sub>A</sub> UC Future 24x2xAWG26 LSHF

## Technical Data

xx	Length in m
----	-------------

### TP RJ45 Modules

System platforms	tML <sup>®</sup> / tSML
	4x tBL <sup>®</sup> - 6fold Modules can be integrated in a tSML - TP Module.
	1x tBL <sup>®</sup> - 6fold Module can be integrated in a tML <sup>®</sup> - TP Module.
Equipping	6x tBL <sup>®</sup> RJ45 DC Module Cat.6 <sub>A</sub>

### TP RJ45 Modules

#### Mechanical properties

Type	RJ45 Jack shielded
Connector standard	IEC 60603-7-5-1
Installation dimension	19.3 x 14.7 mm
Mating force	≤30 N
Mating cycles (RJ45 side)	≥750
Mating cycles (opposite side)	≥100
Housing material	nickel-plated die-cast zinc
Insulation components material	PC aqua
Gold plating in contact area	30 μ <sup>2</sup>
Contacting	AWG 27-22
Cable diameter	5-10 mm

#### Environmental requirements

Connection class	IP20
Temperature range	-40°C to +70°C

#### Electrical properties

Contact resistance	≤20 mΩ
Insulation resistance between contacts	≥500 MΩ
Dielectric withstanding voltage contact – contact	≥1000 V DC/AC
Dielectric withstanding voltage contact – screen	≥1500 V DC/AC
Current-carrying capacity at 50°C	1.25 A
PoE+ per IEEE 802.3at	PoE+

## tML<sup>®</sup> - TP Trunk Cable both ends RJ45 DC 6fold Module Cat.6<sub>A</sub> UC Future 24x2xAWG26 LSHF

### Transmission characteristics

10 GbE	supported
Cat.6 <sub>A</sub>	ISO/IEC 11801 AM1 and AMD2, Link length: >1 m

### TP Termination Block

Construction	plastic with insulation displacement connection
Gold plating termination block	30 μ"
Color	transparent white
Application	Flex cable AWG 26 - AWG 27, alternative AWG 26 Solid Wire
	Plug bears small flag-like installation guide with color codes for pin-out according to EIA/TIA 568 A and B.

### TP Cable

#### Construction

Type	UC FUTURE COMPACT AWG26/1 Cat.7 S/FTP 24P
Conductor	Bare copper wire, diameter 0.4 mm (AWG26)
Insulation	Foam-skin PP, diameter 1.0 mm
Twisting	2 insulated wires to the pair
Pair screening	Pet-Al foil around each pair
Stranding	6 (5+1) bundles with 4 foiled pairs blue, orange, green, brown
	Coloured tapes are around each bundle
Screen	Tinned copper braid 85% coverage
Sheath	LSHF-FR, diameter 13.9 mm

#### Application

IEEE 802.3: 10Base-T; 100Base-T; 10GBase-T, ISDN; xDSL

IEEE 802.5 16 MB; ISDN; TPDDI; ATM155Mbit/s

The conductor diameter is smaller compared to the standard installation cables. This leads to an increased attenuation and therefore the operating distance is reduced (60m instead of 90m installation cable in standard permanent link).

#### Standards

IEC 61156-6 work area cable

ISO/IEC 11801 2<sup>nd</sup> ed.

EN 50173-5

EN 50288-4-2

#### Flame resistance

PVC IEC 60332-1

LSHF-FR IEC 60332-3-24; IEC 60754-2; IEC 61034 ; EN 50399 Class D<sub>ca</sub>

## tML<sup>®</sup> - TP Trunk Cable both ends RJ45 DC 6fold Module Cat.6<sub>A</sub> UC Future 24x2xAWG26 LSHF

### Mechanical properties

Minimum bending radius	Without load	≥ 55 mm
	With load	≥ 110 mm
Temperature range	During operation	-20°C up to +60°C
	During installation	10°C up to +40°C

### Electrical properties at 20°C

Loop resistance		≤ 280 Ω/km
Resistance unbalance		≤ 2%
Test voltage	core/core	1000 V <sub>DC</sub> 1 min
	core/screen	1000 V <sub>DC</sub> 1 min
Capacitance	800 Hz	Nom. 44 nF/km
Capacitance unbalance		≤ 1600 pF/km
Impedance	100 MHz	100 Ω ± 5 Ω
Nominal velocity of propagation		ca. 76%
Insulation resistance	500 V	≥ 2000 MΩkm
Transfer impedance	at 1 MHz	≤ 5 mΩ /m
	at 10 MHz	≤ 5 mΩ /m
	at 30 MHz	≤ 10 mΩ /m

### Electrical Data (nominal) acc. to Cat.7 (at 20°C)

F	Attenuation	NEXT	PS-NEXT	ELFEXT	PS-ELFEXT	Return loss
MHZ	dB/10m	dB	dB	dB/100m	dB/100m	dB
1.0	0.3	90	87	80	77	23
4.0	0.6	90	87	80	77	24
10.0	1.0	90	87	80	77	25
16.0	1.3	90	87	76	73	25
20.0	1.4	90	87	74	71	25
31.2	1.8	90	87	70	67	25
62.5	2.6	90	87	64	61	23
100.0	3.2	87	84	60	57	21
125.0	3.6	85	82	58	55	20
155.5	4.0	84	81	56	53	19
175.0	4.3	83	80	55	52	19
200.0	4.6	82	79	54	51	18
250.0	5.1	81	78	52	49	18
300.0	5.6	80	77	50	47	17
450.0	6.9	77	74	47	44	17
600.0	7.9	75	72	44	41	17

tML<sup>®</sup> - TP Trunk Cable both ends RJ45 DC 6fold Module Cat.6<sub>A</sub> UC Future 24x2xAWG26 LSHF

## Technical Data

Designation	J-02YS(ST)CH
Type	24x2x0.4PiMF
Outer diameter	13.9 mm
Fire load	2.171 MJ/km
Fire load	0.603 kWh/m
Reaction to Fire	D <sub>ca</sub> -s2, d2, a1
Weight	230 kg/km
Copper content	115 kg/km
Tensile force	500 N

## Product variants & accessories

Art.-No.	Description
TML-MS06RJ45C26-xx	tML <sup>®</sup> - TP Trunk Cable both ends RJ45 DC 6fold Module Cat.6 <sub>A</sub> UC Future 24x2xAWG26 LSHF
TML-MS06RJ45C26-xxL	tML <sup>®</sup> - TP Trunk Cable both ends RJ45 DC 6fold Module w. LID Cat.6 <sub>A</sub> UC Future 24x2xAWG26 LSHF
TML-MS06RJ45C26-xxLU	tML <sup>®</sup> - TP Trunk Cable both ends RJ45 DC 6fold Module w. LID (one enclosed) Cat.6 <sub>A</sub> UC Future 24x2xAWG26 LSHF
TML-MS06RJ45C26-xxU	tML <sup>®</sup> - TP Trunk Cable both ends RJ45 DC 6fold Module (one enclosed) Cat.6 <sub>A</sub> UC Future 24x2xAWG26 LSHF
TML-TKT/TKT-N26Cxxx	tML <sup>®</sup> - TP Trunk Cable both ends preterminated 6x termination block Cat.6 <sub>A</sub> UC Future 24x2xAWG26 LSHF