

tML<sup>®</sup> 24 - FO Patch cord both sides 1x 24F MPO Female 24G50/125µ OM4, Type A, Length: xxx in m



## tML<sup>®</sup> - tde Modular Link

tML<sup>®</sup> is a patented, modular cabling system consisting of the three key components module, trunk cable and rack mount enclosure. The system components are 100 percent manufactured, pre-assembled and tested in Germany. They enable plug-and-play installation on site – especially in data centres, but also in industrial environments – within the shortest possible time. Heart of the system are the rear MPO/MTP<sup>®</sup> and Telco connectors, which can be used to connect at least six or twelve ports at a time. Depending on the module configuration, transfer rates of up to 200G are currently possible with SR4. The fibre optic and TP modules can be used together in a module carrier with a very high port density. The tde offers its tML<sup>®</sup> cabling system as a proven tML<sup>®</sup> standard system and in the highly innovative variants tML<sup>®</sup> Xtended, tML<sup>®</sup> 24 System and now tML<sup>®</sup> 32 System for extreme scalability and very easy migration to higher transmission rates such as 40G, 100G, 200G and 400G.



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 914 36 99  
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tML<sup>®</sup> 24 - FO Patch cord both sides 1x 24F MPO Female 24G50/125 $\mu$  OM4, Type A, Length: xxx in m

## Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5 $\mu$ . The max. adjacent fiber height difference is 0.2 $\mu$ m and for all fibers 0.3 $\mu$ m.

Cable	Round cable 3.6 mm, loose tube, LSOH, magenta
Connectors	MPO/MTP <sup>®</sup> Push Pull (magenta)
Pin out	Type A
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

## FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP<sup>®</sup> plug has a defined fiber height of 1 - 3.5 $\mu$ . The max. adjacent fiber height difference is 0.2 $\mu$ m and for all fibers 0.3 $\mu$ m.

### Connector

Type	MPO/MTP <sup>®</sup> Female Push Pull Locking (magenta)
Ferrule	24 Fiber MM Elite <sup>®</sup> ferrule, PPS
Boot colour	Red
Temperature range	-40°C to +75°C
Manufacturer	tde/US Conec

### Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 $\mu$ OM4	MPO/MTP <sup>®</sup>	850 nm	≤ 0.12 dB	0.25 dB	35 dB

## FO Cables

Standards	EN 50173-5
	IEC 60794-2-20
	ISO/IEC 24764

### Construction

Type	IVH24G50-OM4
Fiber	24 primary coated fibres nominally 242 $\mu$ m, arranged in 2 groups of 12 fibres, Group 1: Red id tread Group 2: Green id tread
Fiber colors	According to TIA/EIA 598-C also in agreement with IEC 60304: 1-12: Blue, orange, green, brown, grey, white, red, black, yellow, violet, pink and aqua

tML<sup>®</sup> 24 - FO Patch cord both sides 1x 24F MPO Female 24G50/125 $\mu$  OM4, Type A, Length: xxx in m

	13-24: Blue, orange, green, brown, grey, white, red, transparent, yellow, violet, pink and aqua (with add. ring mark)
Strength member	Ultra high modulus Aramid yarns
Sheath	Halogen free, flame resistant thermoplastic sheathing compound acc. to EN 50290-2-27, UV stabilised
Sheath colors	Magenta, RAL 4003

## Fire rating

IEC 60332-1-2	Pass
IEC 60332-2-2	Pass
IEC 60754-1	No halogens
IEC 60754-2	No acid matters
IEC 61034-2	No dense smoke

## Heat of combustion

200 MJ/km	0.5 KWh/m
-----------	-----------

## Physical properties IEC60974-1-2

Outer diameter cable	$\varnothing$ 3.6 mm +0.1 mm -0.3 mm
Diameter PVC-core tube	2.0 $\pm$ 0.1 mm
Wall thickness PVC-core tube	0.35 mm – 0.40 mm
Weight	11 kg/km
Tensile strength (dynamic)	220 N
Tensile strength (permanent)	110 N
Compressive strength (crush)	400 N
Impact	4 Nm, R= 12.5 mm
Kink	No Kink
Min. Bending radius	R = 20 mm
Temperature range	Operation and installation: -0°C to 50°C. Storage: -20°C to 50°C

## FO Fiber

Type	Corning ClearCurve <sup>®</sup> 50/125 $\mu$ OM4 multimode fiber
Optimized Data Rate over Distance	40/100 Gb over 170 m* 10 Gb/s over 550 m 1 Gb/s over 1100 m
Standard Compliance	ISO/IEC 11801: type OM4 fiber** IEC 60793-2-10: type A1a.3 fiber** TIA/EIA: 492AAAD ITU: ITU G651.1
*	Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation $\leq$ 3.0 dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4)

tML<sup>®</sup> 24 - FO Patch cord both sides 1x 24F MPO Female 24G50/125µ OM4, Type A, Length: xxx in m

\*\* Assumes IEC draft standard is harmonized with 492AAAD which was approved by TIA

## Optical Specifications

Bandwidth	High Performance EMB* (MHz.km): 4700 at 850 nm only Legacy Performance EMB** (MHz.km): 3500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. ≤ 2.3 dB/km At 1300 nm max. ≤ 0.6 dB/km
Macrobend Loss	Mandrel Radius (mm): 37.2 / 15 / 7.5 Number of Turns: 100 / 2 / 2 Induced Attenuation (dB) at 850 nm: ≤ 0.05 / ≤ 0.1 / 0.2 Induced Attenuation (dB) at 1300 nm: ≤ 0.15 / ≤ 0.3 / ≤ 0.5
Numerical Aperture	0.200 ± 0.015
*	Ensured via miniEMBc, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10Gb/s)
**	OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s)

## Dimensional Specifications

Core Diameter	50.0 ± 2.5 µm
Cladding Diameter	125.0 ± 1.0 µm
Core-Clad Concentricity	≤ 1.5 µm
Cladding Non-Circularity	≤ 1.0%
Core Non-Circularity	≤ 5.0%
Coating Diameter	242 ± 5 µm
Coating-Cladding Concentricity	< 12 µm

## Environmental

Environmental Test	Test Condition	Induced Attenuation 850 nm & 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	≤ 0.10
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	≤ 0.10
Water Immersion	23°C ± 2°C	≤ 0.20
Heat Aging	85°C ± 2°C	≤ 0.20
Damp Heat	85°C at 85% RH	≤ 0.20
Operating Temperature Range	-60°C to +85°C	

## Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress ≥ 100 kpsi (0.7 GN/m <sup>2</sup> ).
Length	Fiber lengths available up to 17.6 km/spool.

tML<sup>®</sup> 24 - FO Patch cord both sides 1x 24F MPO Female 24G50/125 $\mu$  OM4, Type A, Length: xxx in m

## Performance Characterizations

Refractive Index Difference	1%
Effective Group Index of Refraction	850 nm: 1.480 1300 nm: 1.479
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength ( $\lambda_0$ ): 1295 nm $\leq \lambda_0 \leq$ 1315 nm Zero Dispersion Slope ( $S_0$ ): $\leq 0.101$ ps/(nm <sup>2</sup> *km)

## Product variants & accessories

Art.-No.	Description
TML-M2/M2-09I24E-Axxx	tML <sup>®</sup> 24 - FO Patch cord both sides 1x 24F MPO Female 24E9/125 $\mu$ OS2, Type A, Length: xx in m
TML-M2/M2-50I24G3Axxx	tML <sup>®</sup> 24 - FO Patch cord both sides 1x 24F MPO Female 24G50/125 $\mu$ OM3, Type A, Length: xxx in m
TML-M2/M2-50I24G4Axxx	tML <sup>®</sup> 24 - FO Patch cord both sides 1x 24F MPO Female 24G50/125 $\mu$ OM4, Type A, Length: xxx in m
TML-M2/M2-50I24G5Axxx	tML <sup>®</sup> 24 - FO Patch cord both sides 1x 24F MPO Female 24G50/125 $\mu$ OM5, Type A, Length: xxx in m