

tSML - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125 μ OM4 LSHF, Type C, Length xxx in

m



tSML - tde Semi Modular Link

tSML is a modular developed cabling system, which consists of two core components: module and trunk cable. The system components, preterminated with connectors and tested ex works, facilitate very fast installation of both twisted pair and fiber-optic cables. Ready-made trunk cables, providing a high number of pairs or fibers, can simply be plugged together using patch panels. Up to 96x LC duplex and/or 48 x RJ45 of haven can be accommodated in such a way on 1U. At the heart of the System are MPO/MTP[®] and Telco connectors, with which 12 optical fibers or 24 copper pairs can be connected simultaneously. Fiber-optic and twisted pair modules can be combined on 1U within a panel without difficulty.



tde[®] trans data elektronik GmbH

Headquarter address:

Lingener Str. 2
D-49626 Bippen/Ohrte
Tel.: +49 5435 9511 0
Fax.: +49 5435 9511 32

Sales office address:

Prinz-Friedrich-Karl-Str. 46
D-44135 Dortmund
Tel.: +49 231 914 36 99
Fax.: +49 231 914 31 29

info@tde.de | www.tde.de

tSML - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125µ OM4 LSHF, Type C, Length xxx in m

Technical Data

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

Cable	Universal Cable
Connectors	MPO/MTP [®] Push Pull (magenta)
Pin out	Methode C
Tests	Interferometer, Insertion Loss, Return Loss and Visual Final Inspection; all measured values are electronically archived
	QS-Managementsystem ISO 9001, ISO 14001 and TL 9000

FO Connectors

The end faces of the connectors are optimized by means of Lasercleaving and machine polish. The MPO/MTP[®] plug has a defined fiber height of 1 - 3.5µ. The max. adjacent fiber height difference is 0.2µm and for all fibers 0.3µm.

Connector

Type	MPO/MTP [®] Female Push Pull Locking (Magenta)
Ferrule	12 Fiber MM Elite [®] ferrule, PPS
Boot colour	Black
Manufacturer	tde/US Conec

Optical Performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125µ OM4	MPO/MTP [®]	850 /1300 nm	≤ 0.12 dB	0.25 dB	35 dB

FO Fan-Out

Ø Single unit length	3.0 mm
Shortest Single unit length	68 ± 5 cm
Highest Single unit length	78 ± 5 cm
Number of stepping	1

FO Cables

Mechanical characteristics

Temperature range	Storage -25 to +70°C, IEC 60794-1-22 F1
	Pulling in -10 to +50°C

tSML - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125 μ OM4 LSHF, Type C, Length xxx in
m

	Operation -25 to +60°C
Tensile performance	IEC 60794-1-21 E1
Crush resistance	IEC 60794-1-21 E3
Impact	IEC 60794-1-21 E4
Repeated bending	IEC 60794-1-21 E6
Torsion	IEC 60794-1-21 E7
Bend	IEC 60794-1-21 E11
Water penetration	IEC 60794-1-22 F5

General characteristics

Sheath colour	green, similar to RAL 6016
Zero halogen, no corrosive gases	IEC 60754-1/-2, EN 60754-1/-2, VDE 0482-754-1/-2
Flame propagation	IEC 60332-1-2, EN 60332-1-2, VDE 0482-332-1-2
Flame spread	IEC 60332-3-24, EN 50266-2-4, VDE 0482-266-2-4
Smoke density	IEC 61034-1/-2, EN 61034-1/-2, VDE 0482-1034-1/-2
Reaction to fire (Euroclasses)	EN 13501-6: E _{ca}

Cabletype	Universal U-DQ(ZN)BH for indoor and outdoor use
	non metallic, dry interstices, rodent protection, flame retardant, in accordance with IEC 60332.1 and IEC 60332.3 C
Fibertype	Corning G50/125 OM4
No. of fibers	96
Loose tube	8
Sheath \varnothing	13.5 mm
Weight	198 kg/km
Bending radius	205 mm
Tensile load	6000 N
Crush resistance	3000 N continuous 5000 N short term
Fire load	808 kWh/km 3200 MJ/km

Length tolerances (prefabricated with plugs)

Tolerances for lengths up to 40m	± 100 cm
Tolerances for lengths up to 100m	± 100 cm
Tolerances for lengths from 100m	$\pm 2\%$

FO Fiber

tSML - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125 μ OM4 LSHF, Type C, Length xxx in m

Optical properties

Attenuation typical (cabled)	850 nm: 2.5 / 1300 nm: 0.5 dB/km
Attenuation maximum (cabled)	850 nm: 2.7 / 1300 nm: 0.7 dB/km
OFL bandwidth as per TIA/EIA 455-204 and IEC 60793-1-41	850 nm: 3500 / 1300 nm: 500 MHz x km
High-Performance EMB bandwidth as per TIA/EIA 455-220A and IEC 60793-1-49	850 nm: 4700 / 1300 nm: 4700 MHz x km
Refractive Index	850 nm: 1.480 / 1300 nm: 1.479

Technical properties

Bending radius	No. of windings (turns)	Max. induced attenuation
37.5 mm	100	850 nm: ≤ 0.05 / 1300 nm: ≤ 0.15 dB/km
15 mm	2	850 nm: ≤ 0.1 / 1300 nm: ≤ 0.3 dB/km
7.5 mm	2	850 nm: ≤ 0.2 / 1300 nm: ≤ 0.5 dB/km

Geometrical and mechanical characteristics

Numerical Aperture	0.200 +/- 0.015
Core \varnothing	50.0 +/- 2.5 μ m
Maximum Core Non-Circularity	5 %
Cladding \varnothing	125.0 +/- 1.0 μ m
Maximum Cladding Non-Circularity	1.0 %
Maximum Cladding/Core Concentricity Error	1.5 μ m
Maximum Coating Concentricity Error	12 μ m
Coating \varnothing	242 +/- 5 μ m
Test load	100 kpsi

Product variants & accessories

Art.-No.	Description
TSML-MP/MP09B96Exxx	tSML - FO Trunk Cable 8x MPO Female/8x MPO Female 96E9/125 μ OS2 LSHF, Type C, Length: xxx in m
TSMLMP/MP50B96G3-xxx	tSML - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125 μ OM3 LSHF, Type C, Length xxx in m
TSMLMP/MP50B96G4-xxx	tSML - FO Trunk Cable 8x MPO Female/8x MPO Female 96G50/125 μ OM4 LSHF, Type C, Length xxx in m