


FO-Patch cord LC/SC tde 50/125 $\mu$  OM3 Duplex FlatTwin LSOH Length: xxxxx



## tde - Fiber Optic Assemblies

The tde patch and trunk cables are manufactured completely at the German facility in Ohrte. Production processes at tde meet the latest standards, and the company has one of the most up-to-date fiber optic assembly houses in Europe. Fiber optic patch cables and trunk cables are manufactured in many different configurations using highly automated processes on two independent mass production lines. The range of products on offer encompasses the entire spectrum of connector types available on the market. Production capacity is around 100,000 fiber optic connectors per month, and this can be ramped up easily whenever required. To guarantee consistently top quality, only the best components from renowned vendors are used. All tde production staff have the necessary qualifications and education, and have been well trained in using specialist technical equipment such as laser cleavers and glue-dispensing robots.

Each cable application is subjected to a full test procedure comprising interferometer measurements, insertion loss and return loss measurements and a final visual inspection to ensure that only 100% error-free products are shipped to the customer.

Products made by tde perform at least internationally accepted quality standards and norms. The quality management system is ISO 9001, ISO 14001 and TL9000 certified.



**tde<sup>®</sup> trans data elektronik GmbH**

**Headquarter address:**

Lingener Str. 2  
D-49626 Bippen/Ohrte  
Tel.: +49 5435 9511 0  
Fax.: +49 5435 9511 32

**Sales office address:**

Prinz-Friedrich-Karl-Str. 46  
D-44135 Dortmund  
Tel.: +49 231 8805 61 13  
Fax.: +49 231 8805 61 15

info@tde.de | www.tde.de

FO-Patch cord LC/SC tde 50/125 $\mu$  OM3 Duplex FlatTwin LSOH Length: xxxxx

## Technical Data

### FO Connectors

Connector Type	LC Unibody Duplex
Housing	Plastic, Aqua
Ferrule	Zirconia Straight Split, Spring-loaded Axially
Ferrule Hole	126 $\mu$
Mating Cycles	1.000
Operating Temperature	-40°C up to +75°C
Strain Relief to	100 N
Manufacturer	tde
Simplex / Duplex Clip	with Duplex Clip

### Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 $\mu$ OM3	LC	850 nm	$\leq$ 0.25 dB	0.45 dB	30 dB

### FO Connectors

Connector Type	SC Duplex
Housing	Plastic, Aqua
Ferrule	Zirconia Straight Split, Spring-loaded Axially
Ferrule Hole	126 $\mu$
Mating Cycles	1.000
Operating Temperature	-40°C up to +75°C
Strain Relief to	150 N
Manufacturer	tde
Simplex / Duplex Clip	with Duplex Clip

### Optical performance

Fiber	Type	Wavelength	Insertion loss typ.	Insertion loss max.	Return loss min.
50/125 $\mu$ OM3	SC	850 nm	$\leq$ 0.25 dB	0.45 dB	30 dB

## FO Cables

### Mechanical characteristics

Temperature range	Operation: -20 to +60°C IEC 60794-2-10 -10 to +60°C for assembled patch cords
Tensile performance	IEC 60794-1-21 E1 A
Crush resistance	IEC 60794-1-21 E3
Impact	IEC 60794-1-21 E4

## FO-Patch cord LC/SC tde 50/125 $\mu$ OM3 Duplex FlatTwin LSOH Length: xxxxx

Repeated bending	IEC 60794-1-21 E6
Torsion	IEC 60794-1-21 E7
Bend	IEC 60794-1-21 E11 A

### General characteristics

Sheath colour	G50/125 OM3 aqua, RAL 6027
Zero halogen, no corrosive gases	IEC 60754-1/-2, EN 60754-1/-2, VDE 0482-754-1/-2
Flame propagation	EC 60332-1-2, EN 60332-1-2, VDE 0482-332-1-2, SEV TP 20B/3C 3.4.1.1
Smoke density	IEC 61034-1/-2, EN 61034-1/-2, VDE 0482-1034-1/-2
Reaction to fire (Euroclasses)	EN 13501-6: D <sub>ca</sub> -s2,d1,a1

### Optical characteristics

Fibertype	MM-OM3, 50/125 $\mu$	
Numerical aperture	0.200 $\pm$ 0.015	
Core $\varnothing$	50 $\pm$ 2.5 $\mu$ m	
Max. Core non-circularity	5 %	
Cladding $\varnothing$	125 $\pm$ 2 $\mu$ m	
Max. Cladding non-circularity	1.0 %	
Max. Cladding/Core concentricity error	1.5 $\mu$ m	
Max. Cladding/Core concentricity error	12 $\mu$ m	
Coating $\varnothing$	242 $\pm$ 5 $\mu$ m	
Proof test	100 kpsi	
Wavelength	850 nm	1300 nm
Attenuation typ. (cabled)	2.5 dB/km	0.5 dB/km
Attenuation max. (cabled)	2.7 dB/km	0.7 dB/km
OFL Bandbreite per TIA/EIA 455-204 and IEC 60793-1-41	1500 MHz x km	500 MHz x km
High Performance EMB, minEMBc, per TIA/EIA 455-220A and IEC 60793-1-49	2000 MHz x km	
Refractive index	1.480	1.479

Description	Duplex I-K(ZN)HH
Cable $\varnothing$	4.8 x 3.2 mm
Weight	21 kg/km
Bending radius	50 mm
Tensile load	200 N
Crush resistance short term	3000 N/cm
Fire load	100 kWh/km
Fire load	360 MJ/km

### FO Fiber

Type	Corning ClearCurve <sup>®</sup> 50/125 $\mu$ OM3 multimode fiber
------	--

## FO-Patch cord LC/SC tde 50/125 $\mu$ OM3 Duplex FlatTwin LSOH Length: xxxxx

Optimized Data Rate over Distance	40/100 Gb/s über 140 m* 10 Gb/s over 300 m 1 Gb/s over 1000 m
Standard Compliance	ISO/IEC 11801: type OM3 fiber IEC 60793-2-10: type A1a.2 fiber TIA/EIA: 492AAAC-B ITU: ITU G651.1
*	Distances specified in the 40G/100G per IEEE 802.3ba standard are 150m on OM4 and 100m on OM3; Corning fibers are manufactured to tighter dispersion specifications and thereby support the extended distances shown in the table (assuming cable attenuation $\leq 3.0$ dB/km and same 1.0 dB of connector loss for OM3 that the standard requires for OM4).

### Optical Specifications

Bandwidth	High Performance EMB* (MHz.km): 2000 at 850 nm only Legacy Performance EMB* (MHz.km): 1500 at 850 nm / 500 at 1300 nm
Attenuation	At 850 nm max. $\leq 2.3$ dB/km At 1300 nm max. $\leq 0.6$ dB/km
Macrobend Loss	Mandrel Radius (mm): 37.5 / 15 / 7.5 Number of Turns: 100 / 2 / 2 Induced Attenuation (dB) at 850 nm: $\leq 0.05 / \leq 0.1 / \leq 0.2$ Induced Attenuation (dB) at 1300 nm: $\leq 0.15 / \leq 0.3 / \leq 0.5$
Numerical Aperture	0.200 $\pm$ 0.015
*	Ensured via miniEMBc, per TIA/EIA 455-220A and IEC 60793-1-49, for high performance laser-based systems (up to 10 Gb/s).
**	OFL BW, per TIA/EIA 455-204 and IEC 60793-1-41, for legacy and LED-based systems (typically up to 100 Mb/s).

### Dimensional Specifications

Core Diameter	50.0 $\pm$ 2.5 $\mu$ m
Cladding Diameter	125.0 $\pm$ 1.0 $\mu$ m
Core-Clad Concentricity	$\leq 1.5$ $\mu$ m
Cladding Non-Circularity	$\leq 1.0\%$
Core Non-Circularity	$\leq 5.0\%$
Coating Diameter	242 $\pm$ 5 $\mu$ m
Coating-Cladding Concentricity	$< 12$ $\mu$ m

### Environmental

Environmental Test	Test Condition	Induced Attenuation 850 nm & 1300 nm (dB/km)
Temperature Dependence	-60°C to +85°C	$\leq 0.10$
Temperature Humidity Cycling	-10°C to +85°C and 4% to 98% RH	$\leq 0.10$
Water Immersion	23°C $\pm$ 2°C	$\leq 0.20$
Heat Aging	85°C $\pm$ 2°C	$\leq 0.20$
Damp Heat	85°C at 85% RH	$\leq 0.20$
Operating Temperature Range	-60°C to +85°C	

## FO-Patch cord LC/SC tde 50/125 $\mu$ OM3 Duplex FlatTwin LSOH Length: xxxxx

### Mechanical Specifications

Proof Test	The entire fiber length is subjected to a tensile stress $\geq 100$ kpsi (0.7 GN/m <sup>2</sup> ).
Length	Fiber lengths available up to 17.6 km/spool.

### Performance Characterizations

Refractive Index Difference	1%
Effective Group Index of Refraction	850 nm: 1.480 1300 nm: 1.479
Fatigue Resistance Parameter (nd)	20
Coating Strip Force	Dry: 0.6 lbs (2.7N) Wet: 14 days in 23°C water soak: 0.6 lbs (2.7N)
Chromatic Dispersion	Zero Dispersion Wavelength ( $\lambda_0$ ): 1295 nm $\leq \lambda_0 \leq$ 1315 nm Zero Dispersion Slope (S0): $\leq 0.101$ ps/(nm <sup>2</sup> *km)

### Product variants & accessories

Art.-No.	Description
L-LC/SC09TMxxxxx	FO-Patch cord LC/SC tde 9/125 $\mu$ OS2 Duplex FlatTwin LSOH Length: xxxxx
L-LC/SC50TM3-xxxxx	FO-Patch cord LC/SC tde 50/125 $\mu$ OM3 Duplex FlatTwin LSOH Length: xxxxx
L-LC/SC50TM4-xxxxx	FO-Patch cord LC/SC tde 50/125 $\mu$ OM4 Duplex FlatTwin LSOH Length: xxxxx
L-LC/SC50TMxxxxx	FO-Patch cord LC/SC tde 50/125 $\mu$ OM2 Duplex FlatTwin LSOH Length: xxxxx
L-LC/SC62TMxxxxx	FO-Patch cord LC/SC tde 62,5/125 $\mu$ OM1 Duplex FlatTwin LSOH Length: xxxxx